High Voltage C0G Dielectric, 500 – 3,000 VDC (Commercial Grade)



Overview

KEMET's High Voltage surface mount MLCCs in C0G dielectric feature a 125°C maximum operating temperature and are considered "stable." The Electronics Industries Alliance (EIA) characterizes C0G dielectric as a Class I material. Components of this classification are temperature compensating and are suited for resonant circuit applications or those where Q and stability of capacitance characteristics are required. C0G exhibits no change in capacitance with respect to time and voltage and boasts a negligible change in capacitance with reference to ambient temperature. Capacitance change is limited to ±30ppm/°C from -55°C to +125°C.

These devices exhibit low ESR at high frequencies and find conventional use as snubbers or filters in applications such as switching power supplies and lighting ballasts. Their exceptional performance at high frequencies has made high voltage MLCC's the preferred dielectric choice of design engineers worldwide. In addition to their use in power supplies, these capacitors are widely used in industries related to automotive(hybrid), telecommunications, medical, military, aerospace, semiconductors and test/diagnostic equipment.

In addition to Commercial Grade, Automotive Grade devices are available which meet the demanding Automotive Electronics Council's AEC-Q200 qualification requirements.



Open PDF in Adobe Reader for full functionality

Ordering Information

C	1210	C	332	J	C	G	Α	C	TU
Ceramic	Case Size (L" x W")	Specification/ Series	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/ Design	Termination Finish ²	Packaging/ Grade (C-Spec)
	0805 1206 1210 1808 1812 1825 2220 2225	C = Standard	Two significant digits + number of zeros.	$B = \pm 0.10 \text{ pF}$ $C = \pm 0.25 \text{ pF}$ $D = \pm 0.5 \text{ pF}$ $F = \pm 1\%$ $G = \pm 2\%$ $J = \pm 5\%$ $K = \pm 10\%$ $M = \pm 20\%$	C = 500 B = 630 D = 1,000 F = 1,500 G = 2,000 Z = 2,500 H = 3,000	G = C0G	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table" below

¹ Additional capacitance tolerance offerings may be available. Contact KEMET for details.

² Additional termination finish options may be available. Contact KEMET for details.



Packaging C-Spec Ordering Options Table

Packaging Type ¹	Packaging/Grade Ordering Code (C-Spec)
Bulk Bag / Unmarked	Not required (Blank)
7" Reel / Unmarked	TU
7" Reel / Unmarked / 2 mm pitch ²	7081
13" Reel / Unmarked / 2 mm pitch ²	7082

¹ Default packaging is "Bulk Bag". An ordering code C-Spec is not required for "Bulk Bag" packaging.

Benefits

- · -55°C to +125°C operating temperature range
- · Lead (Pb)-Free, RoHS and REACH compliant
- EIA 0805, 1206, 1210, 1808, 1812, 1825, 2220, and 2225 case sizes
- DC voltage ratings of 500 V, 630 V, 1 KV, 1.5 KV, 2 KV, 2.5 KV, and 3 KV
- Capacitance offerings ranging from 1 pF to 0.039 μF
- Available capacitance tolerances of ±0.10 pF, ±0.25 pF, ±0.5 pF, ±1%, ±2%, ±5%, ±10%, and ±20%
- No piezoelectric noise
- · Extremely low ESR and ESL
- High thermal stability
- High ripple current capability

- Preferred capacitance solution at line frequencies & into the MHz range
- · No capacitance change with respect to applied rated DC voltage
- Negligible capacitance change with respect to temperature from -55°C to +125°C
- No capacitance decay with time
- · Non-polar device, minimizing installation concerns
- Automotive (AEC-Q200) grade available
- 100% pure matte tin-plated termination finish allowing for excellent solderability
- SnPb plated termination finish option available upon request (5% Pb minimum)

Applications


Typical applications include switch mode power supplies (input filters, resonators, tank circuits, snubbed circuits, output filters), high voltage coupling and DC blocking, lighting ballasts, voltage multiplier circuits, DC/DC converters and coupling capacitors in Ćuk converters. Markets include power supply, LCD fluorescent backlight ballasts, HID lighting, telecom equipment, industrial and medical equipment/control, LAN/WAN interface, analog and digital modems, and automotive.

¹ The terms "Marked" and "Unmarked" pertain to laser marking option of capacitors. All packaging options labeled as "Unmarked" will contain capacitors that have not been laser marked. The option to laser mark is not available on these devices. For more information see "Capacitor Marking".

² The 2 mm pitch option allows for double the packaging quantity of capacitors on a given reel size. This option is limited to EIA 0603 (1608 metric) case size devices. For more information regarding 2 mm pitch option see "Tape & Reel Packaging Information".



Dimensions – Millimeters (Inches)



EIA Size Code	Metric Size Code	L Length	W Width	T Thickness	B Bandwidth	S Separation Minimum	Mounting Technique
0805	2012	2.00 (.079) ±0.20 (.008)	1.25 (.049) ±0.20 (.008)		0.50 (0.02) ±0.25 (.010)	0.75 (.030)	Solder Wave or
1206	3216	3.20 (.126) ±0.20 (.008)	1.60 (.063) ±0.20 (.008)		0.50 (0.02) ±0.25 (.010)		Solder Reflow
1210	3225	3.20 (.126) ±0.20 (.008)	2.50 (.098) ±0.20 (.008)		0.50 (0.02) ±0.25 (.010)		
1808	4520	4.70 (.185) ±0.50 (.020)	2.00 (.079) ±0.20 (.008)	See Table 2 for	0.60 (.024) ±0.35 (.014)		
1812	4532	4.50 (.177) ±0.30 (.012)	3.20 (.126) ±0.30 (.012)	Thickness	0.60 (.024) ±0.35 (.014)	N/A	Solder Deflow Only
1825	4564	4.50 (.177) ±0.30 (.012)	6.40 (.252) ±0.40 (.016)		0.60 (.024) ±0.35 (.014)		Solder Reflow Only
2220	5650	5.70 (.224) ±0.40 (.016)	5.00 (.197) ±0.40 (.016)		0.60 (.024) ±0.35 (.014)		
2225	5664	5.60 (.220) ±0.40 (.016)	6.40 (.248) ±0.40 (.016)		0.60 (.024) ±0.35 (.014)		

Qualification/Certification

Commercial Grade products are subject to internal qualification. Details regarding test methods and conditions are referenced in Table 4, Performance & Reliability.

Environmental Compliance

Lead (Pb)-Free, RoHS, and REACH compliant without exemptions (excluding SnPb termination finish option).



Electrical Parameters/Characteristics

Item	Parameters/Characteristics
Operating Temperature Range	-55°C to +125°C
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	±30 ppm/°C
Aging Rate (Maximum % Capacitance Loss/Decade Hour)	0%
Dielectric Withstanding Voltage (DWV)	150% of rated voltage for voltage rating of < 1,000 V 120% of rated voltage for voltage rating of ≥ 1,000 V (5 ±1 seconds and charge/discharge not exceeding 50 mA)
Dissipation Factor (DF) Maximum Limit at 25°C	0.1%
Insulation Resistance (IR) Limit at 25°C	1,000 megohm microfarads or 100 GΩ (500 VDC applied for 120 ±5 seconds at 25°C)

To obtain IR limit, divide $M\Omega$ - μ F value by the capacitance and compare to $G\Omega$ limit. Select the lower of the two limits. Capacitance and dissipation factor (DF) measured under the following conditions:

Note: When measuring capacitance it is important to ensure the set voltage level is held constant. The HP4284 and Agilent E4980 have a feature known as Automatic Level Control (ALC). The ALC feature should be switched to "ON."

Post Environmental Limits

	High Temperatu	ıre Life, Biased	Humidity, Moist	ture Resistance	
Dielectric	Rated DC Voltage	Capacitance Value	Dissipation Factor (Maximum %)	Capacitance Shift	Insulation Resistance
C0G	All	All	0.5	0.3% or ±0.25 pF	10% of Initial Limit

¹ MHz ± 100 kHz and 1.0 Vrms ± 0.2 V if capacitance $\leq 1,000$ pF

¹ kHz ±50 Hz and 1.0 Vrms ±0.2 V if capacitance > 1,000 pF



Table 1A – Capacitance Range/Selection Waterfall (0805 – 1808 Case Sizes)

		С	ase	e Si	ze/	Se	ries	5	C	0805	iC		С	1206	iC .			С	1210	C				С	1808	C		
	Сар		١	/olta	ge C	ode			С	В	D	С	В	D	F	G	С	В	D	F	G	С	В	D	F	G	z	Н
Capacitance	Code		Rate	d Vo	ltage	e (VC	C)		500	630	1000	500	630	1000	1500	2000	500	630	1000	1500	2000	500	630	1000	1500	2000	2500	3000
				apa			е	\neg					F		uct A					p Th	ickne			S				
1.0 - 9.1 pF*	109 - 919*	В	СГ	<u>Fole</u>	ran	ice			DG	DG	DG			See	Tab	le 21	or C	hip i	nick	ness	Dim	ensi LB	ons LB	LB	LB	LB	LB	LB
10 pF - 47pF*	100 - 470*		١	' _F	G	J	к	м	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
11 pF	110			F		J	K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
12 pF	120			F		J	K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
13 pF	130			F	G	J	K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
15 pF	150			F			K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
16 pF	160			F			K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
18 pF	180			F	1 -		K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
20 pF	200			F			K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
22 pF	220			F		-	K	M	DG DG	DG DG	DG DG	ED ED	ED ED	ED ED	ED ED	ED ED	FM FM	FM FM	FM FM	FM FM	FM FM	LB	LB	LB	LB	LB LB	LB	LB LB
24 pF 27 pF	240 270			F			K	M	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB LB	LB LB	LB	LB LB	LB	LB LB	LB
30 pF	300			F			K	M	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
33 pF	330			l'E			K	M	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
36 pF	360			F			K	M	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
39 pF	390			Ē	_		K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
43 pF	430			F	G	J	K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
47 pF	470			F	G	J	K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
51 pF	510			F	G	J	K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
56 pF	560			F		J	K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
62 pF	620			F			K	M	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
68 pF	680			F			K	М	DG	DG	DG	ED	ED	ED	ED	ED	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
75 pF	750			F			K	М	DG	DG	DG	ED	ED	ED	ED	EF	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LB	LB
82 pF	820 910			F			K	M	DG	DG DG	DG DG	ED ED	ED	ED ED	ED	EF	FM	FM	FM FM	FM	FM	LB	LB	LB LB	LB	LB LB	LB	LB LB
91 pF 100 pF	101			F	_	_	K	M	DG DG	DG	DG	ED	ED ED	ED	ED ED	EF EF	FM FM	FM FM	FM	FM FM	FM FM	LB LB	LB LB	LB	LB LB	LB	LB	LB
110 pF	111			F	1 -		K	М	DG	DG	DG	ED	ED	ED	ED	EG	FM	FM	FM	FM	FM	LB	LB	LB	LB	LB	LC	LB
120 pF	121			l'F			K	М	DG	DG	DG	ED	ED	ED	ED	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LB	LC	LB
130 pF	131			l F	1 -		K	М	DG	DG	DG	ED	ED	ED	ED	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LB	LC	LC
150 pF	151			F			K	М	DG	DG	DG	ED	ED	ED	EF	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LB	LC	LC
160 pF	161			F	G	J	K	М	DG	DG	DG	ED	ED	ED	EF	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LC	LC	LC
180 pF	181			F	G	J	K	М	DG	DG	DG	ED	ED	ED	EF	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LC	LC	LC
200 pF	201			F		J		M	DG	DG	DG	ED	ED	ED	EF	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LC	LC	
220 pF	221			F		J	K	M	DG	DG	DG	ED	ED	ED	EG	EG	FG	FG	FG	FM	FM	LA	LA	LA	LA	LC	LC	
240 pF	241			F	_	J	K	М	DG	DG	DG	ED	ED	ED	EG	EG	FG	FG	FG	FM	FM	LA	LA	LA	LB	LC	LC	
270 pF	271			F	1 -		K	М	DG	DG	DG	ED	ED	ED	EG	EG	FG	FG	FG	FK	FK	LA	LA	LA	LB	LC	LC	
300 pF	301 331			F			K	M	DG	DG DG		ED ED	ED ED	EF EF	EG EG		FG FG	FG FG	FG FG	FK	FK FK	LA	LA	LA	LB	LC	LC	
330 pF 360 pF	331 361			F	1 -		K	M M	DG DG	DG		ED	ED	EF	EG		FG	FG	FG	FK FK	FS	LA LA	LA LA	LA LA	LB LB	LA	LC	
390 pF	391			F			K	M	DG	DG		ED	ED	EF	EG		FG	FG	FG	FK	FS	LA	LA	LA	LB	LA	LC	
430 pF	431			F		-	K	M	DG	DG		ED	ED	EF	EG		FG	FM	FM	FS	FS	LA	LB	LB	LC	LA	20	
470 pF	471			F			K	М	DG	DG		ED	ED	EG	EG		FG	FM	FM	FS	FS	LA	LB	LB	LC	LA		
510 pF	511			F	G		K	М	DG	DG		ED	ED	EG	EG		FG	FM	FM	FS	FS	LA	LB	LB	LC	LB		
560 pF	561			F			K	М	DG	DG		ED	ED	EG	EG		FG	FM	FM	FS	FS	LA	LB	LB	LC	LB		
620 pF	621			F			K	М	DG			ED	ED	EG			FG	FM	FM	FS	FS	LA	LB	LB	LA	LC		
680 pF	681			F			K	М	DG			ED	ED	EG			FG	FM	FM	FS	FS	LB	LB	LB	LA	LC		
750 pF	751			F			K	М	DG			ED	EF	EG			FG	FM	FM	FM		LB	LB	LB	LA			
820 pF	821			F	1 -		K	М	DG			ED	EF	EG			FG	FM	FM	FM		LB	LB	LB	LA			
910 pF	911			F			K	М				ED	EF	EG			FM	FM	FM	FY		LB	LB	LB	LA			
1,000 pF	102 112			F			K	M				ED EF	EF EG	EG			FM FM	FM	FM FK	FY FS		LB	LB	LB	LB LB			
1,100 pF	112						_	IVI	9	2	00			8	8	00	_	FK		_	00	_	-		_	00	00	9
Canacitanes	Сар			d Vo			OC)	_	200	630	1000	200	630	1000	1500	2000	200	630	1000	1200	2000	200	630	1000	1500	2000	2500	3000
Capacitance	Code	<u> </u>		/olta	_			4	С	В	D	С	В	D	F	G	С	В	D	F	G	С	В	D	F	G	Z	Н
		_ (Cas	e Si	ze/	Ser	ies		С	0805	С		С	1206	C			С	1210	C				С	1808	C		

^{*}Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91)
KEMET reserves the right to substitute product with an improved temperature characteristic, tighter capacitance tolerance and/or higher voltage capability within the same form factor (configuration and dimensions).



Table 1A - Capacitance Range/Selection Waterfall (0805 - 1808 Case Sizes) cont'd

		(Cas	se S	Siz	e/S	Sei	ries		C	080	5C		С	1206	C			C	121 0	C				С	1808	C		
	Сар	l		Vol	tage	e Co	de		-	С	В	D	С	В	D	F	G	С	В	D	F	G	С	В	D	F	G	z	н
Capacitance	Code		Ra	ted \	Volt	age	(VD	C)		200	630	1000	200	630	1000	1500	2000	200	630	1000	1500	2000	200	630	1000	1500	2000	2500	3000
			C	Cap To		ita an		•							Prod See				y and hip T						S				
1,200 pF	122				F	G	J	K	М				EF	EG				FM	FK	FK	FS		LC	LC	LC	LC			
1,300 pF	132				F	G	J	K	М				EF	EG				FM	FS	FS			LC	LC	LC	LC			
1,500 pF	152				F	G	J	K	М				EF	EG				FK	FS	FS			LC	LC	LC	LC			
1,600 pF	162				F	G	J	K	М				EF	EG				FK	FS	FS			LC	LC	LC				
1,800 pF	182				F	G	J	K	М				EF	EG				FK	FS	FS			LC	LC	LC				
2,000 pF	202				F	G	J	K	М				EG	EB				FK	FL	FS			LC	LA	LB				
2,200 pF	222				F	G	J	K	М				EG	EB				FK	FL	FS			LC	LA	LB				
2,400 pF	242				F	G	J	K	М				EG	EB				FS	FL	FS			LC	LA	LB				
2,700 pF	272				F	G	J	K	М				EG	EB				FS	FL	FS			LC	LA	LC				
3,000 pF	302				F	G	J	K	М				EB	EB				FS	FL				LA	LA					
3,300 pF	332				F	G	J	K	М				EB	EB				FS	FM				LA	LA					
3,600 pF	362				F	G	J	K	М				EC	EC				FL	FM				LA	LB					
3,900 pF	392				F	G	J	K	М				EC	EC				FL	FY				LA	LB					
4,300 pF	432				F	G	J	K	М				ED	ED				FM	FY				LA	LC					
4,700 pF	472				F	G	J	K	М				ED	ED				FM	FY				LA	LC					
5,100 pF	512				F	G	J	K	М				l					FY	FS				LA						
5,600 pF	562				F	G	J	K	М				l					FY	FS				LB						
6,200pF	622				F	G	J	K	М				l					FY	FE				LC						
6,800pF	682				F	G	J	K	М				l					FY	FE				LC						
7,500pF	752				F	G	J	K	М									FS											
8,200pF	822				F	G	J	K	М									FS											
		Г	Ra	ted \	Volt	age	(VD	C)	7	200	630	1000	200	630	1000	1500	2000	500	630	1000	1500	2000	200	630	1000	1500	2000	2500	3000
Capacitance	Cap Code	Г		Vol	tage	e Co	de		┪	С	В	D	С	В	D	F	G	С	В	D	F	G	С	В	D	F	G	z	Н
			Ca	se (Siz	e/S	Ser	ies		С	0805	С		C	1206	С			С	1210	С				С	1808	С		

^{*}Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91)

KEMET reserves the right to substitute product with an improved temperature characteristic, tighter capacitance tolerance and/or higher voltage capability within the same form factor (configuration and dimensions).



Table 1B - Capacitance Range/Selection Waterfall (1812 - 2225 Case Sizes)

			Ca				1			C.	181	2C					C1	182	5C					C2	222	0C					C2	222	5C		
	Can	L	8	er Ser	ies	5				Ŭ	101/							102						02		-					02				
Capacitance	Cap Code	┡	Vol	tage	Co	ode		С	В	D	F	G	Z	Н	С	В	D	F	G	Z	Н	С	В	D	F	G	Z	Н	С	В	D	F	G	Z	н
	Code	R	ated	Volt	age	(VD	C)	200	630	1000	1500	2000	2500	3000	200	630	1000	1500	2000	2500	3000	200	630	1000	1500	2000	2500	3000	200	630	1000	1500	2000	2500	3000
		Г		pac				П											labi	-															
10 pF - 47pF*	100 - 470*	F	G	oler:		e K	M	GK	GK	GK	GK	GK	GK	GK	HG			HG	HG	HG		JK	JK	JK	JK	JK	JK	S JK	KF	KF	KF	KF	KF	KF	KF
11 pF	110	F	G	J		K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
12 pF	120	F	G	J		K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
13 pF	130	F	G	J		K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
15 pF	150	F	G	J	_	K	M	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
16 pF	160	F	G	l i	- 1	K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
18 pF	180	F	G	J	- 1	K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
20 pF	200 220	F F	G	J	- 1	K K	M M	GK GK	GK GK	GK GK	GK GK	GK GK	GK GK	GK GK	HG HG	HG HG	HG HG	HG HG	HG HG	HG HG	HG HG	JK JK	JK JK	JK JK	JK JK	JK JK	JK JK	JK JK	KF KF	KF KF	KF KF	KF KF	KF KF	KF KF	KF KF
22 pF 24 pF	240	F	G	J	- 1	ĸ	M	GK	GK	GK	GK	GK	GK	GK		HG		HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
27 pF	270	F	G	J	_	K	M	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
30 pF	300	F	G	J		ĸ	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
33 pF	330	F	G	J		K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
36 pF	360	F	G	J		к	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
39 pF	390	F	G	J		K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
43 pF	430	F	G	J		K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
47 pF	470	F	G	J	- 1	K	M	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
51 pF	510	F	G	J	- 1	K	M	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
56 pF	560	F	G	J	- 1	K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
62 pF	620	F	G	J	_	K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	_	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
68 pF	680	F	G	J		K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
75 pF	750 820	F	G	J		K K	M	GK GK	GK GK	GK GK	GK GK	GK GK	GK GK	GK GK	HG HG	HG HG	HG HG	HG HG	HG	HG HG	HG HG	JK JK	JK JK	JK JK	JK JK	JK JK	JK JK	JK JK	KF KF	KF KF	KF KF	KF KF	KF KF	KF KF	KF KF
82 pF 91 pF	910	F	G	J		K	M	GK	GK	GK	GK	GK	GK	GK		HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
100 pF	101	F	G	J		ĸ	M	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
110 pF	111	F	G	J	_	K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
120 pF	121	F	G	J	- 1	ĸ	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
130 pF	131	F	G	J		к	M	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
150 pF	151	F	G	J		K	M	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
160 pF	161	F	G	J	_	K	М	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
180 pF	181	F	G	J		K	M	GK	GK	GK	GK	GK	GK	GK	HG	HG	HG	HG	HG	HG	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
200 pF	201	F	G	J		K	M	GH	GH	GH	GH	GH	GK	GM	HE	HE	HE	HE	HE	HE	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
220 pF	221	F	G	J		K	М	GH	GH	GH	GH	GH	GK	GM	HE	HE	HE	HE	HE	HE	HG	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KF	KF	KF
240 pF	241	F	G	J		K	M	GH	GH	GH	GH	GH	GK	GM	HE	HE	HE	HE	HE	HE	HG	JK	JK	JK	JK	JK	JK	JK	KE	KE	KE	KE	KE	KE	KF
270 pF 300 pF	271 301	F	G	J	_	K K	M	GH GH	GH	GH	GH	GH	GK GK	GM	HE	HE	HE	HE	HE	HE	HG	JK JK	JK JK	JK JK	JK JK	JK JK	JK JK	JK JK	KE KE	KE	KE	KE	KE	KE	KF KF
330 pF	331	' F	G	J	- 1	ĸ	M	GH	GH	GH	GH	GH	GK	GO	HE	HE	HE	HE	HE	HE	HG	JE	JE	JE	JE	JE	JK	JK	KE	KE	KE	KE	KE	KE	KF
360 pF	361	F	G	J	- 1	ĸ	M	GK	GK	GK	GK	GH	GK	GO		HE	HE	HE	HE	HE	HG	JE	JE	JE	JE	JE	JK	JK	KE	KE	KE	KE	KE	KE	KF
390 pF	391	F	G	J	- 1	ĸ	М	GK	GK	GK	GK	GK	GK	GO	HE	HE	HE	HE	HE	HE	HG	JE	JE	JE	JE	JE	JK	JK	KE	KE	KE	KE	KE	KE	KF
430 pF	431	F	G	J	- 1	K	M	GK	GK	GK	GK	GK			HE	HE	HE	HE	HE	HE		JE	JE	JE	JE	JE	JK	JE	KE	KE	KE	KE	KE	KE	KF
470 pF	471	F	G	J		K	M	GK	GK	GK	GK	GK	GK		HE	HE	HE	HE	HE	HE	HJ	JE	JE	JE	JE	JE	JK	JK	KF	KF	KF	KF	KE	KE	KF
510 pF	511	F	G	J		K	M	GH	GH	GH	GK	GH	GM		HE	HE	HE	HE	HE	HE	HJ	JK	JK	JK	JK	JK	JK	JK	KF	KF	KF	KF	KE	KE	KF
560 pF	561	F	G	J		K	M					GH			HE	HE		HE		HE		JK	JK	JK	JK	JK	JK	JL	KF	KF	KF	KF	KE	KE	KF
620 pF	621	F	G	J		K	М					GH				HE				HE		JK	JK	JK	JK	JK	JK	JL	KF	KF	KF	KF	KE	KF	KH
680 pF	681	F	G	J		K	M	_	_	_	_	GH	GO		HE	HE	_	HE		HG	HK	JE	JE	JE	JK	JK	JK	JL	KF	KF	KF	KF	KE	KF	KH
750 pF	751	F	G	J	- 1	K	M				GK				HE	HE		HG		HG		JE	JE	JE	JK	JK	JK	JL	KE	KE	KE KE	KF	KE	KF	KH
820 pF	821	F F	G	J		K	M					GK										JE	JE	JE	JK	JK	JK	JN	KE	KE		KF	KE	KF	KJ
910 pF	911		ated	J Volt		K	M (C)	200	089	1000	1500	GM 2000	_	3000	200	089	1000	1500	HG 2000	2500		JE 200	930	1000 JK	1500 TK	JK	2500 K	3000	200	KE 069	1000	1500	2000	Z500	3000
0	Сар	Ľ			_	_	,	C EU	_	D 5	£ €	9 G	Z Z	н	C	В	D D	£ €	9 G	z z	В	C ED	B	D D	E E	9 G	2 Z	н	C	B	D D	F E	9 0	25 Z	ж н
Capacitance	Code	Ļ		tage				۳	-					n	۴	-						۴	-					<u> </u>	۳						п
		C	ase	SIZ	e/\$	seri	ies			C	1812	2C					C,	182) C					C	2220	UC					C	222) C		

^{*}Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91)
KEMET reserves the right to substitute product with an improved temperature characteristic, tighter capacitance tolerance and/or higher voltage capability within the same form factor (configuration and dimensions).



Table 1B - Capacitance Range/Selection Waterfall (1812 - 2225 Case Sizes) cont'd

			Cas	se S eri		e/				C'	1812	2C					C,	182	5C					CZ	222	0C					CZ	222	5C		
Capacitance	Cap	ı	Vol	tage	Code	e	1	С	В	D	F	G	z	н	С	В	D	F	G	z	н	С	В	D	F	G	z	н	С	В	D	F	G	z	н
Capacitance	Code	R	ated \	/olta	ge (\	/DC)	1	200	630	1000	1500	2000	2500	3000	200	630	1000	1500	2000	2500	3000	200	630	1000	1200	2000	2500	3000	200	630	1000	1500	2000	2500	3000
		Г		pacit		:	Ť											∖vai	labi	lity	and	CI			kne	ess	Cod	les							
4.000 5	400	_	_	lera	_	Τ.	۱,	I	011	011	011	014			_	_	_	_	_	_	iip i	hic	_	_	_	_	_	_	1/5	145	1/5	145	145	ИЕ	161
1,000 pF	102	F	G	J	K			- 1	- 1		GH				HE	HE		HG		HG		JE	JK	JK	JK	JK	JK	JN	KE	KE	KE	KF	KE	KF	KJ
1,100 pF	112	F	G	J	K	N			GK	GK	GH	GO			HE	HE	HE	HG	HG	HJ		JE	JK	JK	JK	JK	JK		KE	KE	KE	KF	KF	KF	
1,200 pF	122	F	G	J	K	I N				GK		GO			HE	HE	HE	HG		HJ		JE	JK	JK	JK	JK	JL		KE	KE	KE	KF	KF	KF	
1,300 pF	132	F	G	J	K	N.				GK	GH	GO			HE	HE	HE	HG	HE	HJ		JE	JK	JK	JK	JE	JL		KE	KE	KE	KF	KF	KH	
1,500 pF	152	F	G	J	K	N.				GK	GK	GO			HE	HE	HE	HG		HK		JE	JK	JK	JK	JE	JL		KE	KE	KE	KF	KF	KH	
1,600 pF	162	F	G	J	K	N.				GK	GK				HE	HG		HG	HG	HK		JE	JK	JK	JK	JE	JL		KE	KE	KE	KF	KE	KH	
1,800 pF	182	F	G	J	K	N			_		GM				HE	HG	HG	HG	HG			JE	JK	JK	JK	JE	JN		KE	KE	KE	KF	KE	KH	
2,000 pF	202	F	G	J	K	N					GM				HE	HG		HE	HJ			JE	JK	JK	JE	JK			KE	KE	KE	KF	KE	KJ	
2,200 pF	222	F	G	J	K	N					GO				HE	HG	HG	HE	HJ			JE	JK	JK	JE	JK			KE	KE	KE	KF	KF	KJ	
2,400 pF	242	F	G	J	K	N					GO				HE			HE	HJ			JK	JK	JK	JE	JL			KE	KE	KE	KE	KH		
2,700 pF	272	F	G	J	K	N					GO				HE	HG	HG	HE	HK			JK	JK	JK	JE	JL			KE	KE	KE	KE	KH		
3,000 pF	302	F	G	J	K	N	_		GH						HG		HG	HE	HK			JK	JK	JK	JE	JL			KE	KE	KE	KE	KH	ш	
3,300 pF	332	F	G	J	K	N	l G		GH						HG			HG				JK	JK	JK	JK	JN			KE	KE	KE	KE	KJ		
3,600 pF	362	F	G	J	K	N	l G		GH						HG	HG		HG				JK	JK	JK	JK	JN			KE	KF	KF	KF	KJ		
3,900 pF	392	F	G	J	K	N	l G	K	GH	GM					HG	HG	HG	HJ				JK	JK	JK	JK	JN			KE	KF	KF	KF	KJ		
4,300 pF	432	F	G	J	K	N.	1 6	H	GH	GO					HG	HG	HG	HJ				JK	JK	JK	JK				KE	KF	KF	KF			
4,700 pF	472	F	G	J	K	N	1 6	H	GH	GO					HG	HG	HG	HJ				JK	JK	JK	JL				KE	KF	KF	KH			
5,100 pF	512	F	G	J	K	N	0	H	GK	GO					HG	HE	HG	HK				JK	JK	JK	JL				KE	KF	KF	KH			
5,600 pF	562	F	G	J	K	N	G	H	GK	GO					HG	HE	HG	HK				JK	JK	JK	JN				KE	KF	KF	KH			
6,200pF	622	F	G	J	K	N	G	H	GK						HG	HE	HG					JK	JE	JE	JN				KE	KF	KF	KJ			
6,800pF	682	F	G	J	K	N	G	нΙ	GM						HG	HE	HJ					JK	JE	JK	JN				KE	KF	KF	KJ			
7,500pF	752	F	G	J	K	N	G	нΙ	GM						HG	HE	HJ					JK	JE	JK					KF	KE	KF				
8,200pF	822	F	G	J	K	N	0	K	GO						HG	HE	HJ					JK	JE	JL					KF	KE	KF				
		R	ated \	/olta	ge (\	/DC)	T	200	630	1000	1500	2000	2500	3000	200	630	1000	1500	2000	2500	3000	200	630	1000	1500	2000	2500	3000	200	630	1000	1500	2000	2500	3000
Capacitance	Cap		Vol	tage	Code	e	1	С	В	D	F	G	Z	Н	С	В	D	F	G	z	Н	С	В	D	F	G	Z	Н	С	В	D	F	G	Z	Н
	Code	Ca	se (Size	/Se	rie	s			C	1812	2C					С	182	5C					Cź	222	0C					C	222	5C		

^{*}Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91)
KEMET reserves the right to substitute product with an improved temperature characteristic, tighter capacitance tolerance and/or higher voltage capability within the same form factor (configuration and dimensions).



Table 1C - Capacitance Range/Selection Waterfall (2824 - 4540 Case Sizes)

		റം	se Siz	I																				
			se Siz Series			C	2824	С			C	3040	C			C	3640	C			C	4540	C	
Capacitance	Сар	Vo	Itage Co	de	С	В	D	F	G	С	В	D	F	G	С	В	D	F	G	С	В	D	F	G
- Capacitanio	Code	Vo	Rated Itage (VD	IC)	200	630	1000	1500	2000	200	630	1000	1500	2000	200	630	1000	1500	2000	200	630	1000	1500	2000
			apacitano Folerance						ı				bility for C							3				
10 - 2,000 pF	100 - 202	J	К	M							Tub			p		1000		-	<u> </u>					
2,200 pF	222	J	K	M	TA	TA	TA	TA	TA															
2,400 pF	242	J	K	M																				
2,700 pF	272	J	K	M	TA	TA	TA	TA	TA															
3,000 pF	302	J	K	M																				
3,300 pF	332	J	K	M	TA	TA	TA	TA	TA	QB	QB	QB	QB	QB										
3,600 pF	362	J	K	М	l	_	_								l l		l	l	l					
3,900 pF	392	J	K	М	TA	TA	TA	TA	TB	QB	QB	QB	QB	QB	MA	MA	MA	MA	MA					
4,300 pF	432	J	K	М	l										ا ا			١	١	١	١ ا	٠.		١.,
4,700 pF	472	J	K	M	TA	TA	TA	TB	TB	QB	QB	QB	QB	QB	MA	MA	MA	MA	MA	SA	SA	SA	SA	SA
5,100 pF	512	J	K	M	Τ.	т.	та	TD	то.	OD.	OD.	O.D.	OD.	O.D.									0.4	0.4
5,600 pF	562	J	K	M	TA	TA	TA	TB	TC	QB	QB	QB	QB	QB	MA	MA	MA	MA	MA	SA	SA	SA	SA	SA
6,200 pF	622 682	J J	K K	M M	TA	TA	TA	ТВ		QB	QB	O.D.	QB	QC	MA	MA	MA	MA	MA	SA	SA	SA	SA	SA
6,800 pF 7,500 pF	752	J	K	M	IA	IA	IA	IB		ИВ	ЦB	QB	QB	QU	MA	MA	MA	MA	MA	δA	5A	SA	SA	SA
8,200 pF	822	J	K	M	TA	TA	TA	TC		QB	QB	QB	QC	QC	MA	MA	MA	MA	MB	SA	SA	SA	SA	SA
9,100 pF	912	J	K	M	IA.	IA	IA	10		ЦD	ЦD	QD	QU	QU	IVIA	IVIA	IWIA	IWIA	INID	OA	OA	OA	OA	OA.
10,000 pF	103	J	K	M	TA	TA	TA			QB	QB	QB	QC	QD	ма	MA	MA	MA	МВ	SA	SA	SA	SA	SB
12,000 pF	123	Ĵ	ĸ	M	TA	TA	TA			QB	QB	QB	QD	G(D	MA	MA	MA	MB	MB	SA	SA	SA	SA	SB
15,000 pF	153	J	ĸ	M	TA	TA	TB			QB	QB	QB	QD		MA	MA	MA	MB	MC	SA	SA	SA	SB	SB
18,000 pF	183	J	K	M	TA	TA	TB			QB	QB	QB	Q,D		MA	MA	MA	MC	1010	SA	SA	SA	SB	SC
22,000 pF	223	J	K	M	TA	TB	TC			QB	QB	QC			MA	MA	MA			SA	SA	SA	SB	
27,000 pF	273	J	K	M	TA	TB				QB	QB	QC			MA	MA	MA			SA	SA	SA	SC	
33,000 pF	333	J	K	M	ТВ	TB				QB	QC	QC			MA	MA	MB			SA	SA	SA		
39,000 pF	393	J	K	M	ТВ	TC				QB	QC	QD			MA	MA	MB			SA	SA	SB		
47,000 pF	473	J	K	M	ТВ					QB	QC				MA	MB	MC			SA	SA	SB		
56,000 pF	563	J	К	M	TC					QC	QD				MA	MB				SA	SA	SB		
68,000 pF	683	J	к	M						QC	QD				МВ	MC				SA	SB	SC		
82,000 pF	823	J	K	M						QC					MB					SA	SB			
0.1 µF	104	J	К	M						QD					MC					SB	SC			
0.12 µF	124	J	K	M											MC					SB				
0.15 µF	154	J	K	М																SC				
		Rated	Voltage	(VDC)	200	630	1000	1500	2000	200	630	1000	1500	2000	200	630	1000	1500	2000	200	630	1000	1500	2000
Capacitance	Сар	Vo	Itage Co	de	С	В	D	F	G	С	В	D	F	G	С	В	D	F	G	С	В	D	F	G
	Code	Case	Size/S	eries		С	2824	С			С	3040	С			С	3640	C			С	4540	С	

^{*}Capacitance range Includes E24 decade values only. (i.e., 10, 11, 12, 13, 15, 16, 18, 20, 22, 24, 27, 30, 33, 36, 39, 43, 47, 51, 56, 62, 68, 75, 82 and 91)

KEMET reserves the right to substitute product with an improved temperature characteristic, tighter capacitance tolerance and/or higher voltage capability within the same form factor (configuration and dimensions).



Table 2A – Chip Thickness/Tape & Reel Packaging Quantities

Thickness	Case	Thickness ±	Paper C	Quantity	Plastic (Quantity
Code	Size	Range (mm)	7" Reel	13" Reel	7" Reel	13" Reel
DG	0805	1.25 ± 0.15	0	0	2,500	10,000
EB	1206	0.78 ± 0.10	4000	10000	4,000	10,000
EC ED	1206	0.90 ± 0.10	0	0	4,000	10,000
EF	1206 1206	1.00 ± 0.10 1.20 ± 0.15	0	0	2,500 2,500	10,000 10,000
EG	1206	1.60 ± 0.15	0	0	2,000	8,000
FE	1210	1.00 ± 0.10	0	Ö	2,500	10,000
FG	1210	1.25 ± 0.15	0	0	2,500	10,000
FL	1210	1.40 ± 0.15	0	0	2,000	8,000
FM	1210	1.70 ± 0.20	0	0	2,000	8,000
FY	1210	2.00 ± 0.20	0	0	2,000	8,000
FK FS	1210 1210	2.10 ± 0.20	0	0	2,000 1,000	8,000
LA	1808	2.50 ± 0.30 1.40 ± 0.15	0	0	1,000	4,000 4,000
LB	1808	1.60 ± 0.15	0	0	1,000	4,000
LC	1808	2.00 ± 0.15	0	0	1,000	4,000
GH	1812	1.40 ± 0.15	0	0	1,000	4,000
GK	1812	1.60 ± 0.20	0	0	1,000	4,000
GM	1812	2.00 ± 0.20	0	0	500	2,000
GO	1812	2.50 ± 0.20	0	0	500	2,000
HE	1825	1.40 ± 0.15	0	0	1,000	4,000
HG HJ	1825 1825	1.60 ± 0.20 2.00 ± 0.20	0	0	1,000 500	4,000 2,000
HK	1825	2.50 ± 0.20 2.50 ± 0.20	0	0	500	2,000
JE	2220	1.40 ± 0.15	0	ő	1,000	4,000
JK	2220	1.60 ± 0.20	0	0	1,000	4,000
JL	2220	2.00 ± 0.20	0	0	500	2,000
JN	2220	2.50 ± 0.20	0	0	500	2,000
KE	2225	1.40 ± 0.15	0	0	1,000	4,000
KF	2225	1.60 ± 0.20	0	0	1,000	4,000
KH KJ	2225 2225	2.00 ± 0.20 2.50 ± 0.20	0 0	0	500 500	2,000 2,000
TA	2824	1.40 ± 0.15	0	0	750	2,500
TB	2824	2.00 ± 0.20	0	0	300	2,000
TC	2824	2.50 ± 0.20	0	0	300	2,000
QB	3040	1.40 ± 0.15	0	0	300	1,000
QC	3040	2.00 ± 0.20	0	0	300	1,000
QD	3040	2.50 ± 0.20	0	0	350	1,400
MA MB	3640 3640	1.40 ± 0.15 2.00 ± 0.20	0 0	0 0	250 250	1,000 1,000
MC	3640	2.50 ± 0.20 2.50 ± 0.20	0	0	250	1,000
SA	4540	1.40 ± 0.15	0	0	250	1,500
SB	4540	2.00 ± 0.20	0	0	250	1,500
SC	4540	2.50 ± 0.20	0	0	250	1,500
Thickness	Case	Thickness ±	7" Reel	13" Reel	7" Reel	13" Reel
Code	Size	Range (mm)	Paper C	Quantity	Plastic (Quantity

Package quantity based on finished chip thickness specifications.



Table 2B - Bulk Packaging Quantities

D 1		Loose P	ackaging
Раска	jing Type	Bulk Bag	(default)
Packagi	ng C-Spec¹	N/	/A²
Cas	e Size	Packaging Quantities	(pieces/unit packaging)
EIA (in)	Metric (mm)	Minimum	Maximum
0402	1005		
0603	1608		
0805	2012		50,000
1206	3216		
1210	3225	1	
1808	4520] '	
1812	4532		
1825	4564		20,000
2220	5650		
2225	5664		

¹ The "Packaging C-Spec" is a 4 to 8 digit code which identifies the packaging type and/or product grade. When ordering, the proper code must be included in the 15th through 22nd character positions of the ordering code. See "Ordering Information" section of this document for further details. Commercial Grade product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging. Contact KEMET if you require a bulk bag packaging option for Automotive Grade products.

² A packaging C-Spec (see note 1 above) is not required for "Bulk Bag" packaging (excluding Anti-Static Bulk Bag and Automotive Grade products). The 15th through 22nd character positions of the ordering code should be left blank. All product ordered without a packaging C-Spec will default to out standard "Bulk Bag" packaging.




Table 3 - Chip Capacitor Land Pattern Design Recommendations per IPC-7351

EIA Size Code	Metric Size Code	Density Level A: Maximum (Most) Land Protrusion (mm)			Density Level B: Median (Nominal) Land Protrusion (mm)				Density Level C: Minimum (Least) Land Protrusion (mm)							
Code		С	Υ	X	V1	V2	С	Υ	X	V1	V2	С	Y	X	V1	V2
0805	2012	1.00	1.35	1.55	4.40	2.60	0.90	1.15	1.45	3.50	2.00	0.75	0.95	1.35	2.80	1.70
1206	3216	1.60	1.35	1.90	5.60	2.90	1.50	1.15	1.80	4.70	2.30	1.40	0.95	1.70	4.00	2.00
1210	3225	1.60	1.35	2.80	5.65	3.80	1.50	1.15	2.70	4.70	3.20	1.40	0.95	2.60	4.00	2.90
1808	4520	2.30	1.75	2.30	7.40	3.30	2.20	1.55	2.20	6.50	2.70	2.10	1.35	2.10	5.80	2.40
1812	4532	2.15	1.60	3.60	6.90	4.60	2.05	1.40	3.50	6.00	4.00	1.95	1.20	3.40	5.30	3.70
1825	4564	2.15	1.60	6.90	6.90	7.90	2.05	1.40	6.80	6.00	7.30	1.95	1.20	6.70	5.30	7.00
2220	5650	2.75	1.70	5.50	8.20	6.50	2.65	1.50	5.40	7.30	5.90	2.55	1.30	5.30	6.60	5.60
2225	5664	2.70	1.70	6.90	8.10	7.90	2.60	1.50	6.80	7.20	7.30	2.50	1.30	6.70	6.50	7.00

Density Level A: For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes. KEMET only recommends wave soldering of EIA 0603, 0805 and 1206 case sizes.

Density Level B: For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes. **Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC Standard 7351 (IPC–7351).

Image below based on Density Level B for an EIA 1210 case size.





Soldering Process

Recommended Soldering Technique:

- Solder wave or solder reflow for EIA case sizes 0603, 0805 and 1206
- · All other EIA case sizes are limited to solder reflow only

Recommended Reflow Soldering Profile:

KEMET's families of surface mount multilayer ceramic capacitors (SMD MLCCs) are compatible with wave (single or dual), convection, IR or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/J-STD-020 standard for moisture sensitivity testing. These devices can safely withstand a maximum of three reflow passes at these conditions.

Profile Feature	Termination Finish				
Frome readure	SnPb	100% Matte Sn			
Preheat/Soak					
Temperature Minimum (T _{smin})	100°C	150°C			
Temperature Maximum (T _{Smax})	150°C	200°C			
Time (t_s) from $T_{s_{min}}$ to $T_{s_{max}}$	60 – 120 seconds	60 – 120 seconds			
Ramp-Up Rate (T _L to T _P)	3°C/second maximum	3°C/second maximum			
Liquidous Temperature (T _L)	183°C	217°C			
Time Above Liquidous (t _L)	60 – 150 seconds	60 – 150 seconds			
Peak Temperature (T _P)	235°C	260°C			
Time Within 5°C of Maximum Peak Temperature (t _P)	20 seconds maximum	30 seconds maximum			
Ramp-Down Rate (T _P to T _L)	6°C/second maximum	6°C/second maximum			
Time 25°C to Peak Temperature	6 minutes maximum	8 minutes maximum			

Note 1: All temperatures refer to the center of the package, measured on the capacitor body surface that is facing up during assembly reflow.






Table 4 - Performance & Reliability: Test Methods and Conditions


Stress	Reference	Test or Inspection Method
Terminal Strength	JIS-C-6429	Appendix 1, Note: Force of 1.8 kg for 60 seconds.
Board Flex	JIS-C-6429	Appendix 2, Note: Standard termination system – 2.0 mm (minimum) for all except 3 mm for COG. Flexible termination system – 3.0 mm (minimum).
		Magnification 50 X. Conditions:
Solderability	J-STD-002	a) Method B, 4 hours at 155°C, dry heat at 235°C
Solderability	J-31D-002	b) Method B at 215°C category 3
		c) Method D, category 3 at 260°C
Temperature Cycling	JESD22 Method JA-104	1,000 cycles (-55°C to +125°C). Measurement at 24 hours +/- 4 hours after test conclusion.
Biased Humidity	MIL-STD-202 Method 103	Load Humidity: 1,000 hours 85°C/85% RH and 200 VDC maximum. Add 100 K ohm resistor. Measurement at 24 hours +/- 4 hours after test conclusion.
Biased Humidity	MIL-STD-202 Method 103	Low Volt Humidity: 1,000 hours 85°C/85% RH and 1.5 V. Add 100 K ohm resistor. Measurement at 24 hours +/- 4 hours after test conclusion.
Moisture Resistance	MIL-STD-202 Method 106	t = 24 hours/cycle. Steps 7a and 7b not required. Measurement at 24 hours +/- 4 hours after test conclusion.
Thermal Shock	MIL-STD-202 Method 107	-55°C/+125°C. Note: Number of cycles required – 300. Maximum transfer time – 20 seconds. Dwell time – 15 minutes. Air – Air.
High Temperature Life	MIL-STD-202 Method 108	1,000 hours at 125°C (85°C for X5R, Z5U and Y5V) with 1.2 X rated voltage applied.
Storage Life	MIL-STD-202 Method 108	150°C, 0 VDC for 1,000 hours.
Vibration	MIL-STD-202 Method 204	5 g's for 20 min., 12 cycles each of 3 orientations. Note: Use 8" X 5" PCB 0.031" thick 7 secure points on one long side and 2 secure points at corners of opposite sides. Parts mounted within 2" from any secure point. Test from 10 – 2,000 Hz
Mechanical Shock	MIL-STD-202 Method 213	Figure 1 of Method 213, Condition F.
Resistance to Solvents	MIL-STD-202 Method 215	Add aqueous wash chemical, OKEM Clean or equivalent.

Storage and Handling

Ceramic chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature- reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 70% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulfur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within 1.5 years of receipt.



Construction



Capacitor Marking (Optional):

Laser marking option is not available on:

- · C0G, Ultra Stable X8R and Y5V dielectric devices
- · EIA 0402 case size devices
- EIA 0603 case size devices with Flexible Termination option.
- KPS Commercial and Automotive grade stacked devices.

These capacitors are supplied unmarked only.



Tape & Reel Packaging Information

KEMET offers multilayer ceramic chip capacitors packaged in 8, 12 and 16 mm tape on 7" and 13" reels in accordance with EIA Standard 481. This packaging system is compatible with all tape-fed automatic pick and place systems. See Table 2 for details on reeling quantities for commercial chips.




Table 5 - Carrier Tape Configuration, Embossed Plastic & Punched Paper (mm)

	Tape	Embosse	ed Plastic	Punched Paper		
EIA Case Size	Size	7" Reel	13" Reel	7" Reel	13" Reel	
	(W)*	Pitch	(P,)*	Pitch (P ₄)*		
01005 - 0402	.8			2	2	
0603	.8			2/4	2/4	
0805	.8	4	4	4	4	
1206 – 1210	8	4	4	4	4	
1805 – 1808	12	4	4			
≥ 1812	12	8	8			
KPS 1210	12	8	8			
KPS 1812 & 2220	16	12	12			
Array 0508 & 0612	8	4	4			

^{*}Refer to Figures 1 & 2 for W and P, carrier tape reference locations.

New 2 mm Pitch Reel Options*

Packaging Ordering Code (C-Spec)	Packaging Type/Options
C-3190	Automotive grade 7" reel unmarked
C-3191	Automotive grade 13" reel unmarked
C-7081	Commercial grade 7" reel unmarked
C-7082	Commercial grade 13" reel unmarked

^{* 2} mm pitch reel only available for 0603 EIA case size.
2 mm pitch reel for 0805 EIA case size under development.

Benefits of Changing from 4 mm to 2 mm Pitching Spacing

- · Lower placement costs
- Double the parts on each reel results in fewer reel changes and increased efficiency
- Fewer reels result in lower packaging, shipping and storage costs, reducing waste

^{*}Refer to Tables 6 & 7 for tolerance specifications.



Figure 1 – Embossed (Plastic) Carrier Tape Dimensions




Table 6 – Embossed (Plastic) Carrier Tape Dimensions

Metric will govern

	Constant Dimensions — Millimeters (Inches)									
Tape Size	D _o	D ₁ Minimum Note 1	E,	P _o	P ₂	R Reference Note 2	S ₁ Minimum Note 3	T Maximum	T ₁ Maximum	
8 mm		1.0 (0.039)				25.0 (0.984)				
12 mm	1.5 +0.10/-0.0 (0.059 +0.004/-0.0)	1.5	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	30	0.600 (0.024)	0.600 (0.024)	0.100 (0.004)	
16 mm		(0.059)				(1.181)				
	Variable Dimensions — Millimeters (Inches)									
Tape Size	Tape Size Pitch B ₁ Maximum E ₂ F P ₁ T ₂ W Maximum A ₀ ,B ₀ & K ₀								& K ₀	
8 mm	Single (4 mm)	4.35 (0.171)	6.25 (0.246)	3.5 ±0.05 (0.138 ±0.002)	4.0 ±0.10 (0.157 ±0.004)	2.5 (0.098)	8.3 (0.327)			
12 mm	Single (4 mm) & Double (8 mm)	8.2 (0.323)	10.25 (0.404)	5.5 ±0.05 (0.217 ±0.002)	8.0 ±0.10 (0.315 ±0.004)	4.6 (0.181)	12.3 (0.484)	Note 5		
16 mm	Triple (12 mm)	12.1 (0.476)	14.25 (0.561)	7.5 ±0.05 (0.138 ±0.002)	12.0 ±0.10 (0.157 ±0.004)	4.6 (0.181)	16.3 (0.642)			

- 1. The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location and hole location shall be applied independent of each other.
- 2. The tape with or without components shall pass around R without damage (see Figure 6).
- 3. If $S_1 < 1.0$ mm, there may not be enough area for cover tape to be properly applied (see EIA Standard 481 paragraph 4.3 section b).
- 4. B, dimension is a reference dimension for tape feeder clearance only.
- 5. The cavity defined by A, B, and K, shall surround the component with sufficient clearance that:
 - (a) the component does not protrude above the top surface of the carrier tape.
 - (b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
 - (c) rotation of the component is limited to 20° maximum for 8 and 12 mm tapes and 10° maximum for 16 mm tapes (see Figure 3).
 - (d) lateral movement of the component is restricted to 0.5 mm maximum for 8 and 12 mm wide tape and to 1.0 mm maximum for 16 mm tape (see Figure 4).
 - (e) for KPS Series product, A, and B, are measured on a plane 0.3 mm above the bottom of the pocket.
 - (f) see Addendum in EIA Standard 481 for standards relating to more precise taping requirements.



Figure 2 - Punched (Paper) Carrier Tape Dimensions




Table 7 - Punched (Paper) Carrier Tape Dimensions

Metric will govern

	Constant Dimensions — Millimeters (Inches)									
Tape Size	D _o	E,	P _o	P ₂	T, Maximum	G Minimum	R Reference Note 2			
8 mm	1.5 +0.10 -0.0 (0.059 +0.004 -0.0)	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	0.10 (0.004) Maximum	0.75 (0.030)	25 (0.984)			
	Variable Dimensions — Millimeters (Inches)									
Tape Size	Pitch	E2 Minimum	F	P ₁	T Maximum	W Maximum	$A_{_{0}}B_{_{0}}$			
8 mm	Half (2 mm)	6.25	3.5 ±0.05	2.0 ±0.05 (0.079 ±0.002)	1.1	8.3 (0.327)	Note 1			
8 mm	Single (4 mm)	(0.246)	(0.138 ±0.002)	4.0 ±0.10 (0.157 ±0.004)	(0.098)	8.3 (0.327)	Note 1			

- 1. The cavity defined by A_o, B_o and T shall surround the component with sufficient clearance that:
 - a) the component does not protrude beyond either surface of the carrier tape.
 - b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
 - c) rotation of the component is limited to 20° maximum (see Figure 3).
 - d) lateral movement of the component is restricted to 0.5 mm maximum (see Figure 4).
 - e) see Addendum in EIA Standard 481 for standards relating to more precise taping requirements.
- 2. The tape with or without components shall pass around R without damage (see Figure 6).



Packaging Information Performance Notes


- 1. Cover Tape Break Force: 1.0 Kg minimum.
- 2. Cover Tape Peel Strength: The total peel strength of the cover tape from the carrier tape shall be:

Tape Width	Peel Strength
8 mm	0.1 to 1.0 Newton (10 to 100 gf)
12 and 16 mm	0.1 to 1.3 Newton (10 to 130 gf)

The direction of the pull shall be opposite the direction of the carrier tape travel. The pull angle of the carrier tape shall be 165° to 180° from the plane of the carrier tape. During peeling, the carrier and/or cover tape shall be pulled at a velocity of 300 ±10 mm/minute.

 Labeling: Bar code labeling (standard or custom) shall be on the side of the reel opposite the sprocket holes. Refer to EIA Standards 556 and 624.

Figure 3 - Maximum Component Rotation






Figure 4 - Maximum Lateral Movement




Figure 5 - Bending Radius







Figure 6 - Reel Dimensions



Note: Drive spokes optional; if used, dimensions B and D shall apply.

Table 8 - Reel Dimensions

Metric will govern

	Constant Dimensions — Millimeters (Inches)									
Tape Size	A	B Minimum	С	D Minimum						
8 mm	178 ±0.20									
12 mm	(7.008 ±0.008) or	1.5 (0.059)	13.0 +0.5/-0.2 (0.521 +0.02/-0.008)	20.2 (0.795)						
16 mm	330 ±0.20 (13.000 ±0.008)	, ,	,	, ,						
	Variable Dimensions — Millimeters (Inches)									
Tape Size	N Minimum	W ₁	W ₂ Maximum	W_3						
8 mm		8.4 +1.5/-0.0 (0.331 +0.059/-0.0)	14.4 (0.567)							
12 mm	50 (1.969)	12.4 +2.0/-0.0 (0.488 +0.078/-0.0)	18.4 (0.724)	Shall accommodate tape width without interference						
16 mm		16.4 +2.0/-0.0 (0.646 +0.078/-0.0)	22.4 (0.882)							



Figure 7 - Tape Leader & Trailer Dimensions





Figure 8 - Maximum Camber





KEMET Corporation World Headquarters

2835 KEMET Way Simpsonville, SC 29681

Mailing Address: P.O. Box 5928 Greenville, SC 29606

www.kemet.com Tel: 864-963-6300 Fax: 864-963-6521

Corporate Offices Fort Lauderdale, FL Tel: 954-766-2800

North America

Northeast Wilmington, MA Tel: 978-658-1663

Southeast Lake Mary, FL Tel: 407-855-8886

Central Novi. MI

Tel: 248-994-1030

Irving, TX

Tel: 972-915-6041

West

Milpitas, CA Tel: 408-433-9950

Mexico

Guadalajara, Jalisco Tel: 52-33-3123-2141

Europe

Southern Europe Sasso Marconi, Italy Tel: 39-051-939111

Skopje, Macedonia Tel: 389-2-55-14-623

Central Europe Landsberg, Germany Tel: 49-8191-3350800

Kamen, Germany Tel: 49-2307-438110

Northern Europe Wyboston, United Kingdom Tel: 44-1480-273082

Espoo, Finland Tel: 358-9-5406-5000

Asia

Northeast Asia Hong Kong Tel: 852-2305-1168

Shenzhen, China Tel: 86-755-2518-1306

Beijing, China Tel: 86-10-5877-1075

Shanghai, China Tel: 86-21-6447-0707

Seoul, South Korea Tel: 82-2-6294-0550

Taipei, Taiwan Tel: 886-2-27528585

Southeast Asia Singapore Tel: 65-6701-8033

Penang, Malaysia

Tel: 60-4-6430200

Bangalore, India Tel: 91-806-53-76817

Note: KEMET reserves the right to modify minor details of internal and external construction at any time in the interest of product improvement. KEMET does not assume any responsibility for infringement that might result from the use of KEMET Capacitors in potential circuit designs. KEMET is a registered trademark of KEMET Electronics Corporation.



Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed.

All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product—related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.