

ALUMINUM ELECTROLYTIC CAPACITORS


nichicon

ULR

Chip Type, High Voltage.




- Chip Type, high Voltage.
- Applicable to automatic mounting machine using carrier tape.
- Compliant to the RoHS directive (2011/65/EU,(EU)2015/863).
- AEC-Q200 compliant. Please contact us for details.




■ Specifications

Item	Performance Characteristics																				
Category Temperature Range	-40 to +105°C																				
Rated Voltage Range	160 to 500V																				
Rated Capacitance Range	2.7 to 39μF																				
Capacitance Tolerance	±20% at 120Hz, 20°C																				
Leakage Current	After 1 minute's application of rated voltage at 20°C, leakage current is not more than 0.04CV +100(μA).																				
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz at 20°C <table border="1"> <tr> <th>Rated voltage (V)</th> <th>160</th> <th>200</th> <th>250</th> <th>400</th> <th>450</th> <th>500</th> </tr> <tr> <th>tan δ (MAX.)</th> <td>0.20</td> <td>0.20</td> <td>0.25</td> <td>0.25</td> <td>0.30</td> <td>0.30</td> </tr> </table>							Rated voltage (V)	160	200	250	400	450	500	tan δ (MAX.)	0.20	0.20	0.25	0.25	0.30	0.30
Rated voltage (V)	160	200	250	400	450	500															
tan δ (MAX.)	0.20	0.20	0.25	0.25	0.30	0.30															
Stability at Low Temperature	Measurement frequency: 120Hz <table border="1"> <tr> <th>Rated voltage (V)</th> <th>160</th> <th>200</th> <th>250</th> <th>400</th> <th>450</th> <th>500</th> </tr> <tr> <th>Impedance ratio Z-40°C / Z+20°C (MAX.)</th> <td>6</td> <td>6</td> <td>10</td> <td>10</td> <td>15</td> <td>15</td> </tr> </table>							Rated voltage (V)	160	200	250	400	450	500	Impedance ratio Z-40°C / Z+20°C (MAX.)	6	6	10	10	15	15
Rated voltage (V)	160	200	250	400	450	500															
Impedance ratio Z-40°C / Z+20°C (MAX.)	6	6	10	10	15	15															
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 3000 hours at 105°C.				<table border="1"> <tr> <td>Capacitance change</td> <td>Within ±20% of the initial capacitance value</td> </tr> <tr> <td>tan δ</td> <td>200% or less than the initial specified value</td> </tr> <tr> <td>Leakage current</td> <td>Less than or equal to the initial specified value</td> </tr> </table>	Capacitance change	Within ±20% of the initial capacitance value	tan δ	200% or less than the initial specified value	Leakage current	Less than or equal to the initial specified value										
Capacitance change	Within ±20% of the initial capacitance value																				
tan δ	200% or less than the initial specified value																				
Leakage current	Less than or equal to the initial specified value																				
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.																				
Resistance to soldering heat	The capacitors are kept on a hot plate for 30 seconds, which is maintained at 250°C and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the characteristic requirements listed at right when they are removed from the plate.				<table border="1"> <tr> <td>Capacitance change</td> <td>Within ±10% of the initial capacitance value</td> </tr> <tr> <td>tan δ</td> <td>Less than or equal to the initial specified value</td> </tr> <tr> <td>Leakage current</td> <td>Less than or equal to the initial specified value</td> </tr> </table>	Capacitance change	Within ±10% of the initial capacitance value	tan δ	Less than or equal to the initial specified value	Leakage current	Less than or equal to the initial specified value										
Capacitance change	Within ±10% of the initial capacitance value																				
tan δ	Less than or equal to the initial specified value																				
Leakage current	Less than or equal to the initial specified value																				
Marking	Black print on the case top.																				

■ Chip Type



Type numbering system (Example : 400V 8.2μF)



● Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10 kHz or more
Coefficient	0.80	1.00	1.25	1.40	1.60

● Dimension table in next page.

CAT.8100J

ULR

■ Dimensions

Rated Voltage (V) (code)	Rated Capacitance (μ F)	Case Size ϕ D×L(mm)	$\tan \delta$	Leakage Current (μ A) (at 20°C after 1 minute)	Rated Ripple (mArms) (105°C/120Hz)	Part Number
160 (2C)	15	8×10	0.20	196	50	ULR2C150MNL1GS
	27	10×10	0.20	272.8	65	ULR2C270MNL1GS
	39	10×13.5	0.20	349.6	70	ULR2C390MNL1GS
200 (2D)	12	8×10	0.20	196	50	ULR2D120MNL1GS
	22	10×10	0.20	276	65	ULR2D220MNL1GS
	33	10×13.5	0.20	364	70	ULR2D330MNL1GS
250 (2E)	10	8×10	0.25	200	35	ULR2E100MNL1GS
	15	10×10	0.25	250	50	ULR2E150MNL1GS
	22	10×13.5	0.25	320	55	ULR2E220MNL1GS
400 (2G)	4.7	8×10	0.25	175.2	35	ULR2G4R7MNL1GS
	8.2	10×10	0.25	231.2	50	ULR2G8R2MNL1GS
	12	10×13.5	0.25	292	55	ULR2G120MNL1GS
450 (2W)	3.9	8×10	0.30	170.2	25	ULR2W3R9MNL1GS
	6.8	10×10	0.30	222.4	40	ULR2W6R8MNL1GS
	10	10×13.5	0.30	280	45	ULR2W100MNL1GS
500 (2H)	2.7	8×10	0.30	154	20	ULR2H2R7MNL1GS
	3.9	10×10	0.30	178	35	ULR2H3R9MNL1GS
	5.6	10×13.5	0.30	212	40	ULR2H5R6MNL1GS

- Taping specifications are given in page 20.
- Recommended land size, soldering by reflow are given in page 16, 17.
- Please refer to page 3 for the minimum order quantity.