

Product

TK PS 2518-11-to



Empty enclosure, base: polystyrene, grey, similar to RAL 7035, cover: polycarbonate, transparent

without knockouts

Article: TK PS 2518-11-to

Technical Data

Dimensions:

Width: 254 mm

material:


Base: Polystyrene, grey, similar to RAL 7035
 Cover: Polycarbonate, transparent
 Sealing: Polyurethane
 Cover screw: Polyamide 6, fiber-glass reinforced

Properties:

Ingress protection: IP66 - acc. EN 60529 / DIN VDE 0470-1
 Ambient temperature (min.): -25 °C
 Ambient temperature (max.): 40 °C
 Ambient temperature (24 h): 35 °C
 Max. rel. humidity at 25° C (short Therm): {100%}
 Rated insulation voltage AC: 690V
 Impact resistance: IK07 acc. DIN EN 5012 / VDE 0470 Part 100
 Protection class: II - isolate protection acc. VDE 0106 Protective insulation as per VDE 0106
 Halogen-free: ✓
 Heavy metals-free: ✓
 PVC-free: ✓
 Silicone-free: ✓

UV resistance: -
Weatherproof: -
Combustion behaviour to UL: HB/V-2 acc. UL 94
Combustion behaviour to VDE: 650°C acc. VDE 0471/ EN 60695
Fitted for outdoor application: -
Knockouts: -

Drawing



Manufacturer

Günther Spelsberg GmbH + Co. KG
 Im Gewerbepark 1
 58579 Schalksmühle
 +49 (0)2355/892-0
 +49 (0)2355/892-299
 www.spelsberg.de