

# HyFlex® 11-600 11-601 11-605

MECHANICAL PROTECTION

 MULTI-PURPOSE

 LIGHT

STYLE #	CONSTRUCTION	GAUGE	LINER MATERIAL	COATING MATERIAL	FINISHING	CUFF STYLE	COLOUR	EN SIZE	LENGTH MM	PACKAGING
11-600	Knitted	15	Nylon	Polyurethane	Palm coated	Knitwrist	White	6, 7, 8, 9, 10, 11	210 - 260	12 pairs in a bag, 12 bags in a carton
11-601	Knitted	15	Nylon	Polyurethane	Palm coated	Knitwrist	Grey and black	6, 7, 8, 9, 10	210 - 260	12 pairs in a bag, 12 bags in a carton
11-605	Knitted	15	Nylon	Polyurethane	Fingertip coated	Knitwrist	White	6, 7, 8, 9, 10	195 - 235	12 pairs in a bag, 12 bags in a carton



## Maximal dexterity and sensitivity for the most delicate handling

### PRIMARY INDUSTRIES



### IDEAL APPLICATIONS

- Assembly of small pieces such as small bearings, joints and springs

### DESCRIPTION

- Ansell's HyFlex® 11-600, 11-601 and 11-605 industrial gloves are designed for light and delicate applications in dry environments that require maximal levels of dexterity.
- Like a second skin, they offer comfortable, exact handling of small objects.
- They also ensure product protection from glove-generated debris, and cross-product contamination.
- When your operators need precision and/or clean handling, HyFlex® 11-600, 11-601 and 11-605 gloves are the answer.

### REMARKS

- Fit for special purpose

11-600:3131  
11-601:3131  
11-605:003X



**CATEGORY II**

Print date: 07-05-2014

**Ansell Healthcare Europe N.V. (European Head Office)**

Riverside Business Park, Block J

Boulevard International 55, 1070 Brussels, Belgium

Tel. +32 (0) 2 528 74 00 • Fax +32 (0) 2 528 74 01 • Fax Customer Service +32 (0) 2 528 74 03

<http://www.ansell.eu> • E-mail [info@ansell.eu](mailto:info@ansell.eu)