**IR33 Refrigeration Controllers** 



The IR33 refrigeration controllers are designed for management of refrigeration and food processing applications. The controllers have 2 NTC inputs for ambient and defrost temperatures and versions are available which have 1, 2, 3 or 4 relay outputs for control of the compressor, active defrost, evaporator ventilation fan and auxiliary output. Versions incorporating a real time clock and HACCP function are also available.

The controllers feature a simple user interface and are housed in a compact panel mounting enclosure. All versions can be connected to a network for monitoring and programming, using the optional RS-485 serial interface. The IR33 controllers are powered from 12 to 24Vac/dc or 230Vac and optional transformers are available for powering the controllers from 110Vac or 230Vac.

#### **Models Available**

**IR33S** 1 Relay O/P Refrigeration Controller **IR33Y** 2 Relay O/P Refrigeration Controller

IR33F 3 Relay O/P Refrigeration Controller


IR33C 4 Relay O/P Refrigeration Controller


#### **Product Features**

- NTC thermistor probe inputs
- Up to 4 relay outputs
- Real time clock and HACCP function
- Infrared receiver and buzzer
- 12 to 24Vac/dc or 230Vac powered
- RS-485 serial connection
- IP65 enclosure
- Plug-in terminals
- Front panel mounting system

# For digital monitoring and control in refrigeration and food processing

#### **Dimensions**






Panel cutout 71mm x 29mm (-0.0/+0.5)

Allow 95mm x 40mm clearance around controller for panel clip

#### **Connections**



## **Ordering information**

**Auxiliary Power** 

Model	Code	Description
	IR33S	1 Relay Output Digital Refrigeration Controller
		For use on static refrigeration units
		(i.e. with no evaporator fan)
	IR33Y	2 Relay Output Digital Refrigeration Controller
		For use on static refrigeration units
		with active defrost by heater
	IR33F	3 Relay Output Digital Refrigeration Controller
		For use on ventilated refrigeration units
		with compressor, defrost and fan control
	IR33C	4 Relay Output Digital Refrigeration Controller
	For	use on ventilated refrigeration units with compressor
	de	frost and fan control with additional auxiliary output

	OL	12 to 24Vac (N/A for IR33F)
	0E	230Vac
Features	Code	Description
	R00	Standard (Infrared control and RS-485 serial port)
	B00	As above but with real time clock and HACCP

**Description** 

Code

Options	Code	Description
	TRA12UNI11	110/12Vac Transformer
	TRA12UNI00	240/12Vac Transformer
	IRTRUES000	Remote control for IR33 universal
	IROPZKEY00	Programming key with battery
	IROPZKEYA0	Programming key with 230V power supply
	IROPZ485S0	RS485 serial communication interface
Example	IR33S0LR00	

## **Options**

## **Temperature Probes**

A range of NTC temperature probes are available to suit the IR33 refrigeration controllers.

#### **Remote Control**

The infrared remote control allows access to all the main functions and configuration parameters for easy set up of all IR33 controllers from a distance.

## **Programming Key**

All IR33 controllers can be programmed quickly using the optional programming key, even when not powered, reducing the risk of errors.

Tempatron: Eltime House, Hall Road, Maldon, Essex, CM9 4NF UK.



Tempatron Industrial Controls is a division of Eltime Ltd.

© Eltime Ltd. Tempatron IR33 Refrigeration Controllers 04/2011

### **Specification**

#### **Accuracy:**

- ±1% of scale range

#### **Power Supply Voltage:**

- OL: 12 to 24Vac (±10%)
- 110Vac with TRA12UNI11 transformer
- 230Vac with TRA12UNI00 transformer
- 0E: 230Vac (±10%)

#### Frequency:

- 50/60Hz

#### **Burden:**

- <3VA

## Inputs:

2 NTC inputs (10kohm @ 25°C)

## Scale Range:

- -50 to +90°C (standard)
- -40 to +150°C (extended)

#### Resolution:

- 0.1°C between -20.0°C and 20.0°C
- 1°C over the rest of the range

### **Digital Inputs:**

- 2 voltage free contacts

#### **Relay Outputs (Resistive):**

- IR33S0L: 16A changeover contact
- IR33S0E: 8A changeover contact
- IR33Y: 16A changeover contact
  - & 8A changeover contact
- IR33F: two 8A changeover contacts & 5A changeover contact
- IR33C: 16A changeover contact
  - & three 8A changeover contacts

## **Operating Temperature & Humidity:**

- -10°C to 50°C
- <90% rH (non-condensing)</p>

## **Enclosure Code:**

- Case IP65

## Weight:

- IR33S: 160g

- IR33Y: 180g

- IR33F: 200g

- IR33C: 220g

## Markings:

- CE marked (meets EN61010-1 low voltage and EN50081-1/50082-1

EMC directives)

Specification subject to change without notice.