

Ferrites and accessories

EELP 22, EILP 22 Core set (with and without clamp recess)

Series/Type: B66285G, B66285P, B66455G, B66455P, B65804

Date: September 2006

[©] EPCOS AG 2006. Reproduction, publication and dissemination of this data sheet and the information contained therein without EPCOS' prior express consent is prohibited.



ELP 22/6/16

Core (with clamp recess)

B66285

Core set EELP 22

Combination: ELP 22/6/16 with ELP 22/6/16

■ To IEC 62317-9


■ Delivery mode: single units

Magnetic characteristics (per set)


 $\Sigma I/A = 0.41 \text{ mm}^{-1}$ $I_e = 32.5 \text{ mm}$ $A_e = 78.3 \text{ mm}^2$

 $A_{min} = 77.9 \text{ mm}^2$ $V_e = 2540 \text{ mm}^3$

Approx. weight 13 g/set



ELP 22/6/16



Ungapped

Material	A _L value nH	μ_{e}	P _V W/set	Ordering code (per piece)
N49	3100 ±25%	1010	< 0.65 (50 mT, 500 kHz, 100 °C)	B66285G0000X149
N92	3400 ±25%	1110	< 1.65 (200 mT, 100 kHz, 100 °C)	B66285G0000X192
N87	4500 ±25%	1470	< 1.50 (200 mT, 100 kHz, 100 °C)	B66285G0000X187
N97	4600 ±25%	1520	< 1.20 (200 mT, 100 kHz, 100 °C)	B66285G0000X197

Calculation factors (for formulas, see "E cores: general information") **EELP 22:**

Material	Relationship between air gap – A _L value		Calculation o	of saturation current		
	K1 (25 °C)	K2 (25 °C)	K3 (25 °C)	K4 (25 °C)	K3 (100 °C)	K4 (100 °C)
N87	126	-0.814	232	-0.796	200	-0.873

Validity range: K1, K2: 0.10 mm < s < 1.50 mm

K3, K4: $100 \text{ nH} < A_L < 700 \text{ nH}$



ELP 22/6/16

ELP 22/6/16 with I 22/2.5/16

Core and accessories (with clamp recess)

B66285, B65804

FEK0340-U

122/2.5/16

Core set EILP 22 Combination: ELP 22/6/16 with I 22/2.5/16

- = To IEC 00017.0
- To IEC 62317-9
- Delivery mode: single units

Magnetic characteristics (per set)

 $\Sigma I/A = 0.33 \text{ mm}^{-1}$

 $I_0 = 26.1 \text{ mm}$

 $A_e = 78.5 \text{ mm}^2$

 $A_{min} = 77.9 \text{ mm}^2$

 $V_e = 2050 \text{ mm}^3$

Approx. weight 10.5 g/set

3,2±0,1 16,8±0,4 12,8±0,4 21,8±0,4 21,8±0,4 21,8±0,4

FEK0339-R

Ungapped

Material	A _L value nH	μ_{e}	P _V W/set	Ordering code (per piece)
N49	3700 ±25%	960	< 0.50 (50 mT, 500 kHz, 100 °C)	B66285G0000X149 (ELP core) B66285P0000X149 (I core)
N92	4000 ±25%	1050	< 1.38 (200 mT, 100 kHz, 100 °C)	B66285G0000X192 (ELP core) B66285P0000X192 (I core)
N87	5200 ±25%	1360	< 1.25 (200 mT, 100 kHz, 100 °C)	B66285G0000X187 (ELP core) B66285P0000X187 (I core)
N97	5250 ±25%	1390	< 1.00 (200 mT, 100 kHz, 100 °C)	B66285G0000X197 (ELP core) B66285P0000X197 (I core)

Calculation factors (for formulas, see "E cores: general information") EILP 22:

Material	Relationship between air gap – A _L value		Calculation o	of saturation current		
	K1 (25 °C)	K2 (25 °C)	K3 (25 °C)	K4 (25 °C)	K3 (100 °C)	K4 (100 °C)
N87	134	-0.806	243	-0.796	206	-0.873


Validity range: K1, K2: 0.10 mm < s < 1.50 mm

K3, K4: $100 \text{ nH} < A_L < 700 \text{ nH}$

Clamp

Ordering code per piece, 2 pieces required

Ordering code: B65804P2204X000





ELP 22/6/16

Core (without clamp recess)

B66455

Core set EELP 22

Combination: ELP 22/6/16 with ELP 22/6/16

■ To IEC 62317-9

■ Delivery mode: single units


Magnetic characteristics (per set)

 $\Sigma I/A = 0.41 \text{ mm}^{-1}$ $I_e = 32.5 \text{ mm}$ $A_e = 78.3 \text{ mm}^2$


 $A_{min} = 77.9 \text{ mm}^2$ $V_e = 2540 \text{ mm}^3$

v_e = 2010 111111

Approx. weight 13 g/set



ELP 22/6/16



Ungapped

Material	A _L value nH	μ_{e}	P _V W/set	Ordering code (per piece)
N49	3100 ±25%	1010	< 0.65 (50 mT, 500 kHz, 100 °C)	B66455G0000X149
N92	3400 ±25%	1110	< 1.65 (200 mT, 100 kHz, 100 °C)	B66455G0000X192
N87	4500 ±25%	1470	< 1.50 (200 mT, 100 kHz, 100 °C)	B66455G0000X187
N97	4600 ±25%	1520	< 1.20 (200 mT, 100 kHz, 100 °C)	B66455G0000X197

Calculation factors (for formulas, see "E cores: general information") **EELP 22**:

Material	Relationship between air gap – A _L value		Calculation o	Calculation of saturation current				
	K1 (25 °C)	K2 (25 °C)	K3 (25 °C)	K4 (25 °C)	K3 (100 °C)	K4 (100 °C)		
N87	126	-0.814	232	-0.796	200	-0.873		

Validity range: K1, K2: 0.10 mm < s < 1.50 mm

K3, K4: $100 \text{ nH} < A_L < 700 \text{ nH}$



ELP 22/6/16 with I 22/2.5/16

Core (without clamp recess)

B66455

Core set EILP 22 Combination: ELP 22/6/16 with I 22/2.5/16


= To IEC 60017.0

- To IEC 62317-9
- Delivery mode: single units

Magnetic characteristics (per set)

 Σ I/A = 0.33 mm⁻¹ I_e = 26.1 mm A_e = 78.5 mm² A_{min} = 77.9 mm² V_e = 2050 mm³

Approx. weight 10.5 g/set



Ungapped

Material	A _L value nH	μ_{e}	P _V W/set	Ordering code (per piece)
N49	3700 ±25%	960	< 0.50 (50 mT, 500 kHz, 100 °C)	B66455G0000X149 (ELP core) B66455P0000X149 (I core)
N92	4000 ±25%	1050	< 1.38 (200 mT, 100 kHz, 100 °C)	B66455G0000X192 (ELP core) B66455P0000X192 (I core)
N87	5200 ±25%	1360	< 1.25 (200 mT, 100 kHz, 100 °C)	B66455G0000X187 (ELP core) B66455P0000X187 (I core)
N97	5250 ±25%	1390	< 1.00 (200 mT, 100 kHz, 100 °C)	B66455G0000X197 (ELP core) B66455P0000X197 (I core)

Calculation factors (for formulas, see "E cores: general information") **EILP 22:**

Material	Relationship between air gap – A _L value K1 (25 °C) K2 (25 °C)		Calculation of saturation current				
			K3 (25 °C)	K4 (25 °C)	K3 (100 °C)	K4 (100 °C)	
N87	134	-0.806	243	-0.796	206	-0.873	

Validity range: K1, K2: 0.10 mm < s < 1.50 mm

K3, K4: $100 \text{ nH} < A_1 < 700 \text{ nH}$



Ferrites and accessories

Cautions and warnings

Mechanical stress and mounting

Ferrite cores have to meet mechanical requirements during assembling and for a growing number of applications. Since ferrites are ceramic materials one has to be aware of the special behavior under mechanical load.

As valid for any ceramic material, ferrite cores are brittle and sensitive to any shock, fast changing or tensile load. Especially high cooling rates under ultrasonic cleaning and high static or cyclic loads can cause cracks or failure of the ferrite cores.

For detailed information see Data Book 2007, chapter "General – Definitions, 8.1".

Effects of core combination on A_L value

Stresses in the core affect not only the mechanical but also the magnetic properties. It is apparent that the initial permeability is dependent on the stress state of the core. The higher the stresses are in the core, the lower is the value for the initial permeability. Thus the embedding medium should have the greatest possible elasticity.

For detailed information see Data Book 2007, chapter "General – Definitions, 8.2".

Heating up

Ferrites can run hot during operation at higher flux densities and higher frequencies.

NiZn-materials

The magnetic properties of NiZn-materials can change irreversible in high magnetic fields.

Processing notes

- The start of the winding process should be soft. Else the flanges may be destroid.
- To strong winding forces may blast the flanges or squeeze the tube that the cores can no more be mount.
- To long soldering time at high temperature (>300 °C) may effect coplanarity or pin arrangement.
- Not following the processing notes for soldering of the J-leg terminals may cause solderability problems at the transformer because of pollution with Sn oxyd of the tin bath or burned insulation of the wire. For detailed information see Data Book 2007, chapter "Processing notes, 2.2".
- The dimensions of the hole arrangement have fixed values and should be understood as a recommendation for drilling the printed circuit board. For dimensioning the pins, the group of holes can only be seen under certain conditions, as they fit into the given hole arrangement. To avoid problems when mounting the transformer, the manufacturing tolerances for positioning the customers' drilling process must be considered by increasing the hole diameter.

Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of passive electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of a passive electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of a passive electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as "hazardous"). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.
 - We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).
- 7. The trade names EPCOS, EPCOS-JONES, Baoke, Alu-X, CeraDiode, CSSP, MLSC, PhaseCap, PhaseMod, SIFI, SIFERRIT, SIKOREL, SilverCap, SIMID, SIOV, SIP5D, SIP5K, UltraCap, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.