



## SINGLE INSULATED TPE OM PROBE Ø 5 X 20MM

### SPECIFICATIONS

- TPE Overmolded Thermistor Probe for HVAC Applications
- Probe head dimensions of Ø 5 x 20mm
- 24 AWG Zipcord cable
- IP-67 Rated
- Ideal from ambient air sensing in building management applications, heater controls, air conditioning
- Available in a variety of connector types
- RoHS Compliant

This thermistor assembly consists of a NTC thermistor soldered to a single insulated TPE extension cable. The sensor and the extension cable are moulded together as one hot vulcanised unit to give a high degree of protection against water/moisture ingress.



### FEATURES

- 24AWG Zipcord TPE cable
- IP-67 Rated
- Insulation Resistance 100MΩ @ 500VDC
- Available in a variety of connector types
- Customized tolerances and resistances available on request
- Temperature range -35°C to +105°C

### APPLICATIONS

- Building Management Applications
- Heater Control
- Air Conditioning

## SINGLE INSULATED TPE OM PROBE Ø 5 X 20MM

### PERFORMANCE SPECS

Parameters	Value	Units
Nominal Resistance at +25°C	10,000	Ohms
Tolerance at +25°C	± 1	%
Beta Value 25/85	3435	K
Tolerance on Beta Value	± 1	%
Max power (probe in still air at +25°C)	400	mW
Time Constant. (63.2% Span)	Approx. 15	Seconds
Temperature range	-35 to +105	°C

### MECHANICAL DETAILS




Figure 1: TPE Overmoulded Probe Ø 5 x 20mm

	Dimensions			
	A	B	C	D
	5 ± 1mm	35 ± 3mm	Ø 5mm	20 ± 1mm
<b>Note 1</b>	NTC encapsulated using Black TPE over-mold material (Temp. Rating +125°C)			
<b>Note 2</b>	24AWG (7/32) Tin plated Zipcord cable with Black TPE jacket (Temp. Rating +125°C)			
<b>Note 3</b>	Ref part description for dimension L			

# SINGLE INSULATED TPE OM PROBE Ø 5 X 20MM

## RESISTANCE V TEMPERATURE TABLE

Temp °C	KOhms
-35°C	144.30
-34°C	136.92
-33°C	129.96
-32°C	123.39
-31°C	117.19
-30°C	111.34
-29°C	105.81
-28°C	100.58
-27°C	95.64
-26°C	90.97
-25°C	86.55
-24°C	82.37
-23°C	78.42
-22°C	74.68
-21°C	71.13
-20°C	67.77
-19°C	64.59
-18°C	61.58
-17°C	58.72
-16°C	56.01
-15°C	53.44
-14°C	51.01
-13°C	48.69
-12°C	46.50
-11°C	44.41
-10°C	42.43
-9°C	40.55
-8°C	38.76
-7°C	37.06
-6°C	35.44
-5°C	33.91
-4°C	32.44
-3°C	31.05
-2°C	29.73
-1°C	28.47
0°C	27.27

Temp °C	KOhms
1°C	26.12
2°C	25.03
3°C	23.99
4°C	23.00
5°C	22.06
6°C	21.16
7°C	20.30
8°C	19.48
9°C	18.70
10°C	17.95
11°C	17.24
12°C	16.56
13°C	15.91
14°C	15.29
15°C	14.69
16°C	14.12
17°C	13.58
18°C	13.06
19°C	12.56
20°C	12.09
21°C	11.63
22°C	11.20
23°C	10.78
24°C	10.38
25°C	10.00
26°C	9.63
27°C	9.28
28°C	8.95
29°C	8.62
30°C	8.31
31°C	8.02
32°C	7.73
33°C	7.46
34°C	7.20
35°C	6.95
36°C	6.70

Temp °C	KOhms
37°C	6.47
38°C	6.25
39°C	6.04
40°C	5.83
41°C	5.63
42°C	5.44
43°C	5.26
44°C	5.08
45°C	4.92
46°C	4.75
47°C	4.60
48°C	4.45
49°C	4.30
50°C	4.16
51°C	4.03
52°C	3.90
53°C	3.77
54°C	3.66
55°C	3.54
56°C	3.43
57°C	3.32
58°C	3.22
59°C	3.12
60°C	3.02
61°C	2.93
62°C	2.84
63°C	2.75
64°C	2.67
65°C	2.59
66°C	2.51
67°C	2.44
68°C	2.37
69°C	2.30
70°C	2.23
71°C	2.16
72°C	2.10

Temp °C	KOhms
73°C	2.04
74°C	1.98
75°C	1.93
76°C	1.87
77°C	1.82
78°C	1.77
79°C	1.72
80°C	1.67
81°C	1.62
82°C	1.58
83°C	1.53
84°C	1.49
85°C	1.45
86°C	1.41
87°C	1.37
88°C	1.34
89°C	1.30
90°C	1.27
91°C	1.23
92°C	1.20
93°C	1.17
94°C	1.14
95°C	1.11
96°C	1.08
97°C	1.05
98°C	1.02
99°C	1.00
100°C	0.97
101°C	0.95
102°C	0.92
103°C	0.90
104°C	0.88
105°C	0.86

## SINGLE INSULATED TPE OM PROBE Ø 5 X 20MM

### ORDERING INFORMATION

TE Part Number	Legacy Ref	Description	$\Omega$ @25°C	MOQ
GA10K3435STM010	10K3435STM010	TPE OM Probe Ø 5 x 20mm Length 1 meter	10,000	1,000*
20024687-20	10K3435STM020	TPE OM Probe Ø 5 x 20mm Length 2 meter	10,000	1,000*
20024687-30	10K3435STM030	TPE OM Probe Ø 5 x 20mm Length 3 meter	10,000	1,000*

\* For quantities less than Minimum Order Quantity – contact distribution

#### NORTH AMERICA

Measurement Specialties, Inc.,  
customercare.ando@te.com

#### EUROPE

Measurement Specialties (Europe), Ltd.,  
Email: customercare.glwy@te.com

#### ASIA

Measurement Specialties (China), Ltd.,  
Email: customercare.chdu@te.com

#### [te.com/sensorsolutions](https://te.com/sensorsolutions)

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2022 TE Connectivity Ltd. family of companies All Rights Reserved.

