

Radial Leaded PTC - Nickel Thin Film Linear Thermistors



FEATURES

- Nickel thin film PTC element
- High stability over the entire temperature range
- cUL recognized component: File E148885
- Epoxy coated UL 94 V-0 approved
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

APPLICATIONS

Temperature measurement, sensing, compensation, and control in industrial and consumer applications. For on-board or remote sensing.

MARKING

The thermistors are laser marked with value and tolerance reference on an epoxy based coating.
(Example: 102F = 10 x 10² = 1000 Ω 1 %))

MOUNTING

By soldering or welding in any position.

DESCRIPTION

These thermistors are based on a Nickel thin film resistor technology as thermal sensitive material. The device consists of a thin film ceramic chip with two tinned copper clad steel wire leads.

| QUICK REFERENCE DATA | | | |
|---|---------------------------|-----------|-------|
| PARAMETER DESCRIPTION | VALUE | | UNIT |
| | TFPTL10 | TFPTL15 | |
| Resistance value at 25 °C ⁽²⁾ | 100 to 1K | 100 to 5K | Ω |
| Tolerance on R ₂₅ -value ⁽²⁾ | ± 1; ± 5 | | % |
| TCR at 25 °C | 4110 | | ppm/K |
| Tolerance on TCR at 25 °C ⁽¹⁾ | ± 400 | | ppm/K |
| Operating temperature range: at rated power at zero dissipation | -55 to +70 -55 to +150 | | °C |
| Response time (in oil) | ≈ 1.1 | ≈ 1.6 | s |
| Dissipation factor δ (for information only) | 2.9 | 3.4 | mW/K |
| Maximum rated power at 70 °C (P ₇₀) | 75 | 100 | mW |
| Maximum working voltage RCWV ⁽³⁾ | 30 | 40 | V |
| Climatic category (LCT/UCT/days) | 55/150/56 | | - |
| Weight | 0.12 | 0.14 | g |

Notes


- (1) Contact Vishay if closer TCR lot tolerance is desired
- (2) Other R₂₅-values and tolerances are available upon request
- (3) Rated continuous working voltage is maximum working voltage or $\sqrt{P_{70} \times R}$, whichever is less


| STANDARD RESISTANCE VALUES at 25 °C in Ω | | | | | | | | | | |
|--|-----|-----|-----|-----|-----|------|------|------|------|------|
| 100 | 150 | 220 | 330 | 470 | 680 | 1K | 1.5K | 2.2K | 3.3K | 4.7K |
| 120 | 180 | 270 | 390 | 560 | 820 | 1.2K | 1.8K | 2.7K | 3.9K | 5.0K |

Note

- Other R₂₅-values and tolerances are available upon request

| GLOBAL PART NUMBER INFORMATION | | | | | | | | | | | | | | | |
|---|----------|-----------------|---------------------------------------|------------------------|--------------------|--|---|---|---|---|---|---|---|---|---|
| Global Part Numbering: TFPTL10L1001FL2B | | | | | | | | | | | | | | | |
| T | F | P | T | L | 1 | 0 | L | 1 | 0 | 0 | 1 | F | L | 2 | B |
| PRODUCT TYPE | SIZE | CHARACTERISTICS | RESISTANCE VALUE | TOLERANCE | LEAD CONFIGURATION | PACKAGING | | | | | | | | | |
| TFPT Leaded | 10 15 | L = Linear | 1000 = 100R 1001 = 1K 5001 = 5K | F = ± 1 % J = ± 5 % | L2 H5 | B = Bulk (500 pieces) U = Ammopack (2500 pieces) T = T/R (4000 pieces) | | | | | | | | | |

DIMENSIONS

L2


 Component outline for
lead spacing $2.5 \text{ mm} \pm 0.8 \text{ mm}$
(straight leads)

H5

 Component outline for
lead spacing $5.0 \text{ mm} \pm 0.8 \text{ mm}$
(flat bent leads)

| TFPTL DIMENSIONS in millimeters | | | | |
|-------------------------------------|-----------------|---------------|---------------|---------------|
| | SIZE L10 | | SIZE L15 | |
| | L2 | H5 | L2 | H5 |
| $Wb_{\text{max.}}$ | 3.6 | | 4.0 | |
| $H_{\text{max.}}$ | 3.5 | | 3.8 | |
| $SH_{\text{max.}}$ (seating height) | 5.0 | 6.2 | 5.2 | 6.5 |
| d | $0.5 \pm 10 \%$ | | | |
| L | 25 min. | | | |
| F | 2.5 ± 0.8 | 5.0 ± 0.8 | 2.5 ± 0.8 | 5.0 ± 0.8 |
| $T_{\text{max.}}$ | 2.2 | | 2.4 | |

Notes

- Bulk packed types have a standard lead length $L = 25 \text{ mm}$ minimum
- Thickness is defined as “T”


Note

- Zero power is considered as measuring power max. 1 % of rated power P_{70}



| PERFORMANCE | |
|---|---|
| TEST | MAXIMUM $\Delta R_{25}/R_{25}$ ⁽¹⁾ |
| Storage dry heat (5000 h at 125 °C) | ± 0.25 % |
| High temperature exposure (1000 h at 150 °C) | ± 0.3 % |
| Damp heat steady state, unloaded (1344 h at 40 °C/95 % RH) | ± 0.2 % |
| Thermal cycling (15 min at -55 °C, 15 min at 150 °C, 100 cycles) | ± 0.2 % |
| Thermal cycling (15 min at -55 °C, 15 min at 125 °C, 1000 cycles) | ± 0.2 % |
| Short time overload (2.5 x P ₇₀ for 60s at 70 °C) | ± 0.2 % |
| Long term dissipation (1000 h rated power at 70 °C) | ± 0.2 % |
| Resistance to soldering heat (10 s at 260 °C) | ± 0.25 % |

Note

(1) TFPTs are ESD sensitive

| AVERAGE RATIO R/R ₂₅ TFPTL ALL SIZES AND VALUES | | | | | | | | | | | |
|--|-------------------|-------|-------------------|-------|-------------------|-------|-------------------|-------|-------------------|-------|-------------------|
| TEMP. | R/R ₂₅ | TEMP. | R/R ₂₅ | TEMP. | R/R ₂₅ | TEMP. | R/R ₂₅ | TEMP. | R/R ₂₅ | TEMP. | R/R ₂₅ |
| -55 | 0.702 | -15 | 0.843 | 25 | 1.000 | 65 | 1.173 | 105 | 1.362 | 145 | 1.568 |
| -54 | 0.705 | -14 | 0.847 | 26 | 1.004 | 66 | 1.177 | 106 | 1.367 | 146 | 1.574 |
| -53 | 0.708 | -13 | 0.851 | 27 | 1.008 | 67 | 1.182 | 107 | 1.372 | 147 | 1.579 |
| -52 | 0.712 | -12 | 0.854 | 28 | 1.012 | 68 | 1.186 | 108 | 1.377 | 148 | 1.584 |
| -51 | 0.715 | -11 | 0.858 | 29 | 1.017 | 69 | 1.191 | 109 | 1.382 | 149 | 1.590 |
| -50 | 0.719 | -10 | 0.862 | 30 | 1.021 | 70 | 1.196 | 110 | 1.387 | 150 | 1.595 |
| -49 | 0.722 | -9 | 0.866 | 31 | 1.025 | 71 | 1.200 | 111 | 1.392 | | |
| -48 | 0.725 | -8 | 0.869 | 32 | 1.029 | 72 | 1.205 | 112 | 1.397 | | |
| -47 | 0.729 | -7 | 0.873 | 33 | 1.033 | 73 | 1.209 | 113 | 1.402 | | |
| -46 | 0.732 | -6 | 0.877 | 34 | 1.037 | 74 | 1.214 | 114 | 1.407 | | |
| -45 | 0.736 | -5 | 0.881 | 35 | 1.042 | 75 | 1.219 | 115 | 1.412 | | |
| -44 | 0.739 | -4 | 0.885 | 36 | 1.046 | 76 | 1.223 | 116 | 1.417 | | |
| -43 | 0.743 | -3 | 0.889 | 37 | 1.050 | 77 | 1.228 | 117 | 1.422 | | |
| -42 | 0.746 | -2 | 0.892 | 38 | 1.054 | 78 | 1.232 | 118 | 1.427 | | |
| -41 | 0.749 | -1 | 0.896 | 39 | 1.059 | 79 | 1.237 | 119 | 1.432 | | |
| -40 | 0.753 | 0 | 0.900 | 40 | 1.063 | 80 | 1.242 | 120 | 1.437 | | |
| -39 | 0.756 | 1 | 0.904 | 41 | 1.067 | 81 | 1.246 | 121 | 1.442 | | |
| -38 | 0.760 | 2 | 0.908 | 42 | 1.071 | 82 | 1.251 | 122 | 1.448 | | |
| -37 | 0.763 | 3 | 0.912 | 43 | 1.076 | 83 | 1.256 | 123 | 1.453 | | |
| -36 | 0.767 | 4 | 0.916 | 44 | 1.080 | 84 | 1.261 | 124 | 1.458 | | |
| -35 | 0.771 | 5 | 0.920 | 45 | 1.084 | 85 | 1.265 | 125 | 1.463 | | |
| -34 | 0.774 | 6 | 0.924 | 46 | 1.089 | 86 | 1.270 | 126 | 1.468 | | |
| -33 | 0.778 | 7 | 0.927 | 47 | 1.093 | 87 | 1.275 | 127 | 1.473 | | |
| -32 | 0.781 | 8 | 0.931 | 48 | 1.097 | 88 | 1.280 | 128 | 1.478 | | |
| -31 | 0.785 | 9 | 0.935 | 49 | 1.102 | 89 | 1.284 | 129 | 1.484 | | |
| -30 | 0.788 | 10 | 0.939 | 50 | 1.106 | 90 | 1.289 | 130 | 1.489 | | |
| -29 | 0.792 | 11 | 0.943 | 51 | 1.110 | 91 | 1.294 | 131 | 1.494 | | |
| -28 | 0.796 | 12 | 0.947 | 52 | 1.115 | 92 | 1.299 | 132 | 1.499 | | |
| -27 | 0.799 | 13 | 0.951 | 53 | 1.119 | 93 | 1.303 | 133 | 1.505 | | |
| -26 | 0.803 | 14 | 0.955 | 54 | 1.124 | 94 | 1.308 | 134 | 1.510 | | |
| -25 | 0.806 | 15 | 0.959 | 55 | 1.128 | 95 | 1.313 | 135 | 1.515 | | |
| -24 | 0.810 | 16 | 0.963 | 56 | 1.133 | 96 | 1.318 | 136 | 1.520 | | |
| -23 | 0.814 | 17 | 0.967 | 57 | 1.137 | 97 | 1.323 | 137 | 1.526 | | |
| -22 | 0.817 | 18 | 0.971 | 58 | 1.141 | 98 | 1.328 | 138 | 1.531 | | |
| -21 | 0.821 | 19 | 0.975 | 59 | 1.146 | 99 | 1.333 | 139 | 1.536 | | |



RATIO FORMULA

$$R_T = R_{25} \times (9.0014 \times 10^{-1} + 3.87235 \times 10^{-3} (\text{°C})^{-1} \times T + 4.86825 \times 10^{-6} (\text{°C})^{-2} \times T^2 + 1.37559 \times 10^{-9} (\text{°C})^{-3} \times T^3)$$



$$T(\text{°C}) = 28.54 \times (R_T/R_{25})^3 - 158.5 \times (R_T/R_{25})^2 + 474.8 \times (R_T/R_{25}) - 319.85$$

| RATIO TOLERANCES | | |
|------------------|------------|---------|
| LOW TEMP. | HIGH TEMP. | TOL. |
| -55 °C | +150 °C | ± 4 % |
| -40 °C | +125 °C | ± 3 % |
| -20 °C | +85 °C | ± 2 % |
| 0 °C | +55 °C | ± 1 % |
| +12 °C | +40 °C | ± 0.5 % |

Ratio Tolerance Examples:

At 40 °C, ratio = 1.063 ± 0.5 % (0.005)
so, ratio = 1.058 to 1.068

At 125 °C, ratio = 1.460 ± 3 % (0.044)
so, ratio = 1.416 to 1.504





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.