



SPECIFICATIONS

Basic Functions	Range	Best Accuracy
DC Voltage Measurement	400mV 4V/40V/400V 1000V	±(0.8%+3) ±(0.5%+1) ±(1%+3)
AC Voltage Measurement	400mV 4V/40V/400V 750V	±(1.2%+5) ±(1%+3) ±(1.2%+5)
AC Current Measurement	400.0μA/4000μA 40.00mA/400.0mA 4.000A/10.00A	±(1.2%+5) ±(1.5%+5) ±(2%+5)
DC Current Measurement	400.0μA/4000μA 40.00mA/400.0mA 4.000A/10.00A	±(1%+2) ±(1.2%+3) ±(1.5%+3)
Resistance Measurement	400.0Ω 4.000kΩ/40.00kΩ/400.0kΩ 4.000MΩ 40.00MΩ	±(1.2%+2) ±(1%+2) ±(1.2%+2) ±(1.5%+2)
Capacitance Measurement	40.00nF 400.0nF/4.000μF/40.00μF 400.0μF 4000μF	±(3%+5) ±(3%+5) ±(4%+5) Only reference
Frequency	10Hz-10MHz	±(0.1%+4)
Frequency Response		45~400Hz
Duty Cycle	0.1%~99.9%	✓
Special Functions		
Manual Ranging		✓
Diode		✓
EF Function		✓
Audion	1000Ω	✓
Continuity Buzzer		✓
Data Hold		✓
Max/Min Mode		✓
Display Backlight		✓

REL		✓
Sleep Mode	Around 15 Minutes	
Analogue Bar Graph	41	✓
RS232(USB)		
Fuse		✓
Input Impedance for DC Voltage Measurement	Around 10M Ω	✓
Low Battery Display	<7.5V	✓

GENERAL CHARACTERISTICS

Power	9V Battery (6F22) x 1
LCD Size	65 x 43mm
Product Colour	Red and Grey
Product Net Weight	370g
Product Size	180 x 87 x 47mm
Standard Accessories	Battery, Test Lead, English Manual, Socket Adaptor
Optional Accessories	USB
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	20 pcs
Standard Carton Measurement	465 x 335 x 345mm (0.054 CBM Per Standard Carton)
Standard Carton Gross Weight	12kg