


## Carbon Film Resistors

# Professional & Flame-Proof Type

## Miniature Style [ FC0 Series ]



### INTRODUCTION


The FC0 Series Carbon Film Professional & Flame-Proof Resistors are manufactured by coating a homogeneous film of pure carbon on high grade ceramic rods. After a helical groove has been cut in the resistive layer; tinned connecting leads of electrolytic copper are welded to the end-caps. The resistors are coated with layers of green color lacquer.

### FEATURES

Power Rating	0.4W, 0.6W
Resistance Tolerance	±2%, ±5%
T.C.R.	see Table 1
Flameproof Multi-layer Coating Meets	UL-94V-0
Flameproof Feature Meets Overload Test	UL-1412

### DERATING CURVE

For resistors operated in ambient temperatures above 70°C, power rating must be derated in accordance with the curve below.



### TABLE 1 TEMPERATURE COEFFICIENT

STYLE	TEMP. COEFFICIENT (ppm/°C)		
	under 100KΩ	100KΩ - 1MΩ	1MΩ - 10MΩ
FC0204, FC0207	-500~300	-700~0	-1,500~0

### DIMENSIONS

Unit: mm



STYLE	DIMENSION			
	L	øD	H	ød
Miniature				
FC0204	3.4±0.3	1.9±0.2	28±2.0	0.45±0.05
FC0207	6.3±0.5	2.4±0.2	28±2.0	0.55±0.05

Note:

---



---



---



---



---



---

### ELECTRICAL CHARACTERISTICS

STYLE	FC0204	FC0207
Power Rating at 70°C	0.4W	0.6W
Maximum Working Voltage	200V	300V
Maximum Overload Voltage	400V	600V
Voltage Proof on Insulation	300V	500V
Resistance Range	1Ω - 10MΩ & for E24 series value	
Operating Temp. Range	-55°C to +155°C	
Temperature Coefficient	see Table I	

Note: Special value is available on request

### ENVIRONMENTAL CHARACTERISTICS

PERFORMANCE TEST	TEST METHOD	APPRAISE
Short Time Overload	IEC 60115-1 4.13 2.5 times RCWV for 5 sec. (Not more than maximum Overload Voltage)	±0.75%+0.05Ω
Voltage Proof on Insulation	IEC 60115-1 4.7 In V-Block for 60 sec., test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8 Between -55°C to +155°C	By type
Insulation Resistance	IEC 60115-1 4.6 in V-block for 60 Sec.	>1,000MΩ
Solderability	IEC 60115-1 4.17 245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30 IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16 Direct load for 10 Sec. in the direction of the terminal leads	≥2.5kg (24.5N)
Periodic-pulse Overload	IEC 60115-1 4.39 4 times RCWV 10,000 cycles (1 Sec. on, 25 Sec. off)	±1.0%+0.05Ω
Damp Heat Steady State	IEC 60115-1 4.24 40±2°C, 90-95% RH for 56 days, loaded with 0.1 times RCWV	±3.0%+0.05Ω
Endurance at 70°C	IEC 60115-1 4.25 70±2°C at RCWV (or Umax., Whichever less) for 1,000 Hr. (1.5Hr.on, 0.5Hr. Off)	±3.0%+0.05Ω
Temperature Cycling	IEC 60115-1 4.19 -55°C ⇌ Room Temp. ⇌ +155°C ⇌ Room Temp. (5 cycles)	±1.0%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18 260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±1.0%+0.05Ω
Accidental Overload Test	IEC 60115-1 4.26 4 times RCWV for 1 Min.	No evidence of flaming or arcing

Note: RCWV(Rated Continuous Working Voltage) =  $\sqrt{\text{Power Rating} \times \text{Resistance Value}}$  or Max. working voltage listed above, whichever less.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Yageo:

[CFR2WSJT-52-820R](#) [CFR-50JT-52-3R](#) [CFR-50JT-52-4M](#) [CFR-50JT-52-590R](#) [CFR-50JT-52-9R1](#) [CFR50SJR-52-1K8](#) [CFR50SJR-52-220K](#) [CFR50SJR-52-2K2](#) [CFR50SJT-26-1M](#) [CFR50SJT-26-20K](#) [CFR50SJT-26-2K](#) [CFR50SJT-26-3K6](#) [CFR50SJT-26-4K7](#) [CFR50SJT-26-510R](#) [CFR50SJT-26-750R](#) [CFR-50JT-52-8R2](#) [CFR50SJR-52-1K5](#) [CFR50SJR-52-3K3](#) [CFR50SJR-52-510K](#) [CFR50SJR-52-91K](#) [CFR50SJT-26-160K](#) [CFR50SJT-26-1K8](#) [CFR50SJT-26-4K3](#) [CFR50SJT-26-510K](#) [CFR50SJT-26-620K](#) [CFR50SJT-52J2K7](#) [CFR50SJT-PN2K2A](#) [CFR50SJT-26-82K](#) [CFR50SJT-PN3K3](#) [CFR50SJT-PN3K9](#) [FC0207JT-52-1M](#) [CFR50SJT-26-1K2](#) [CFR50SJT-26-1K3](#) [CFR50SJT-26-1K6](#) [CFR50SJT-26-300K](#) [CFR50SJT-26-330K](#) [CFR50SJT-26-560K](#) [CFR50SJT-26-56KC](#) [CFR50SJT-26-5K](#) [CFR50SJT-52-60K](#) [CFR50SJT-52-660R](#) [FC0207JT-52-4K7](#) [CFR100JT-73-120R](#) [CFR50SJR-52-56K](#) [CFR50SJT-26-200K](#) [CFR50SJT-26-2K2](#) [CFR50SJT-26-390R](#) [CFR50SJT-26-51K](#) [CFR50SJT-26-820K](#) [CFR50SJT-52-26K](#) [CFR50SJT-PN100K](#) [CFR50SJT-PN3K3A](#) [FC0207JT-52-2K](#) [CFR100GT-52-470K](#) [CFR100GT-73-2K](#) [CFR100JT-52-500K](#) [CFR100JT-73-12K](#) [CFR100JT-73-100K](#) [CFR25SJT-26-27K](#) [CFR25SJT-26-2R2](#) [CFR25SJT-26-3K6](#) [CFR25SJT-26-5K6](#) [CFR25SJT-26-68K](#) [CFR25SJT-26-75K](#) [CFR25SJT-26-82K](#) [CFR25SJT-52-1M1](#) [CFR25SJT-52-1M5](#) [CFR25SJT-52-2R2](#) [CFR25SJT-52-4R3](#) [CFR25SJT-52-5R1](#) [CFR25SJT-52-7R5](#) [CFR25SJT-52A20K](#) [CFR25SJT-52A2K](#) [CFR25SJT-52A330K](#) [CFR-50JT-52-1R3](#) [CFR-50JT-52-5M](#) [CFR-50JT-52-5M6](#) [CFR-50JT-52-6R8](#) [CFR50SJR-52-1M](#) [CFR50SJR-52-820K](#) [CFR50SJT-26-150K](#) [CFR50SJT-26-27K](#) [CFR50SJT-26-3K9](#) [CFR50SJT-26-5K1](#) [CFR50SJT-PN13K](#) [CFR25SJT-52A47K](#) [CFR25SJT-52A56K](#) [CFR25SJT-52A5K1](#) [CFR2WSJT-52-120K](#) [CFR-50JR-52-280R](#) [CFR50SJR-52-2K7](#) [CFR25SJT-52A1K6](#) [CFR25SJT-52A2K7](#) [CFR25SJT-52A4K3](#) [CFR25SJT-52A510K](#) [CFR25SJT-52A820K](#) [CFR25SJT-52A91K](#) [CFR2WSJT-52-330K](#) [CFR-50JT-52-1M8](#) [CFR-50JT-52-4M3](#)