

Cable marker label - US-WML 14 (25X19) - 0800473

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Cable marker label, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: adhesive, cable diameter: ≤ 14 mm, lettering field size: 25 x 19 mm




Your advantages

- ✓ The cable marker labels do not increase the cross section of the cable, allowing the cable to be subsequently drawn through cable ducts, for example
- ✓ High-quality labeling image created by thermal transfer printing
- ✓ Quick and easy handling
- ✓ Resistant to solvents
- ✓ The protective foil is wound over the labeling and provides permanent protection against dirt and abrasion
- ✓ US-WML ... cable marker labels consist of a labeling field and a transparent protective foil



Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 607056
GTIN	4046356607056
Weight per Piece (excluding packing)	5.150 g
Custom tariff number	39199080
Country of origin	Germany

Technical data

Dimensions

Length (b)	25.4 mm
Width (a)	63.5 mm

Ambient conditions

Ambient temperature (operation)	-50 °C ... 110 °C
---------------------------------	-------------------

General

Cable marker label - US-WML 14 (25X19) - 0800473

Technical data

General

Color	white
Base element material	Vinyl film
Type	Label
Components	Silicone-free
Material	PVC
RoHS compliant	Yes
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	8
Number of individual labels per row	4
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146464 THERMOMARK CARD
	5146451 THERMOMARK CARD-US-MAG1
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Burning behaviour	self-extinguishing
Foil strength	0.06 mm
Marking mounting type	adhesive

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27400400
eCl@ss 6.0	27400400
eCl@ss 7.0	27400401

Cable marker label - US-WML 14 (25X19) - 0800473

Classifications

eCl@ss

eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504

Accessories

Accessories

Magazine

Magazine - TMP-US-MAG1 - 0803341



Magazine, For THERMOMARK CARD and THERMOMARK PRIME, for accommodating US cards