# AC/DC ENCLOSED POWER SUPPLY 15W



## STONTRONICS: SGS15-5, SGS15-12, SGS15-15, SGS15-24

#### **Features:**

- Low Cost, High Reliability
- Overload and Short Circuit Protection
- Free air cooling convection
- High operating temperature up to 60°C



#### **Description:**

The 15W Enclosed power supply has been specially designed to offer high efficiency, long life and high reliability for use in a variety of applications. This range comprises of 5 models with outputs of either 5v, 12v, 15v, 24v, 48v. Each models is RoHS, CE, UL approved and come with a three year warranty.

MODEL		SGS15-5	SGS15-12	SGS15-15	SGS15-24	
Output	DC Voltage	5V	12V	15V	24V	
	Rated Current	3A	1.3A	1A	0.7A	
	Current Range	0~3A	0~1.3A	0~1A	0~0.7A	
	Rated Power	15W	15.6W	15W	16.8W	
	Ripple & Noise	100mVp-p	120mVp-p	150mVp-p	200mVp-p	
	Voltage Regulation Range	4.5~5.5V	10.8~13.2V	13.5~16.5V	21.6~26.4V	
	Voltage Accuracy	+/- 1.0%	+/- 1.0%			
	Line Regulation	+/- 0.5%	+/- 0.5%			
	Load Regulation	+/- 2.0 %	+/- 1.0%	+/- 1.0%	+/- 1.0%	
	Rise Time	2000ms, 50ms	2000ms, 50ms / 230Vac at 100% Load			
	Hold Up Time	20ms / 230Vac	20ms / 230Vac at 100% Load			
Input	Full Input Voltage Range	88-264Vac	88-264Vac			
	Full Frequency Range	47-63Hz	47-63Hz			
	AC Current	0.4A / 115Vac (	0.4A / 115Vac 0.4A / 230Vac			
	In Rush Current	40A / 230Vac	40A / 230Vac			
	Leakage Current	<3.5mA / 230V	<3.5mA / 230Vac			
	Over Load	110~150% rate	110~150% rated output power			
Protection	Short Circuit	Hiccup Mode, a	Hiccup Mode, auto-recovery after fault condition is removed			
Environment	Working Temp	-10°C ~ +60°C (	-10°C ~ +60°C (230Vac) (Refer to output derating curve)			
	Working Humidity	20~90% RH no	20~90% RH non-condensing			
	Storage Temp	-20°C ~ +45°C	-20°C ~ +45°C			
	Storage Humidity	10 ~ 95% RH no	10 ~ 95% RH non-condensing			
	Temp. Co-efficiency	+/-0.03% / °C (0	+/-0.03% / °C (0 ~ 50oC)			
	Vibration Resistance	10 ~ 500Hz, 2G	10 ~ 500Hz, 2G, 10 minute cycle, X, Y, Z 60 minute in each direction			
Safety	Safety Standards	EN60950-1, UL	EN60950-1, UL60950-1, CSA-C22.2 No. 60950-1 Approved			
	Withstand Voltage	I/P-0/P: 3KVac	I/P-0/P: 3KVac   I/P-FG: 1.5KVac   0/P-FG: 0.5KVac			
	Isolation Resistance	I/P-0/P, I/P-FG,	I/P-0/P, I/P-FG, 0/P-FG: >50M $\Omega$ / 500VDC/ 25 °C / 70%RH			
	EMC Emission	Compliance to	Compliance to EN55022 Class B, EN61000-3-2, -3			
	EMC Immunity	Compliance to	Compliance to EN55024, EN61000-4-2, -3, -4, -5, -6, -8, -11			
Others	Lifetime	50,000 Hours (2	50,000 Hours (25 °C)			
	Size	85mm x 58.5m	85mm x 58.5mm x 36.5mm (L x W x H			
	Package	80pcs/ctn, 20K	80pcs/ctn, 20KG, 0.25Kg/piece			
Notes	The power supply is considered a component which must be installed into final equipment. The final equipment must be re-confirmed that it meets all applicable directives.					

### **STONTRONICS**