

# Energizer® Vision HD Rechargeable Metal

# ENPMHRL7

The *Energizer®* Vision HD Rechargeable Metal Light delivers high-performance innovation with exceptional light output. It is easy to use and features USB-in and out ports, which means it is rechargeable and can also charge devices making it a great option for situations when you need to charge your device. This light is built with durable aircraft grade aluminum which makes it a great tool for DIY projects and worktasks. The unique MAXVIZ technology enables users to experience sharp high-definition performance with daylight color and wide uniform light output. Its brightness, durability and features make the *Energizer®* Vision HD Rechargeable Metal Light a dependable light for various tasks. Includes USB charging cable.




Provides 1000 Lumens of Light



Provides Run Time of 4 Hours



Sustains 1 Meter Drop Test



Illuminates objects up to 200m away



Water Resistant IPX4 – works after splashing water on all sides

### DESIGN BENEFITS

- ✓ Durable Aircraft Grade Aluminum
- ✓ Rechargeable
- ✓ USB Port Out: Charges Devices
- ✓ 20 Year Design To Last based on typical consumer usage patterns
- ✓ One press Digital Focusing
- ✓ Easy to use

### LIGHT AND POWER SOURCE


- ✓ Features LED Technology
- ✓ 4.25 hz strobe light
- ✓ Rechargeable Lithium Ion Battery (26650) – non removable battery

### ELECTRICAL CHARACTERISTICS

Electrical Characteristics Nominal Power: Power consumption 11.4W / Battery 26650 Li-ion 3.7V dc  
LED Specifications: LED 3.0V cc / 3800mA

### CERTIFICATES AND COMPLIANCE

**CE RoHS**  
EMC, EN62471, FCC



This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Tested according to ANSI/NEMA FL1 Standards.

\*Light must be turned off while charging.

\*\*Based on an average smartphone battery of 1810 mAh capacity.

### PERFORMANCE BENEFITS

- ✓ Exceptional light output for any task
- ✓ Up to 15X brighter than Standard LED Technology
- ✓ MAXVIZ Technology to deliver a wide, powerful beam and high-definition vision
- ✓ Powerful light even after a full smartphone charge\*\*
- ✓ Rechargeable – Fully charge in 8 hours\*

### SPECIFICATIONS

**Weight including Battery:**  
378 Grams / 13.33 Ounces

**Dimensions:**  
226.5mm x 48mm x 48mm / 8.92" x 1.89" x 1.89"

### NUMBER OF OPERATING MODES: 7

Mode	Lumens (lm)	Runtime (h)	Beam Distance (m)
High	1000	4	200
Low	250	8	--
Strobe	--	--	--
Spot High	Digital Focus		
Spot Low			
Wide High			
Wide Low			