

TTC-6-FMRS-PT - Remote signaling set



2907811

<https://www.phoenixcontact.com/us/products/2907811>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Module set for the optical monitoring and floating remote signaling of adjacent surge protective devices in the TERMITRAB complete or CLIXTRAB product family. Suitable for directly grounded DIN rails.

Your advantages

- Space-saving and cost-saving with a narrow overall width of just 6 mm
- Collective remote monitoring of up to 40 protective devices via optical monitoring
- Finding the right product for all possible requirements in MCR applications is easy, thanks to the complete range of products with customized features

Commercial data

Item number	2907811
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL23
Product key	CL226Z
Catalog page	Page 127 (C-4-2019)
GTIN	4055626244419
Weight per piece (including packing)	74.114 g
Weight per piece (excluding packing)	71.7 g
Customs tariff number	85363010
Country of origin	DE

TTC-6-FMRS-PT - Remote signaling set



2907811

<https://www.phoenixcontact.com/us/products/2907811>

Technical data

Product properties

Type	DIN rail module, one-piece
Product type	Remote signaling set
Product family	TERMITRAB complete

Insulation characteristics

Pollution degree	2
------------------	---

Electrical properties

Indicator/remote signaling

Switching function	N/C contact
--------------------	-------------

Supply: Status indicator/remote signaling

Operating voltage	10 V DC ... 36 V DC
Operating current	30 mA DC (24 V)
	60 mA DC (10 V)

Connection data

Connection method	Push-in connection
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross section AWG	24 ... 12

Ex data

Altitude	≤ 2000 m (amsl)
----------	-----------------

Dimensions

Dimensional drawing	
Width	12.6 mm +0.1 mm
Height	105.8 mm
Depth	83.5 mm (incl. DIN rail 7.5 mm)

Material specifications

Flammability rating according to UL 94	V-0
Insulating material	PBT
Housing material	PBT

Protective circuit

TTC-6-FMRS-PT - Remote signaling set



2907811

<https://www.phoenixcontact.com/us/products/2907811>

Surge protection fault message	Optical, remote indicator contact
--------------------------------	-----------------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	≤ 4000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %

Approvals

Conformity/Approvals

UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D T4A
------------------	--

Standards and regulations

Standards/specifications	EN 61000-6-2
Note	2005
Standards/specifications	EN 61000-6-3
Note	2007 + A1:2011
Standards/specifications	EN IEC 60079-0
Note	2018
Standards/specifications	EN IEC 60079-7
Note	2015 + A1:2018
Standards/specifications	IEC 60079-0
Note	2017
Standards/specifications	IEC 60079-7
Note	2017

Mounting

Mounting type	DIN rail: TH 35 - 7.5 mm
---------------	--------------------------

TTC-6-FMRS-PT - Remote signaling set




2907811


<https://www.phoenixcontact.com/us/products/2907811>

Drawings

Dimensional drawing



Circuit diagram



TTC-6-FMRS-PT - Remote signaling set



2907811

<https://www.phoenixcontact.com/us/products/2907811>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2907811>



CSA

Approval ID: 70136717



DNV GL

Approval ID: TAE000027G



UL Listed

Approval ID: FILE E 138168



CSAus

Approval ID: 70136717

UAE-RoHS

Approval ID: 22-06-16192



cUL Listed

Approval ID: FILE E 333250



UL Listed

Approval ID: FILE E 333250



IECEX

Approval ID: IECEx BVS 21.0057X



CCC

Approval ID: 2022122304116080



ATEX

Approval ID: BVS 21 ATEX E 052 X

cCSAus

TTC-6-FMRS-PT - Remote signaling set

2907811

<https://www.phoenixcontact.com/us/products/2907811>



cULus Listed

TTC-6-FMRS-PT - Remote signaling set



2907811

<https://www.phoenixcontact.com/us/products/2907811>

Classifications

ECLASS

ECLASS-11.0	27130813
ECLASS-13.0	27171501

ETIM

ETIM 9.0	EC001625
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

TTC-6-FMRS-PT - Remote signaling set



2907811

<https://www.phoenixcontact.com/us/products/2907811>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

TTC-6-FMRS-PT - Remote signaling set



2907811

<https://www.phoenixcontact.com/us/products/2907811>

Accessories

ZBF 6 CUS - Zack Marker strip, flat

0825027

<https://www.phoenixcontact.com/us/products/0825027>



Zack Marker strip, flat, Strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 6.2 mm, lettering field size: 5.15 x 6.15 mm, Number of individual labels: 10

ZBF 6:UNBEDRUCKT - Zack Marker strip, flat

0808710

<https://www.phoenixcontact.com/us/products/0808710>



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.15 x 6.15 mm, Number of individual labels: 10

TTC-6-FMRS-PT - Remote signaling set



2907811

<https://www.phoenixcontact.com/us/products/2907811>

ZBF 6/WH-100:UNBEDRUCKT - Zack Marker strip, flat

0808736

<https://www.phoenixcontact.com/us/products/0808736>



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.15 x 6.15 mm, Number of individual labels: 1000

ZBF 6,QR:FORTL.ZAHLEN - Zack Marker strip, flat

0808765

<https://www.phoenixcontact.com/us/products/0808765>



Zack Marker strip, flat, Strip, white, labeled, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 91 ... 100, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.15 x 6.15 mm, Number of individual labels: 10

TTC-6-FMRS-PT - Remote signaling set

2907811

<https://www.phoenixcontact.com/us/products/2907811>



CLIPFIX 35-5 - End bracket

3022276

<https://www.phoenixcontact.com/us/products/3022276>




Quick mounting end clamp for NS 35/7,5 DIN rail or NS 35/15 DIN rail, with marking option, with parking option for FBS...5, FBS...6, KSS 5, KSS 6, width: 5.15 mm, color: gray

TS-UK 6-T - Separating plate

3072820

<https://www.phoenixcontact.com/us/products/3072820>



Separating plate, width: 1 mm, height: 66.5 mm, color: gray

TTC-6-FMRS-PT - Remote signaling set

2907811

<https://www.phoenixcontact.com/us/products/2907811>



TTC-EX-PP - Separating plate

1011977

<https://www.phoenixcontact.com/us/products/1011977>

Partition plate for NS-35/7,5 DIN rails to ensure a clearance of 50 mm between the remote signaling module and surge protection in TTC-EX systems.



X-PEN 0,35 - Marker pen

0811228

<https://www.phoenixcontact.com/us/products/0811228>

Marker pen without ink cartridge, for manual labeling of markers, labeling extremely wipe-proof, line thickness 0.35 mm



Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com