



REV.

NOTES: SUPPLIED IN TUBES

DATE

1. TUBE SPECIFICATIONS: 6.30 [160.00] LONG

DESCRIPTION

800 DOMES PER TUBE

- 2. OPERATING TEMPERATURE: -40°F [-40°C] TO 220°F [105°C]
- 3. STORAGE TEMPERATURE: -65°F [-55°C] TO 250°F [125°C]
- 4. MAT'L: .003 [0.08] STAINLESS STEEL
- 5. FINISH: NICKEL PLATE
- 6. TRIP FORCE: 220g

KEYSTONE ELECTRONICS CORP.		
www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900		
PART NAME		
MINI 4 LEG DOME		
MATERIAL		
AS NOTED		
AS NOTED	DRN BY NT	2.15.17
	APP'D LN	SCALE 6X; NA
TOLERANCES INCH [MM] CODE	DWG NO.	
DECIMAL ± .005 [± 0.13] ANGULAR ± 1° UNI ESS OTHERWISE SPECIFIED	5133	