

LB 10-6 GY - Bridge



0202358

<https://www.phoenixcontact.com/us/products/0202358>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bridge, pitch: 6 mm, number of positions: 10, color: gray



Commercial data

Item number	0202358
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z2X
Catalog page	Page 260 (CL-2002)
GTIN	4017918098575
Weight per piece (including packing)	20.08 g
Weight per piece (excluding packing)	20.08 g
Customs tariff number	85369095
Country of origin	PL

Technical data

Product properties

Product type	Screw bridge
Number of positions	10
Pitch	6 mm

Dimensions

Pitch	6 mm
-------	------

Material specifications

Color	gray
Material	Copper
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Screw mounting
---------------	----------------

LB 10-6 GY - Bridge

0202358

<https://www.phoenixcontact.com/us/products/0202358>



Classifications

ECLASS

ECLASS-11.0	27141140
ECLASS-12.0	27141140
ECLASS-13.0	27250303

ETIM

ETIM 9.0	EC000489
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

LB 10-6 GY - Bridge

0202358

<https://www.phoenixcontact.com/us/products/0202358>



Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e No hazardous substances above threshold values
------------	---

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com