

TA7769P

POWER AMPLIFIER 2x1W

$V_{CC\ MAX} = 14V$

$V_{CC\ TYP} = 6V$

$V_{CC\ RNG} = 4,5...9V$

$P_o = 2 \times 1W$

$R_L = 4\ \Omega$

$TDH = 10\%$

$I_{CCO\ TYP} = 30mA$

$I_{CCO\ MAX} = 55mA$

$I_{MAX} = 1,5A$

$R_{IN} = 30k$

Gain = 45dB

Noise = 2mkV

$R_{THJ-c} = -$

Case DIL16

