

InvenSense Inc.

1745 Technology Drive, San Jose, CA 95110 U.S.A +1(408) 988–7339 www.invensense.com Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

MPU-6881 Product Specification Revision 1.0



Document Number: PS-MPU-6881A-00 Revision: 1.0 Release Date: 05/22/2014

TABLE OF CONTENTS

T	ABLE O	F FIGURES	4
Т	ABLE O	F TABLES	5
1	DOC	JMENT INFORMATION	6
	1.1	REVISION HISTORY	6
	1.2	PURPOSE AND SCOPE	7
	1.3	PRODUCT OVERVIEW	7
	1.4	APPLICATIONS	7
2	FEAT	URES	8
	2.1	GYROSCOPE FEATURES	8
	2.2	ACCELEROMETER FEATURES	8
	2.3	ADDITIONAL FEATURES	8
3	ELEC	TRICAL CHARACTERISTICS	9
	3.1	GYROSCOPE SPECIFICATIONS	9
	3.2	ACCELEROMETER SPECIFICATIONS	10
	3.3	ELECTRICAL SPECIFICATIONS	11
	3.4	I2C TIMING CHARACTERIZATION	15
	3.5	SPI TIMING CHARACTERIZATION	16
	3.6	ABSOLUTE MAXIMUM RATINGS	18
4	APPL	ICATIONS INFORMATION	19
	4.1	PIN OUT DIAGRAM AND SIGNAL DESCRIPTION	19
	4.2	TYPICAL OPERATING CIRCUIT	20
	4.3	BILL OF MATERIALS FOR EXTERNAL COMPONENTS	20
	4.4	BLOCK DIAGRAM	21
	4.5	OVERVIEW	21
	4.6	THREE-AXIS MEMS GYROSCOPE WITH 16-BIT ADCS AND SIGNAL CONDITIONING	22
	4.7	THREE-AXIS MEMS ACCELEROMETER WITH 16-BIT ADCS AND SIGNAL CONDITIONING	22
	4.8	I2C AND SPI SERIAL COMMUNICATIONS INTERFACES	22
	4.9	SELF-TEST	24
	4.10	CLOCKING	25
	4.11	SENSOR DATA REGISTERS	25
	4.12	FIFO	25
	4.13	INTERRUPTS	25
	4.14	DIGITAL-OUTPUT TEMPERATURE SENSOR	25



Document Number: PS-MPU-6881A-00 Revision: 1.0 Release Date: 05/22/2014

	4.15	BIAS AND LDOS	26
	4.16	CHARGE PUMP	26
	4.17	STANDARD POWER MODES	26
5	PRO	GRAMMABLE INTERRUPTS	27
6	DIGIT	AL INTERFACE	28
	6.1	I2C AND SPI SERIAL INTERFACES	28
	6.2	I2C INTERFACE	28
	6.3	I2C COMMUNICATIONS PROTOCOL	28
	6.4	I ² C Terms	31
	6.5	SPI Interface	32
7	SERI	AL INTERFACE CONSIDERATIONS	32
	7.1	MPU-6881 Supported Interfaces	33
8	ASSE	EMBLY	34
	8.1	ORIENTATION OF AXES	34
	8.2	PACKAGE DIMENSIONS	35
9	PART	NUMBER PACKAGE MARKING	36
10	RELI	ABILITY	37
	10.1	QUALIFICATION TEST POLICY	37
	10.2	QUALIFICATION TEST PLAN	37
11	REFE	RENCE	38



Document Number: PS-MPU-6881A-00 Revision: 1.0 Release Date: 05/22/2014

Table of Figures

Figure 1 I2C Bus Timing Diagram	15
Figure 2 SPI Bus Timing Diagram	
Figure 3 Pin out Diagram for MPU-6881 3.0x3.0x0.9mm QFN	
Figure 4 MPU-6881 QFN Application Schematic. (a) I2C operation, (b) SPI operation	20
Figure 5 MPU-6881 Block Diagram	21
Figure 6 MPU-6881 Solution Using I2C Interface	23
Figure 7 MPU-6881 Solution Using SPI Interface	24
Figure 8 START and STOP Conditions	29
Figure 9 Acknowledge on the I ² C Bus	29
Figure 10 Complete I ² C Data Transfer	30
Figure 11 Typical SPI Master / Slave Configuration	32
Figure 12 I/O Levels and Connections	33
Figure 13 Orientation of Axes Sensitivity and Polarity of Rotation	34



Document Number: PS-MPU-6881A-00 Revision: 1.0 Release Date: 05/22/2014

Table of Tables

Table 1 Gyroscope Specifications	<u>C</u>
Table 2 Accelerometer Specifications	10
Table 3 D.C. Electrical Characteristics	
Table 4 A.C. Electrical Characteristics	13
Table 5 Other Electrical Specifications	14
Table 6 I ² C Timing Characteristics	
Table 7 SPI Timing Characteristics	16
Table 8 fCLK = 20MHz	
Table 9 Absolute Maximum Ratings	18
Table 10 Signal Descriptions	19
Table 11 Bill of Materials	
Table 12 Standard Power Modes for MPU-6881	26
Table 13 Table of Interrupt Sources	
Table 14 Serial Interface	
Table 15 I ² C Terms	31



Document Number: PS-MPU-6881A-00 Revision: 1.0 Release Date: 05/22/2014

1 **Document Information**

1.1 Revision History

Revision Date	Revision	Description
05/22/2014	1.0	Initial Release



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

1.2 Purpose and Scope

This document is a preliminary product specification, providing a description, specifications, and design related information on the MPU-6881[™] MotionTracking device. The device is housed in a small 3x3x0.9mm 24-pin QFN package.

Specifications are subject to change without notice. Final specifications will be updated based upon characterization of production silicon. For references to register map and descriptions of individual registers, please refer to the MPU-6881 Register Map and Register Descriptions document.

1.3 Product Overview

The MPU-6881 is a 6-axis MotionTracking device that combines a 3-axis gyroscope, and a 3-axis accelerometer in a small 3x3x0.9mm (24-pin QFN) package. It also features a 4096-byte FIFO that can lower the traffic on the serial bus interface, and reduce power consumption by allowing the system processor to burst read sensor data and then go into a low-power mode. With its dedicated I²C sensor bus, the MPU-6881 directly accepts inputs from external I²C devices. MPU-6881, with its 6-axis integration, enables manufacturers to eliminate the costly and complex selection, qualification, and system level integration of discrete devices, guaranteeing optimal motion performance for consumers. MPU-6881 is also designed to interface with multiple non-inertial digital sensors, such as pressure sensors, on its auxiliary I²C port.

The gyroscope has a programmable full-scale range of ± 250 , ± 500 , ± 1000 , and ± 2000 degrees/sec. The accelerometer has a user-programmable accelerometer full-scale range of $\pm 2g$, $\pm 4g$, $\pm 8g$, and $\pm 16g$. Factory-calibrated initial sensitivity of both sensors reduces production-line calibration requirements.

Other industry-leading features include on-chip 16-bit ADCs, programmable digital filters, a precision clock with 1% drift from -40°C to 85°C, an embedded temperature sensor, and programmable interrupts. The device features I²C and SPI serial interfaces, a VDD operating range of 1.71 to 3.45V, and a separate digital IO supply, VDDIO from 1.71V to 3.45V.

Communication with all registers of the device is performed using either I²C at 400kHz or SPI at 1MHz. For applications requiring faster communications, the sensor and interrupt registers may be read using SPI at 20MHz.

By leveraging its patented and volume-proven CMOS-MEMS Fabrication platform, which integrates MEMS wafers with companion CMOS electronics through wafer-level bonding, InvenSense has driven the package size down to a footprint and thickness of 3x3x0.9mm (24-pin QFN), to provide a very small yet high performance low cost package. The device provides high robustness by supporting 10,000*g* shock reliability.

1.4 Applications

- TouchAnywhere™ technology (for "no touch" UI Application Control/Navigation)
- *MotionCommand*™ technology (for Gesture Short-cuts)
- Motion-enabled game and application framework
- · Location based services, points of interest, and dead reckoning
- Handset and portable gaming
- Motion-based game controllers
- 3D remote controls for Internet connected DTVs and set top boxes, 3D mice
- Wearable sensors for health, fitness and sports



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

2 Features

2.1 Gyroscope Features

The triple-axis MEMS gyroscope in the MPU-6881 includes a wide range of features:

- Digital-output X-, Y-, and Z-axis angular rate sensors (gyroscopes) with a user-programmable fullscale range of ±250, ±500, ±1000, and ±2000°/sec and integrated 16-bit ADCs
- Digitally-programmable low-pass filter
- Gyroscope operating current: 3.2mA
- · Factory calibrated sensitivity scale factor
- Self-test

2.2 Accelerometer Features

The triple-axis MEMS accelerometer in MPU-6881 includes a wide range of features:

- Digital-output X-, Y-, and Z-axis accelerometer with a programmable full scale range of ±2g, ±4g, ±8g and ±16g and integrated 16-bit ADCs
- Accelerometer normal operating current: 450µA
- Low power accelerometer mode current: 7.27μA at 0.98Hz, 18.65μA at 31.25Hz
- User-programmable interrupts
- Wake-on-motion interrupt for low power operation of applications processor
- Self-test

2.3 Additional Features

The MPU-6881 includes the following additional features:

- Auxiliary master I²C bus for reading data from external sensors (e.g. magnetometer)
- 3.4mA operating current when all 6 motion sensing axes are active
- VDD supply voltage range of 1.8 3.3V ± 5%
- VDDIO reference voltage of 1.8 3.3V ± 5% for auxiliary I²C devices
- Smallest and thinnest QFN package for portable devices: 3x3x0.9mm (24-pin QFN)
- Minimal cross-axis sensitivity between the accelerometer and gyroscope axes
- 4096 byte FIFO buffer enables the applications processor to read the data in bursts
- Digital-output temperature sensor
- User-programmable digital filters for gyroscope, accelerometer, and temp sensor
- 10,000 *g* shock tolerant
- 400kHz Fast Mode I²C for communicating with all registers
- 1MHz SPI serial interface for communicating with all registers
- 20MHz SPI serial interface for reading sensor and interrupt registers
- MEMS structure hermetically sealed and bonded at wafer level
- RoHS and Green compliant



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

3 Electrical Characteristics

3.1 Gyroscope Specifications

Typical Operating Circuit of section 4.2, VDD = 1.8V, VDDIO = 1.8V, T_A=25°C, unless otherwise noted.

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS	NOTES
	GYROSCOPE SENSITIVITY					
Full-Scale Range	FS_SEL=0		±250		°/s	
	FS_SEL=1		±500		°/s	
	FS_SEL=2		±1000		°/s	
	FS_SEL=3		±2000		°/s	
Gyroscope ADC Word Length			16		bits	
Sensitivity Scale Factor	FS_SEL=0		131		LSB/(°/s)	
	FS_SEL=1		65.5		LSB/(°/s)	
	FS_SEL=2		32.8		LSB/(°/s)	
	FS_SEL=3		16.4		LSB/(°/s)	
Sensitivity Scale Factor Tolerance	25°C		±4		%	1
Sensitivity Scale Factor Variation Over Temperature	0°C to +55°C		±10		%	1
Nonlinearity	Best fit straight line; 25°C		0.2		%	1
Cross-Axis Sensitivity			±2		%	
	ZERO-RATE OUTPUT (ZRO)					
Initial ZRO Tolerance	25°C		±60		°/s	1
ZRO Variation Over Temperature	0°C to +55°C		±60		°/s	
GYF	ROSCOPE NOISE PERFORMANCE (I	FS_SEL=0))			
Total RMS Noise	DLPFCFG=2 (92 Hz)		0.7		°/s-rms	1
GYROSCOPE MECHANICAL FREQUENCIES		25	27	29	KHz	1
LOW PASS FILTER RESPONSE	Programmable Range	5		250	Hz	
GYROSCOPE START-UP TIME	From Sleep mode		35		ms	1
OUTPUT DATA RATE	Programmable, Normal (Filtered) mode	4		8000	Hz	1

Please refer to the following document for information on Self-Test: MPU-6500 Accelerometer and Gyroscope Self-Test Implementation; AN-MPU-6500A-02.

Table 1 Gyroscope Specifications

Notes:

1. Derived from validation or characterization of parts, not guaranteed in production.



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

3.2 Accelerometer Specifications

Typical Operating Circuit of section 4.2, VDD = 1.8V, VDDIO = 1.8V, T_A=25°C, unless otherwise noted.

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS	NOTES
	ACCELEROMETER SENSIT	TIVITY				
	AFS_SEL=0		±2		g	
Full-Scale Range	AFS_SEL=1		±4		g	
Full-Scale Range	AFS_SEL=2		±8		g	
	AFS_SEL=3		±16		g	
ADC Word Length	Output in two's complement format		16		bits	
	AFS_SEL=0		16,384		LSB/g	
Consitiuity Cools Factor	AFS_SEL=1		8,192		LSB/g	
Sensitivity Scale Factor	AFS_SEL=2		4,096		LSB/g	
	AFS_SEL=3		2,048		LSB/g	
Initial Calibration Tolerance			±4		%	1
Sensitivity Change vs. Temperature	-40°C to +85°C AFS_SEL=0 Component-level		±4		%	1
Nonlinearity	Best Fit Straight Line		0.5		%	
Cross-Axis Sensitivity			±2		%	
	ZERO-G OUTPUT				•	
Initial Tolerance	Component-level, all axes	-80	±60	+80	m <i>g</i>	
Zero-G Level Change vs. Temperature	X and Y axes, 0°C to +70°C Z axis, 0°C to +70°C	-0.64 -1		+0.64 +1	m <i>g/⁰</i> C m <i>g/⁰</i> C	
	NOISE PERFORMANC	E				
Power Spectral Density	Low noise mode		400		μ <i>g</i> /√Hz	1
LOW PASS FILTER RESPONSE	Programmable Range	5		260	Hz	
INTELLIGENCE FUNCTION INCREMENT			32		mg/LSB	
ACCELEROMETER STARTUP TIME	From Sleep mode			20	ms	
	From Cold Start, 1ms V _{DD} ramp			30	ms	
	Low power (duty-cycled)	0.244		500	Hz	
OUTPUT DATA RATE	Duty-cycled, over temp		±15		%	1
	Low noise (active)	4		4000	Hz	

Please refer to the following document for information on Self-Test: MPU-6500 Accelerometer and Gyroscope Self-Test Implementation; AN-MPU-6500A-02.

Table 2 Accelerometer Specifications

Notes:

1. Derived from validation or characterization of parts, not guaranteed in production.



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

3.3 Electrical Specifications

3.3.1 D.C. Electrical Characteristics

Typical Operating Circuit of section 4.2, VDD = 1.8V, VDDIO = 1.8V, T_A=25°C, unless otherwise noted.

PARAMETER	CONDITIONS	MIN	TYP	MAX	Units	Notes		
SUPPLY VOLTAGES								
VDD		1.71	1.8	3.45	V			
VDDIO		1.71	1.8	3.45	V			
SUPPLY CURRENTS								
Normal Mode	6-axis		3.4		mA	1		
	3-axis Gyroscope		3.2		mA	1		
	3-Axis Accelerometer		450		μΑ	1		
Accelerometer Low Power Mode	0.98 Hz update rate		7.27		μΑ	1,2		
(Gyroscope disabled)	31.25 Hz update rate		18.65		μA	1,2		
Standby Mode			1.6		mA	1		
Full-Chip Sleep Mode			6		μΑ	1		
TEMPERATURE RANGE								
Specified Temperature Range	Performance parameters are not applicable beyond Specified Temperature Range	-40		+85	°C			

Table 3 D.C. Electrical Characteristics

Notes:

- 1. Derived from validation or characterization of parts, not guaranteed in production.
- 2. Accelerometer Low Power Mode supports the following output data rates (ODRs): 0.24, 0.49, 0.98, 1.95, 3.91, 7.81, 15.63, 31.25, 62.50, 125, 250, 500Hz. Supply current for any update rate can be calculated as:
 - a. Supply Current in μ A = 6.9 + Update Rate * 0.376



Document Number: PS-MPU-6881A-00

Revision: 1.0 Release Date: 05/22/2014

3.3.2 A.C. Electrical Characteristics

Typical Operating Circuit of section 4.2, VDD = 1.8V, VDDIO = 1.8V, T_A =25°C, unless otherwise noted.

Parameter	Conditions	MIN	TYP	MAX	Units	NOTES
	SUP	PLIES				
Supply Ramp Time	Monotonic ramp. Ramp rate is 10% to 90% of the final value	0.1		100	ms	1
	TEMPERAT	URE SENSOR				
Operating Range	Ambient	-40		85	°C	
Sensitivity	Untrimmed		333.87		LSB/°C	1
Room Temp Offset	21°C		0		LSB	1
	Power-C	n RESET				1
Supply Ramp Time (T _{RAMP})	Valid power-on RESET	0.01	20	100	ms	1
Start-up time for register read/write	From power-up		11	100	ms	1
I ² C ADDRESS	AD0 = 0 AD0 = 1		1101000 1101001	100	1110	
	DIGITAL INPUTS (SYN	IC, AD0, SCLK,	•			I
V _{IH} , High Level Input Voltage		0.7*VDDIO			V	1
V _{IL} , Low Level Input Voltage		0 122.0		0.3*VDDIO	V	1
C _I , Input Capacitance			< 10		pF	
	DIGITAL OUT	PUT (SDO, INT)				
V _{OH} , High Level Output Voltage	R_{LOAD} =1M Ω ;	0.9*VDDIO			V	
V _{OL1} , LOW-Level Output Voltage	R_{LOAD} =1M Ω ;			0.1*VDDIO	V	
V _{OL.INT1} , INT Low-Level Output Voltage	OPEN=1, 0.3mA sink Current			0.1	V	1
Output Leakage Current	OPEN=1		100		nA	
t _{INT} , INT Pulse Width	LATCH_INT_EN=0		50		μs	
	12C I/O (SCL, SDA)				
V _{IL} , LOW Level Input Voltage		-0.5V		0.3*VDDIO	V	
V _{IH} , HIGH-Level Input Voltage		0.7*VDDIO		VDDIO + 0.5V	V	
V _{hys} , Hysteresis			0.1*VDDIO		V	
V _{OL} , LOW-Level Output Voltage	3mA sink current	0		0.4	V	1
I _{OL} , LOW-Level Output Current	V_{OL} =0.4V V_{OL} =0.6V		3 6		mA mA	
Output Leakage Current			100		nA	
$t_{\text{of}},$ Output Fall Time from V_{IHmax} to V_{ILmax}	C _b bus capacitance in pf	20+0.1C _b		250	ns	
	INTERNAL CI	OCK SOURCE				
	Fchoice=0,1,2 SMPLRT_DIV=0		32		kHz	
Sample Rate	Fchoice=3; DLPFCFG=0 or 7 SMPLRT_DIV=0		8		kHz	



Document Number: PS-MPU-6881A-00

Revision: 1.0 Release Date: 05/22/2014

Parameter	Conditions	MIN	TYP	MAX	Units	NOTES
	Fchoice=3; DLPFCFG=1,2,3,4,5,6; SMPLRT_DIV=0		1		kHz	
Clock Fraguency Initial Telerance	CLK_SEL=0, 6; 25°C	-5		+5	%	1
Clock Frequency Initial Tolerance	CLK_SEL=1,2,3,4,5; 25°C	-1		+1	%	1
Frequency Variation over Temperature	CLK_SEL=0,6	-10		+10	%	1
Frequency variation over Temperature	CLK_SEL=1,2,3,4,5		±1		%	1

Table 4 A.C. Electrical Characteristics

Notes:

1. Derived from validation or characterization of parts, not guaranteed in production.



Document Number: PS-MPU-6881A-00

Revision: 1.0 Release Date: 05/22/2014

3.3.3 **Other Electrical Specifications**

Typical Operating Circuit of section 4.2, VDD = 1.8V, VDDIO = 1.8V, T_A=25°C, unless otherwise noted.

PARAMETER	CONDITIONS	MIN	TYP	MAX	Units	Notes		
SERIAL INTERFACE								
SPI Operating Frequency, All Registers Read/Write	Low Speed Characterization		100 ±10%		kHz			
Registers Read/Write	High Speed Characterization		1 ±10%		MHz			
SPI Operating Frequency, Sensor and Interrupt Registers Read Only			20 ±10%		MHz			
I ² C Operating Frequency	All registers, Fast-mode			400	kHz			
1 C Operating Frequency	All registers, Standard-mode			100	kHz			

Table 5 Other Electrical Specifications

Notes:

1. Derived from validation or characterization of parts, not guaranteed in production.



Document Number: PS-MPU-6881A-00

Revision: 1.0 Release Date: 05/22/2014

I2C Timing Characterization

Typical Operating Circuit of section 4.2, VDD = 1.8V, VDDIO = 1.8V, T_A=25°C, unless otherwise noted.

Parameters	Conditions	Min	Typical	Max	Units	Notes
I ² C TIMING	I ² C FAST-MODE					
f _{SCL} , SCL Clock Frequency				400	kHz	
t _{HD.STA} , (Repeated) START Condition Hold Time		0.6			μs	
t _{LOW} , SCL Low Period		1.3			μs	
t _{ніGН} , SCL High Period		0.6			μs	
t _{SU.STA} , Repeated START Condition Setup Time		0.6			μs	
t _{HD.DAT} , SDA Data Hold Time		0			μs	
t _{SU.DAT} , SDA Data Setup Time		100			ns	
t _r , SDA and SCL Rise Time	C _b bus cap. from 10 to 400pF	20+0.1C _b		300	ns	
t _f , SDA and SCL Fall Time	C _b bus cap. from 10 to 400pF	20+0.1C _b		300	ns	
t _{SU.STO} , STOP Condition Setup Time		0.6			μs	
t _{BUF} , Bus Free Time Between STOP and START Condition		1.3			μs	
C _b , Capacitive Load for each Bus Line			< 400		pF	
t _{VD.DAT} , Data Valid Time				0.9	μs	
t _{VD.ACK} , Data Valid Acknowledge Time				0.9	μs	

Table 6 I²C Timing Characteristics

Notes:

- 1. Timing Characteristics apply to both Primary and Auxiliary I2C Bus
- Based on characterization of 5 parts over temperature and voltage as mounted on evaluation board or in sockets




Figure 1 I2C Bus Timing Diagram

Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

3.5 SPI Timing Characterization

Typical Operating Circuit of section 4.2, VDD = 1.8V, VDDIO = 1.8V, T_A=25°C, unless otherwise noted.

Parameters	Conditions	Min	Typical	Max	Units	Notes
SPI TIMING						
f _{SCLK} , SCLK Clock Frequency				1	MHz	
t _{LOW} , SCLK Low Period		400			ns	
t _{нібн} , SCLK High Period		400			ns	
t _{SU.CS} , CS Setup Time		8			ns	
t _{HD.CS} , CS Hold Time		500			ns	
t _{su.sdi} , SDI Setup Time		11			ns	
t _{HD.SDI} , SDI Hold Time		7			ns	
t _{VD.SDO} , SDO Valid Time	C _{load} = 20pF			100	ns	
t _{HD.SDO} , SDO Hold Time	C _{load} = 20pF	4			ns	
t _{DIS.SDO} , SDO Output Disable Time				50	ns	

Table 7 SPI Timing Characteristics

Notes:

3. Based on characterization of 5 parts over temperature and voltage as mounted on evaluation board or in sockets




Figure 2 SPI Bus Timing Diagram

3.5.1 fSCLK = 20MHz

Parameters	Conditions	Min	Typical	Max	Units
SPI TIMING					
f _{SCLK} , SCLK Clock Frequency		0.9		20	MHz
t _{LOW} , SCLK Low Period		-		-	ns
t _{HIGH} , SCLK High Period		-		-	ns
t _{SU.CS} , CS Setup Time		1			ns
t _{HD.CS} , CS Hold Time		1			ns



Document Number: PS-MPU-6881A-00

Revision: 1.0 Release Date: 05/22/2014

t _{SU.SDI} , SDI Setup Time		0			ns
t _{HD.SDI} , SDI Hold Time		1			ns
t _{VD.SDO} , SDO Valid Time	C _{load} = 20pF		25		ns
t _{DIS.SDO} , SDO Output Disable Time				25	ns

Table 8 fCLK = 20MHz

Notes:

1. Based on characterization of 5 parts over temperature and voltage as mounted on evaluation board or in sockets



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

3.6 Absolute Maximum Ratings

Stress above those listed as "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these conditions is not implied. Exposure to the absolute maximum ratings conditions for extended periods may affect device reliability.

Parameter	Rating
Supply Voltage, VDD	-0.5V to +4V
Supply Voltage, VDDIO	-0.5V to +4V
PLLFILT	-0.5V to 2V
Input Voltage Level (AD0, SYNC, INT, SCL, SDA)	-0.5V to VDD + 0.5V
Acceleration (Any Axis, unpowered)	10,000g for 0.2ms
Operating Temperature Range	-40°C to +85°C
Storage Temperature Range	-40°C to +125°C
Electrostatic Discharge (ESD) Protection	2kV (HBM); 250V (MM)
Latch-up	JEDEC Class II (2),125°C ±100mA

Table 9 Absolute Maximum Ratings



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

4 Applications Information

4.1 Pin Out Diagram and Signal Description

Pin Number	Pin Name	Pin Description
7	AUX_CL	I ² C Master serial clock, for connecting to external sensors
8	VDDIO	Digital I/O supply voltage
9	AD0 / SDO	I ² C Slave Address LSB (AD0); SPI serial data output (SDO)
10	REGOUT	Regulator filter capacitor connection
11	FSYNC	Frame synchronization digital input. Connect to GND if unused.
12	INT	Interrupt digital output (totem pole or open-drain)
13	VDD	Power supply voltage and Digital I/O supply voltage
18	GND	Power supply ground
19	RESV	Reserved. Do not connect.
20	RESV	Reserved. Connect to GND.
21	AUX_DA	I ² C master serial data, for connecting to external sensors
22	nCS	Chip select (SPI mode only)
23	SCL / SCLK	I ² C serial clock (SCL); SPI serial clock (SCLK)
24	SDA / SDI	I ² C serial data (SDA); SPI serial data input (SDI)
1 – 6, 14 - 17	NC	No Connect pins. Do not connect.

Table 10 Signal Descriptions




Figure 3 Pin out Diagram for MPU-6881 3.0x3.0x0.9mm QFN



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

4.2 Typical Operating Circuit




Figure 4 MPU-6881 QFN Application Schematic. (a) I2C operation, (b) SPI operation.

4.3 Bill of Materials for External Components

Component	Label	Specification	Quantity
PLL Filter Capacitor	C1	Ceramic, X7R, 0.1µF ±10%, 2V	1
VDD Bypass Capacitor	C2	Ceramic, X7R, 0.1µF ±10%, 4V	1
VDDIO Bypass Capacitor	C3	Ceramic, X7R, 10nF ±10%, 4V	1

Table 11 Bill of Materials



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

4.4 Block Diagram




Figure 5 MPU-6881 Block Diagram

4.5 Overview

The MPU-6881 is comprised of the following key blocks and functions:

- Three-axis MEMS rate gyroscope sensor with 16-bit ADCs and signal conditioning
- Three-axis MEMS accelerometer sensor with 16-bit ADCs and signal conditioning
- Primary I²C and SPI serial communications interfaces
- Auxiliary I²C serial interface
- Self-Test
- Clocking
- Sensor Data Registers
- FIFO
- Interrupts
- Digital-Output Temperature Sensor
- Bias and LDOs
- Charge Pump
- Standard Power Modes



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

4.6 Three-Axis MEMS Gyroscope with 16-bit ADCs and Signal Conditioning

The MPU-6881 consists of three independent vibratory MEMS rate gyroscopes, which detect rotation about the X-, Y-, and Z- Axes. When the gyros are rotated about any of the sense axes, the Coriolis Effect causes a vibration that is detected by a capacitive pickoff. The resulting signal is amplified, demodulated, and filtered to produce a voltage that is proportional to the angular rate. This voltage is digitized using individual on-chip 16-bit Analog-to-Digital Converters (ADCs) to sample each axis. The full-scale range of the gyro sensors may be digitally programmed to ± 250 , ± 500 , ± 1000 , or ± 2000 degrees per second (dps). The ADC sample rate is programmable from 8,000 samples per second, down to 3.9 samples per second, and user-selectable low-pass filters enable a wide range of cut-off frequencies.

4.7 Three-Axis MEMS Accelerometer with 16-bit ADCs and Signal Conditioning

The MPU-6881's 3-Axis accelerometer uses separate proof masses for each axis. Acceleration along a particular axis induces displacement on the corresponding proof mass, and capacitive sensors detect the displacement differentially. The MPU-6881's architecture reduces the accelerometers' susceptibility to fabrication variations as well as to thermal drift. When the device is placed on a flat surface, it will measure 0g on the X- and Y-axes and $\pm 1g$ on the Z-axis. The accelerometers' scale factor is calibrated at the factory and is nominally independent of supply voltage. Each sensor has a dedicated sigma-delta ADC for providing digital outputs. The full scale range of the digital output can be adjusted to $\pm 2g$, $\pm 4g$, $\pm 8g$, or $\pm 16g$.

4.8 I2C and SPI Serial Communications Interfaces

The MPU-6881 communicates to a system processor using either a SPI or an I²C serial interface. The MPU-6881 always acts as a slave when communicating to the system processor. The LSB of the of the I²C slave address is set by pin 4 (AD0).

4.8.1 MPU-6881 Solution Using I2C Interface

In the figure below, the system processor is an I²C master to the MPU-6881.



Document Number: PS-MPU-6881A-00

Revision: 1.0 Release Date: 05/22/2014




Figure 6 MPU-6881 Solution Using I2C Interface



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

4.8.2 MPU-6881 Solution Using SPI Interface

In the figure below, the system processor is an SPI master to the MPU-6881. Pins 2, 3, 4, and 5 are used to support the SCLK, SDI, SDO, and CS signals for SPI communications.




Figure 7 MPU-6881 Solution Using SPI Interface

4.9 Self-Test

Please refer to the register map document for more details on self-test.

Self-test allows for the testing of the mechanical and electrical portions of the sensors. The self-test for each measurement axis can be activated by means of the gyroscope and accelerometer self-test registers (registers 13 to 16).

When the self-test is activated, the electronics cause the sensors to be actuated and produce an output signal. The output signal is used to observe the self-test response.

The self-test response is defined as follows:

Self-test response = Sensor output with self-test enabled – Sensor output without self-test enabled

The self-test response for each gyroscope axis is defined in the gyroscope specification table, while that for each accelerometer axis is defined in the accelerometer specification table.

When the value of the self-test response is within the specified min/max limits of the product specification, the part has passed self-test. When the self-test response exceeds the min/max values, the part is deemed to have failed self-test. It is recommended to use InvenSense MotionApps software for executing self-test.



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

4.10 Clocking

The MPU-6881 has a flexible clocking scheme, allowing a variety of internal clock sources to be used for the internal synchronous circuitry. This synchronous circuitry includes the signal conditioning and ADCs, and various control circuits and registers. An on-chip PLL provides flexibility in the allowable inputs for generating this clock.

Allowable internal sources for generating the internal clock are:

- An internal relaxation oscillator
- Any of the X, Y, or Z gyros (MEMS oscillators with a variation of ±1% over temperature)

Selection of the source for generating the internal synchronous clock depends on the requirements for power consumption and clock accuracy. These requirements will most likely vary by mode of operation.

There are also start-up conditions to consider. When the MPU-6881 first starts up, the device uses its internal clock until programmed to operate from another source. This allows the user, for example, to wait for the MEMS oscillators to stabilize before they are selected as the clock source.

4.11 Sensor Data Registers

The sensor data registers contain the latest gyro, accelerometer, auxiliary sensor, and temperature measurement data. They are read-only registers, and are accessed via the serial interface. Data from these registers may be read anytime.

4.12 FIFO

The MPU-6881 contains a 4096-byte FIFO register that is accessible via the Serial Interface. The FIFO configuration register determines which data is written into the FIFO. Possible choices include gyro data, accelerometer data, temperature readings, auxiliary sensor readings, and SYNC input. A FIFO counter keeps track of how many bytes of valid data are contained in the FIFO. The FIFO register supports burst reads. The interrupt function may be used to determine when new data is available.

For further information regarding the FIFO, please refer to the MPU-6881 Register Map and Register Descriptions document.

4.13 Interrupts

Interrupt functionality is configured via the Interrupt Configuration register. Items that are configurable include the INT pin configuration, the interrupt latching and clearing method, and triggers for the interrupt. Items that can trigger an interrupt are (1) Clock generator locked to new reference oscillator (used when switching clock sources); (2) new data is available to be read (from the FIFO and Data registers); (3) accelerometer event interrupts; and (4) the MPU-6881 did not receive an acknowledge from an auxiliary sensor on the secondary I²C bus. The interrupt status can be read from the Interrupt Status register.

For further information regarding interrupts, please refer to the MPU-6881 Register Map and Register Descriptions document.

4.14 Digital-Output Temperature Sensor

An on-chip temperature sensor and ADC are used to measure the MPU-6881 die temperature. The readings from the ADC can be read from the FIFO or the Sensor Data registers.



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

4.15 Bias and LDOs

The bias and LDO section generates the internal supply and the reference voltages and currents required by the MPU-6881. Its two inputs are an unregulated VDD and a VDDIO logic reference supply voltage. The LDO output is bypassed by a capacitor at PLLFILT. For further details on the capacitor, please refer to the Bill of Materials for External Components.

4.16 Charge Pump

An on-chip charge pump generates the high voltage required for the MEMS oscillators.

4.17 Standard Power Modes

The following table lists the user-accessible power modes for MPU-6881.

Mode	Name	Gyro	Accel
1	Sleep Mode	Off	Off
2	Standby Mode	Drive On	Off
3	Low-Power Accelerometer Mode	Off	Duty-Cycled
4	Low-Noise Accelerometer Mode	Off	On
5	Gyroscope Mode	On	Off
6	6-Axis Mode	On	On

Table 12 Standard Power Modes for MPU-6881

Notes:

1. Power consumption for individual modes can be found in section 3.3.1.



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

5 Programmable Interrupts

The MPU-6881 has a programmable interrupt system which can generate an interrupt signal on the INT pin. Status flags indicate the source of an interrupt. Interrupt sources may be enabled and disabled individually.

Interrupt Name	Module
FIFO Overflow	FIFO
Data Ready	Sensor Registers
I ² C Master errors: Lost Arbitration, NACKs	I ² C Master
I ² C Slave 4	I ² C Master

Table 13 Table of Interrupt Sources

For information regarding the interrupt enable/disable registers and flag registers, please refer to the MPU-6881 Register Map and Register Descriptions document. Some interrupt sources are explained below.



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

6 Digital Interface

6.1 I2C and SPI Serial Interfaces

The internal registers and memory of the MPU-6881 can be accessed using either I²C at 400 kHz or SPI at 1MHz. SPI operates in four-wire mode.

Pin Number	Pin Name	Pin Description
8	VDDIO	Digital I/O supply voltage.
9	AD0 / SDO	I ² C Slave Address LSB (AD0); SPI serial data output (SDO)
23	SCL / SCLK	I ² C serial clock (SCL); SPI serial clock (SCLK)
24	SDA / SDI	I ² C serial data (SDA); SPI serial data input (SDI)

Table 14 Serial Interface

Note:

To prevent switching into I^2C mode when using SPI, the I^2C interface should be disabled by setting the $I2C_IF_DIS$ configuration bit. Setting this bit should be performed immediately after waiting for the time specified by the "Start-Up Time for Register Read/Write" in Section 6.3.

For further information regarding the *I2C_IF_DIS* bit, please refer to the MPU-6881 Register Map and Register Descriptions document.

6.2 I2C Interface

I²C is a two-wire interface comprised of the signals serial data (SDA) and serial clock (SCL). In general, the lines are open-drain and bi-directional. In a generalized I²C interface implementation, attached devices can be a master or a slave. The master device puts the slave address on the bus, and the slave device with the matching address acknowledges the master.

The MPU-6881 always operates as a slave device when communicating to the system processor, which thus acts as the master. SDA and SCL lines typically need pull-up resistors to VDD. The maximum bus speed is 400 kHz.

The slave address of the MPU-6881 is b110100X which is 7 bits long. The LSB bit of the 7 bit address is determined by the logic level on pin AD0. This allows two MPU-6881s to be connected to the same I²C bus. When used in this configuration, the address of the one of the devices should be b1101000 (pin AD0 is logic low) and the address of the other should be b1101001 (pin AD0 is logic high).

6.3 I2C Communications Protocol

START (S) and STOP (P) Conditions

Communication on the I²C bus starts when the master puts the START condition (S) on the bus, which is defined as a HIGH-to-LOW transition of the SDA line while SCL line is HIGH (see figure below). The bus is considered to be busy until the master puts a STOP condition (P) on the bus, which is defined as a LOW to HIGH transition on the SDA line while SCL is HIGH (see figure below).

Additionally, the bus remains busy if a repeated START (Sr) is generated instead of a STOP condition.



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014




Figure 8 START and STOP Conditions

Data Format / Acknowledge

I²C data bytes are defined to be 8-bits long. There is no restriction to the number of bytes transmitted per data transfer. Each byte transferred must be followed by an acknowledge (ACK) signal. The clock for the acknowledge signal is generated by the master, while the receiver generates the actual acknowledge signal by pulling down SDA and holding it low during the HIGH portion of the acknowledge clock pulse.

If a slave is busy and cannot transmit or receive another byte of data until some other task has been performed, it can hold SCL LOW, thus forcing the master into a wait state. Normal data transfer resumes when the slave is ready, and releases the clock line (refer to the following figure).




Figure 9 Acknowledge on the I²C Bus



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

Communications

After beginning communications with the START condition (S), the master sends a 7-bit slave address followed by an 8th bit, the read/write bit. The read/write bit indicates whether the master is receiving data from or is writing to the slave device. Then, the master releases the SDA line and waits for the acknowledge signal (ACK) from the slave device. Each byte transferred must be followed by an acknowledge bit. To acknowledge, the slave device pulls the SDA line LOW and keeps it LOW for the high period of the SCL line. Data transmission is always terminated by the master with a STOP condition (P), thus freeing the communications line. However, the master can generate a repeated START condition (Sr), and address another slave without first generating a STOP condition (P). A LOW to HIGH transition on the SDA line while SCL is HIGH defines the stop condition. All SDA changes should take place when SCL is low, with the exception of start and stop conditions.




Figure 10 Complete I²C Data Transfer

To write the internal MPU-6881 registers, the master transmits the start condition (S), followed by the I²C address and the write bit (0). At the 9th clock cycle (when the clock is high), the MPU-6881 acknowledges the transfer. Then the master puts the register address (RA) on the bus. After the MPU-6881 acknowledges the reception of the register address, the master puts the register data onto the bus. This is followed by the ACK signal, and data transfer may be concluded by the stop condition (P). To write multiple bytes after the last ACK signal, the master can continue outputting data rather than transmitting a stop signal. In this case, the MPU-6881 automatically increments the register address and loads the data to the appropriate register. The following figures show single and two-byte write sequences.

Single-Byte Write Sequence

Master	S	AD+W		RA		DATA		Р
Slave			ACK		ACK		ACK	

Burst Write Sequence

Master	S	AD+W		RA		DATA		DATA		Р
Slave			ACK		ACK		ACK		ACK	



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

To read the internal MPU-6881 registers, the master sends a start condition, followed by the I²C address and a write bit, and then the register address that is going to be read. Upon receiving the ACK signal from the MPU-6881, the master transmits a start signal followed by the slave address and read bit. As a result, the MPU-6881 sends an ACK signal and the data. The communication ends with a not acknowledge (NACK) signal and a stop bit from master. The NACK condition is defined such that the SDA line remains high at the 9th clock cycle. The following figures show single and two-byte read sequences.

Single-Byte Read Sequence

N	laster	S	AD+W		RA		S	AD+R			NACK	Р
S	Slave			ACK		ACK			ACK	DATA		

Burst Read Sequence

Maste	r S	AD+W		RA		S	AD+R			ACK		NACK	Р
Slave			ACK		ACK			ACK	DATA		DATA		

6.4 I²C Terms

Signal	Description
S	Start Condition: SDA goes from high to low while SCL is high
AD	Slave I ² C address
W	Write bit (0)
R	Read bit (1)
ACK	Acknowledge: SDA line is low while the SCL line is high at the 9 th clock cycle
NACK	Not-Acknowledge: SDA line stays high at the 9 th clock cycle
RA	MPU-6881 internal register address
DATA	Transmit or received data
Р	Stop condition: SDA going from low to high while SCL is high

Table 15 I²C Terms



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

6.5 SPI Interface

SPI is a 4-wire synchronous serial interface that uses two control lines and two data lines. The MPU-6881 always operates as a Slave device during standard Master-Slave SPI operation.

With respect to the Master, the Serial Clock output (SCLK), the Serial Data Output (SDO) and the Serial Data Input (SDI) are shared among the Slave devices. Each SPI slave device requires its own Chip Select (CS) line from the master.

CS goes low (active) at the start of transmission and goes back high (inactive) at the end. Only one CS line is active at a time, ensuring that only one slave is selected at any given time. The CS lines of the non-selected slave devices are held high, causing their SDO lines to remain in a high-impedance (high-z) state so that they do not interfere with any active devices.

SPI Operational Features

- 1. Data is delivered MSB first and LSB last
- 2. Data is latched on the rising edge of SCLK
- 3. Data should be transitioned on the falling edge of SCLK
- 4. The maximum frequency of SCLK is 1MHz
- 5. SPI read and write operations are completed in 16 or more clock cycles (two or more bytes). The first byte contains the SPI Address, and the following byte(s) contain(s) the SPI data. The first bit of the first byte contains the Read/Write bit and indicates the Read (1) or Write (0) operation. The following 7 bits contain the Register Address. In cases of multiple-byte Read/Writes, data is two or more bytes:

SPI Address format

MSB							LSB
R/W	A6	A5	A4	A3	A2	A1	A0

SPI Data format

MSB							LSB
D7	D6	D5	D4	D3	D2	D1	D0

6. Supports Single or Burst Read/Writes.




Figure 11 Typical SPI Master / Slave Configuration



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

7 Serial Interface Considerations

7.1 MPU-6881 Supported Interfaces

The MPU-6881 supports I²C communications on its serial interface.

The MPU-6881's I/O logic levels are set to be VDDIO.

The figure below depicts a sample circuit of MPU-6881. It shows the relevant logic levels and voltage connections.




Figure 12 I/O Levels and Connections



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

8 Assembly

This section provides general guidelines for assembling InvenSense Micro Electro-Mechanical Systems (MEMS) gyros packaged in QFN package.

8.1 Orientation of Axes

The diagram below shows the orientation of the axes of sensitivity and the polarity of rotation. Note the pin 1 identifier (•) in the figure.




Figure 13 Orientation of Axes Sensitivity and Polarity of Rotation




Document Number: PS-MPU-6881A-00

Revision: 1.0 Release Date: 05/22/2014

8.2 **Package Dimensions**

24 Lead QFN (3x3x0.9) mm NiPdAu Lead-frame finish



		DIMEN	ISIONS IN MILLIN	/IETERS
SYMBOLS	DESCRIPTION	MIN	NOM	MAX
Α	Package thickness	0.85	0.90	0.95
A1	Lead finger (pad) seating height	0.00	0.02	0.05
b	Lead finger (pad) width	0.15	0.20	0.25
С	Lead frame (pad) height		0.20 REF	
D	Package width	2.90	3.00	3.10
D2	Exposed pad width	1.65	1.70	1.75
E	Package length	2.90	3.00	3.10
E2	Exposed pad length	1.49	1.54	1.59
е	Lead finger-finger (pad-pad) pitch		0.40	
f (e-b)	Lead-lead (Pad-Pad) space	0.15	0.20	0.25
K	Lead (pad) to Exposed Pad Space		0.35 REF	
L	Lead (pad) length	0.25	0.30	0.35
R	Lead (pad) corner radius	0.075	REF	
R'	Corner lead (pad) outer radius	0.10	0.11	0.12
R"	Corner lead (pad) inner radius	0.10	0.11	0.12
s	Corner lead-lead (pad-pad) spacing		0.25 REF	
h	Corner lead dimension		0.22	
w	Corner lead dimension		0.12	
у	Lead Conformality	0.00		0.075



Document Number: PS-MPU-6881A-00

Revision: 1.0 Release Date: 05/22/2014

Part Number Package Marking

The part number package marking for MPU-6881 devices is summarized below:

Part Number	Part Number Package Marking			
MPU-6881	MP688			



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

10 Reliability

10.1 Qualification Test Policy

InvenSense's products complete a Qualification Test Plan before being released to production. The Qualification Test Plan for the MPU-6881 followed the JESD47I Standards, "Stress-Test-Driven Qualification of Integrated Circuits," with the individual tests described below.

10.2 Qualification Test Plan

Accelerated Life Tests

TEST	Method/Condition	Lot Quantity	Sample / Lot	Acc / Reject Criteria
(HTOL/LFR) High Temperature Operating Life	JEDEC JESD22-A108D, Dynamic, 3.63V biased, Tj>125°C [read-points 168, 500, 1000 hours]	3	77	(0/1)
(HAST) Highly Accelerated Stress Test (1)	JEDEC JESD22-A118A Condition A, 130°C, 85%RH, 33.3 psia., unbiased, [read-point 96 hours]	3	77	(0/1)
(HTS) High Temperature Storage Life	JEDEC JESD22-A103D, Cond. A, 125°C Non-Bias Bake [read-points 168, 500, 1000 hours]	3	77	(0/1)

Device Component Level Tests

TEST	Method/Condition	Lot Quantity	Sample / Lot	Acc / Reject Criteria
(ESD-HBM) ESD-Human Body Model	JEDEC JS-001-2012, (2.0 KV)	1	3	(0/1)
(ESD-MM) ESD-Machine Model	JEDEC JESD22-A115C, (250V)	1	3	(0/1)
(LU) Latch Up	JEDEC JESD-78D Class II (2), 125°C; ±100mA	1	6	(0/1)
(MS) Mechanical Shock	JEDEC JESD22-B104C, Mil-Std-883, Method 2002.5, Cond. E, 10,000g's, 0.2ms, ±X, Y, Z – 6 directions, 5 times/direction	3	5	(0/1)
(VIB) Vibration	JEDEC JESD22-B103B, Variable Frequency (random), Cond. B, 5-500Hz, X, Y, Z – 4 times/direction	3	5	(0/1)
Temperature Cycling (TC) (1)	JEDEC JESD22-A104D Condition G, [-40°C to +125°C], Soak Mode 2 [5'], 850 cycles	3	77	(0/1)

(1) Tests are preceded by MSL3 Preconditioning in accordance with JEDEC JESD22-A113F



Document Number: PS-MPU-6881A-00

Revision: 1.0

Release Date: 05/22/2014

11 Reference

Please refer to "InvenSense MEMS Handling Application Note (AN-IVS-0002A-00)" for the following information:

- Manufacturing Recommendations
 - o Assembly Guidelines and Recommendations
 - o PCB Design Guidelines and Recommendations
 - MEMS Handling Instructions
 - ESD Considerations
 - Reflow Specification
 - Storage Specifications
 - Package Marking Specification
 - o Tape & Reel Specification
 - o Reel & Pizza Box Label
 - Packaging
 - Representative Shipping Carton Label
- Compliance
 - Environmental Compliance
 - DRC Compliance
 - o Compliance Declaration Disclaimer

This information furnished by InvenSense is believed to be accurate and reliable. However, no responsibility is assumed by InvenSense for its use, or for any infringements of patents or other rights of third parties that may result from its use. Specifications are subject to change without notice. InvenSense reserves the right to make changes to this product, including its circuits and software, in order to improve its design and/or performance, without prior notice. InvenSense makes no warranties, neither expressed nor implied, regarding the information and specifications contained in this document. InvenSense assumes no responsibility for any claims or damages arising from information contained in this document, or from the use of products and services detailed therein. This includes, but is not limited to, claims or damages based on the infringement of patents, copyrights, mask work and/or other intellectual property rights.

Certain intellectual property owned by InvenSense and described in this document is patent protected. No license is granted by implication or otherwise under any patent or patent rights of InvenSense. This publication supersedes and replaces all information previously supplied. Trademarks that are registered trademarks are the property of their respective companies. InvenSense sensors should not be used or sold in the development, storage, production or utilization of any conventional or mass-destructive weapons or for any other weapons or life threatening applications, as well as in any other life critical applications such as medical equipment, transportation, aerospace and nuclear instruments, undersea equipment, power plant equipment, disaster prevention and crime prevention equipment.

©2014 InvenSense, Inc. All rights reserved. InvenSense, MotionTracking, MotionProcessing, MotionProcessor, MotionFusion, MotionApps, DMP, AAR, and the InvenSense logo are trademarks of InvenSense, Inc. Other company and product names may be trademarks of the respective companies with which they are associated.

©2014 InvenSense, Inc. All rights reserved.

