



Search within category GO

BUY NOW

DESIGN / INSTALL



FTD80-13-TL

Polypropylene insulated ferrules twin wire blue DIN color end sleeve, 14 AWG (2.5mm²), 0.51(13.0mm) pin length.

Specs	Packaging Details	Tools	Documents
Color	Blue		
Pin Length In. (mm)	0.51 (13)		
Style	Twin Wire		
Barrel Type	Seamless		
Base Material	Copper		
Insulation	Polypropylene		
Panduit Color Code	Blue		
Plating Type	Tinned		
Part Number Series	FTD		
Length In (mm)	0.85 (21.5)		
Max. Insulation Diameter In. (mm)	0.15 (3.7)		
Wire Strip Length In. (mm)	23/32 - (16.2mm)		
Flammability Rating	HB		
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)		
Tool	CT-1002, CT-1003, CT-1090, CT-1123, CT-1160, CT-1170, CT-2300/ST with CD-090, CT-2500/L with CT-2523CH		
CSA Certified	C22.2 No. 291-14		
Standards	DIN 46228 color code, UL 486F Listed, CSA		
Packaging Type	Bag		
Inside Diameter (In.)	0.11		
Inside Diameter (mm)	2.9		
Part Features	Twin Wire Polypropylene insulation housing conforms to DIN color requirements Meets DIN, UL and CSA standards for single wire containment Funnel entry for faster insertion and lower installed cost Designed with a seamless barrel to contain loose wire strands for superior terminations Eases insertion of wire into terminal block Suitable for limited space panel applications Multiple pin lengths available for a variety of terminal blocks		
Wire Range	14 AWG		
RoHS Compliancy Status	Compliant		
Min. Order Qty.	250		

★ Add to Favorites Add to BOM