

## DSUB SV MA TSDC 09P AU3



Image is for illustration purposes only. Please refer to product description.

Part number	09 67 009 5604
Specification	DSUB SV MA TSDC 09P AU3
HARTING eCatalogue	<a href="https://b2b.harting.com/09670095604">https://b2b.harting.com/09670095604</a>

### Identification

Category	Connectors
Series	D-Sub
Identification	Standard
Element	Connector
Description of the contact	Turned Straight

### Version

Termination method	Solder cup termination
Gender	Male
Locking type	Fixing flange with feed through hole $\varnothing$ 3.1 mm
Size	D-Sub 1
Connection type	PCB to cable Cable to cable
Number of contacts	9
Performance level	3
Pack contents	Carton

### Technical characteristics

Conductor cross-section	0.5 mm <sup>2</sup> max.
Distance between rows	2.54 mm
Rated current	7.5 A
Clearance distance	$\geq$ 1 mm
Creepage distance	$\geq$ 1 mm

Page 1 / 3 | Creation date 2020-10-08 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany  
Phone +49 5772 47-97200 | [electronics@HARTING.com](mailto:electronics@HARTING.com) | [www.HARTING.com](http://www.HARTING.com)



Pushing Performance

## Technical characteristics

Insulation resistance	>10 <sup>10</sup> Ω
Contact resistance	≤10 mΩ
Limiting temperature	-55 ... +125 °C (Soldering iron temperature during soldering: max. 350 °C for 3-5 s)
Insertion force	≤30 N
Mating cycles	≥50
Test voltage U <sub>r.m.s.</sub>	1 kV
Isolation group	IIIa (175 ≤ CTI < 400)
Hot plugging	No

## Material properties

Material (insert)	Thermoplastic resin, glass-fibre filled (PBTP) Plated steel
Colour (insert)	White
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated Termination side Gold plated Mating side
Material (hood/housing)	Steel
Surface (hood/housing)	Tin plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

Specifications	DIN 41652
UL / CSA	UL 1977 ECBT2.E102079

## Commercial data

Packaging size	100
----------------	-----



Pushing Performance

## Commercial data

Net weight	5.2 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440214 D-Sub coupler