


Features

- Low forward voltage drop
- Low leakage current
- Moisture sensitivity: level 1, per J-STD-020
- Ideal for automated placement
- Meets environmental standard MIL-S-19500D
- Solder dip 275 °C, 10s



Package: DO-214AB (SMC)

Applications

For use in general purpose rectification of lighting, power supply, inverter, converter and freewheeling diodes for consumer, automotive and telecommunication.

Maximum Ratings (T_A = 25°C unless otherwise noted)

Parameter	Symbol	SL32C	SL33C	SL34C	SL35C	SL36C	SL37C	SL38C	SL39C	SL310C	Unit
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	20	30	40	50	60	70	80	90	100	V
Maximum RMS Voltage	V _{RMS}	14	21	28	35	42	49	56	63	70	V
Maximum DC Blocking Voltage	V _{DC}	20	30	40	50	60	70	80	90	100	V
Maximum Average Forward Rectified current at T _L (See Fig.1)	I _{F(AV)}	3									A
Peak Forward Surge Current (8.3 ms single half sine-wave superimposed on rated load)	I _{FSM}	80									A
Operating Junction Temperature Range	T _J	- 55 to + 125				- 55 to + 150					°C
Storage Temperature Range	T _{stg}	- 55 to + 150									°C

Electrical Characteristics (T_A = 25°C unless otherwise noted)

Parameter	Test Conditions	Symbol	SL32C	SL33C	SL34C	SL35C	SL36C	SL37C	SL38C	SL39C	SL310C	Unit
Maximum Instantaneous Forward Voltage	I _F =3 A	V _F	0.42			0.50		0.75				V
Maximum DC Reverse Current at Rated DC Blocking Voltage	T _A =25°C	I _R	0.2				0.05					mA
	T _A =100°C		50				4					
Typical Junction Capacitance	4.0 V, 1 MHz	C _J	220									pF

Thermal Characteristics

Parameter	Symbol	SL32C	SL33C	SL34C	SL35C	SL36C	SL37C	SL38C	SL39C	SL310C	Unit	
Maximum Thermal Resistance	R _{θJA} (1)	52					75					°C/W
	R _{θJT} (2)	17					25					

- Notes: (1) Thermal resistance from junction to ambient, 0.315 × 0.315"(8.0 × 8.0mm)copper pads to each terminal
 (2) Thermal resistance from junction to terminal, 0.315 × 0.315"(8.0 × 8.0mm)copper pads to each terminal

Ratings and Characteristics Curves

($T_A = 25^\circ\text{C}$ unless otherwise noted)




Figure 1. Forward Current Derating Curve




Figure 2. Maximum Non-repetitive Peak Forward Surge Current




Figure 3. Typical Instantaneous Forward Characteristics




Figure 4. Typical Reverse Characteristics




Figure 5. Typical Junction Capacitance


SL32C thru SL310C

Surface Mount Schottky Rectifier
 Reverse Voltage 20-100V Forward Current 3A

Package Outline Dimensions

in inches (millimeters)

DO-214AB (SMC)



Mounting Pad Layout

