


# **RV-4162-C7** Real Time Clock Module with I<sup>2</sup>C-Bus





### APPLICATIONS

IoT Metering Industrial Automotive Health Care Wearables, Portables

### DESCRIPTION


The RV-4162-C7 is a SMT Real-Time Clock Module that incorporates an integrated CMOS circuit together with an XTAL. It operates under vacuum in a hermetically sealed ceramic package with metal lid.

### FEATURES

Low power consumption: 350 nA @ 3 V. Operating voltage range: 1.0 V to 4.4 V. Time accuracy: ±20 ppm @ 25°C. Operating temperature range: -40 to +85°C. User programmable offset value. Oscillator stop detection. Provides year, month, date, weekday, hours, minutes, seconds, 100th. Automatic leap year calculation and century bits. Alarm and Watchdog functions. Clock output frequencies: 32.768 kHz to 1 Hz. I<sup>2</sup>C-bus interface: 400 kHz.

100% Pb-free, RoHS-compliant.

Automotive qualification according to AEC-Q200 available.



## **BLOCK DIAGRAM**

### **ELECTRICAL CHARACTERISTICS** AT 25°C

More detailed information can be found in the Application Manual.

	Symbol	Condition	Min.	Тур.	Мах	Unit	
Supply voltage	V <sub>DD</sub>	I <sup>2</sup> C-bus active	1.3		4.4	V	
Supply voltage	V <sub>DD</sub>	Time keeping 1.0			4.4	V	
Current consumption Time keeping mode	I <sub>DDO</sub>	$I^2$ C-bus inactive, $V_{DD}$ = 3 V		350	500	nA	
CLKOUT frequency	F <sub>CLKOUT</sub>	Programmable	32768 to 1		Hz		
Frequency tolerance	$\Delta F/F$	@ 25°C	±20 <sup>1)</sup>		ppm		
Aging first year max.	$\Delta F/F$	@ 25°C	±3			ppm	
1) Tighter frequency tolerances on request.							

1) Tighter frequency tolerances on request.

## **ENVIRONMENTAL CHARACTERISTICS**

**TERMINATIONS AND** 


**CHARACTERISTICS** 

**FREQUENCY TEMPERATURE** 

PROCESSING


		Conditions	Max. Dev.
Storage temp. range		–55 to +125°C	
TA Operating temperature range		–40 to +85°C	
Shock resistance	$\Delta F/F$	5000 g, 0.3 ms, ½ sine	±5 ppm
Vibration resistance	$\Delta F/F$	20 g / 10–2000 Hz	±5 ppm


Package	Termination	Processing	
SON-8	Au flashed pads	IPC/JEDEC J-STD-020C 260°C / 20 - 40 s	



**PIN CONNECTIONS TOP VIEW** 

**ORDERING INFORMATION** 





All specifications subject to change without notice.

Micro Crystal AG Muehlestrasse 14 CH-2540 Grenchen Switzerland

Phone +41 32 655 82 82 +41 32 655 82 83 Fax sales@microcrystal.com www.microcrystal.com



## **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Micro Crystal:

 RV-4162-C7-32.768kHz-20PPM-TA-QC
 RV-4162-C7-32.768k-20PPM-TA-QA
 RV-4162-C7-32.768KHZ-10PPM-TA-QA

 QC
 RV-4162-C7-EVALUATION-BOARD
 RV-4162-C7-32.768kHZ-10PPM-TA-QA
 RV-4162-C7-32.768KHZ-10PPM-TA-QA