


**PCJ**Chip Type, Low ESR,  
Higher Capacitance

- Low ESR, Higher Capacitance, High ripple current.
- Load life of 2000 hours at 105°C.
- SMD type : Lead free reflow soldering condition at 260°C peak correspondence.
- Compliant to the RoHS directive (2011/65/EU,(EU)2015/863).
- AEC-Q200 compliant. Please contact us for details.



**■ Specifications**

| Item   | Performance Characteristics  |   |                    |  |       |   |          |   |                      |   |
|--|--|---|--------------------|--|-------|---|----------|---|----------------------|---|
| Category Temperature Range                           | -55 to +105°C  |   |                    |  |       |   |          |   |                      |   |
| Rated Voltage Range                                  | 2.5 to 16V   |   |                    |  |       |   |          |   |                      |   |
| Rated Capacitance Range                              | 33 to 2700μF   |   |                    |  |       |   |          |   |                      |   |
| Capacitance Tolerance                                | ±20% at 120Hz, 20°C  |   |                    |  |       |   |          |   |                      |   |
| Tangent of loss angle (tan δ)                        | Less than or equal to the specified value at 120Hz, 20°C   |   |                    |  |       |   |          |   |                      |   |
| ESR (※1)   | Less than or equal to the specified value at 100kHz, 20°C  |   |                    |  |       |   |          |   |                      |   |
| Leakage Current (※2)                                 | Less than or equal to the specified value . After 2 minutes' application of rated voltage at 20°C  |   |                    |  |       |   |          |   |                      |   |
| Temperature Characteristics<br>(Max.Impedance Ratio) | Z(+105°C) / Z(+20°C) ≤ 1.25 (100kHz)<br>Z(-55°C) / Z(+20°C) ≤ 1.25   |   |                    |  |       |   |          |   |                      |   |
| Endurance  | The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 105°C.   | <table border="1"> <tr> <td>Capacitance change</td><td>Within ± 20% of the initial capacitance value (※3)</td></tr> <tr> <td>tan δ</td><td>150% or less than the initial specified value</td></tr> <tr> <td>ESR (※1)</td><td>150% or less than the initial specified value</td></tr> <tr> <td>Leakage current (※2)</td><td>Less than or equal to the initial specified value</td></tr> </table> | Capacitance change | Within ± 20% of the initial capacitance value (※3) | tan δ | 150% or less than the initial specified value | ESR (※1) | 150% or less than the initial specified value | Leakage current (※2) | Less than or equal to the initial specified value |
| Capacitance change                                   | Within ± 20% of the initial capacitance value (※3)   |   |                    |  |       |   |          |   |                      |   |
| tan δ  | 150% or less than the initial specified value  |   |                    |  |       |   |          |   |                      |   |
| ESR (※1)   | 150% or less than the initial specified value  |   |                    |  |       |   |          |   |                      |   |
| Leakage current (※2)                                 | Less than or equal to the initial specified value  |   |                    |  |       |   |          |   |                      |   |
| Damp Heat<br>(Steady State)                          | The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 1000 hours at 60°C, 90% RH.  | <table border="1"> <tr> <td>Capacitance change</td><td>Within ± 20% of the initial capacitance value (※3)</td></tr> <tr> <td>tan δ</td><td>150% or less than the initial specified value</td></tr> <tr> <td>ESR (※1)</td><td>150% or less than the initial specified value</td></tr> <tr> <td>Leakage current (※2)</td><td>Less than or equal to the initial specified value</td></tr> </table> | Capacitance change | Within ± 20% of the initial capacitance value (※3) | tan δ | 150% or less than the initial specified value | ESR (※1) | 150% or less than the initial specified value | Leakage current (※2) | Less than or equal to the initial specified value |
| Capacitance change                                   | Within ± 20% of the initial capacitance value (※3)   |   |                    |  |       |   |          |   |                      |   |
| tan δ  | 150% or less than the initial specified value  |   |                    |  |       |   |          |   |                      |   |
| ESR (※1)   | 150% or less than the initial specified value  |   |                    |  |       |   |          |   |                      |   |
| Leakage current (※2)                                 | Less than or equal to the initial specified value  |   |                    |  |       |   |          |   |                      |   |
| Resistance to<br>Soldering Heat                      | After soldering the capacitor under the soldering conditions prescribed here, the capacitor shall meet the specifications listed at right.<br>Pre-heating shall be done at 150 to 200°C and for 60 to 180 sec. The duration for over +230°C temperature at capacitor surface shall not exceed 60 seconds.<br>In case peak temperature is 250°C or less, reflow soldering shall be two times maximum.<br>In case peak temperature is 260°C or less, reflow soldering shall be once.<br>Measurement for solder temperature profile shall be made at the capacitor top. | <table border="1"> <tr> <td>Capacitance change</td><td>Within ± 10% of the initial capacitance value (※3)</td></tr> <tr> <td>tan δ</td><td>130% or less than the initial specified value</td></tr> <tr> <td>ESR (※1)</td><td>130% or less than the initial specified value</td></tr> <tr> <td>Leakage current (※2)</td><td>Less than or equal to the initial specified value</td></tr> </table> | Capacitance change | Within ± 10% of the initial capacitance value (※3) | tan δ | 130% or less than the initial specified value | ESR (※1) | 130% or less than the initial specified value | Leakage current (※2) | Less than or equal to the initial specified value |
| Capacitance change                                   | Within ± 10% of the initial capacitance value (※3)   |   |                    |  |       |   |          |   |                      |   |
| tan δ  | 130% or less than the initial specified value  |   |                    |  |       |   |          |   |                      |   |
| ESR (※1)   | 130% or less than the initial specified value  |   |                    |  |       |   |          |   |                      |   |
| Leakage current (※2)                                 | Less than or equal to the initial specified value  |   |                    |  |       |   |          |   |                      |   |
| Marking  | Navy blue print on the case top  |   |                    |  |       |   |          |   |                      |   |

※1 ESR should be measured at both of the terminal ends closest where the terminals protrude through the plastic platform.

※2 Conditioning : If any doubt arises, measure the leakage current after the voltage treatment of applying DC rated voltage continuously to the capacitor for 120 minutes at 105°C.

※3 Initial value : The value before test of examination of resistance to soldering.

**■ Dimensions****Type numbering system (Example : 6.3V 220μF)**

| Size | φ5 × 6L    | φ6.3 × 6L  | φ6.3 × 8L  | φ8 × 7L    | φ8 × 8L    | φ8 × 10L   | φ8 × 12L   | φ10 × 8L   | φ10 × 10L  | φ10 × 12.7L | (mm) |
|------|------------|------------|------------|------------|------------|------------|------------|------------|------------|-------------|------|
| φD   | 5.0        | 6.3        | 6.3        | 8.0        | 8.0        | 8.0        | 8.0        | 10.0       | 10.0       | 10.0        |      |
| L    | 5.9        | 5.9        | 7.9        | 6.9        | 7.9        | 9.9        | 11.9       | 7.9        | 9.9        | 12.6        |      |
| A    | 6.0        | 7.3        | 7.3        | 9.0        | 9.0        | 9.0        | 9.0        | 11.0       | 11.0       | 11.0        |      |
| B    | 5.3        | 6.6        | 6.6        | 8.3        | 8.3        | 8.3        | 8.3        | 10.3       | 10.3       | 10.3        |      |
| C    | 5.3        | 6.6        | 6.6        | 8.3        | 8.3        | 8.3        | 8.3        | 10.3       | 10.3       | 10.3        |      |
| E    | 1.6        | 2.1        | 2.1        | 3.2        | 3.2        | 3.2        | 3.2        | 4.6        | 4.6        | 4.6         |      |
| H    | 0.5 to 0.8 | 0.5 to 0.8 | 0.5 to 0.8 | 0.8 to 1.1  |      |

**Voltage**

| V    | 2.5 | 4 | 6.3 | 10 | 16 |
|------|-----|---|-----|----|----|
| Code | e   | g | j   | A  | C  |

**Frequency coefficient of rated ripple current**

| Frequency   | 120Hz | 1kHz | 10kHz | 100kHz or more |
|-------------|-------|------|-------|----------------|
| Coefficient | 0.05  | 0.30 | 0.70  | 1.00           |

● Dimension table in next page.

CAT.8100L

## PCJ

### Dimensions

| Rated Voltage<br>(V)<br>(code) | Surge Voltage<br>(V) | Rated Capacitance<br>( $\mu$ F) | Case Size<br>$\phi D \times L$ (mm) | $\tan \delta$ | Leakage Current<br>( $\mu$ A)<br>(at 20°C after<br>2 minutes) | ESR<br>(m $\Omega$ )<br>(20°C/100kHz) | Rated Ripple<br>(mArms)<br>(105°C/100kHz) | Part Number    |
|--------------------------------|----------------------|---------------------------------|-------------------------------------|---------------|---|---------------------------------------|---|----------------|
| 2.5<br>(0E)                    | 2.8                  | 180                             | 5 × 6                               | 0.12          | 90  | 21                                    | 2670                                      | PCJ0E181MCL1GS |
|                                |                      | 390                             | 6.3 × 6                             | 0.12          | 195   | 15                                    | 3400                                      | PCJ0E391MCL1GS |
|                                |                      | 470                             | 6.3 × 8                             | 0.12          | 235   | 13                                    | 3600                                      | PCJ0E471MCL1GS |
|                                |                      | 560                             | ■ 6.3 × 8                           | 0.12          | 280   | 13                                    | 3600                                      | PCJ0E561MCL4GS |
|                                |                      | 560                             | 8 × 7                               | 0.12          | 280   | 13                                    | 4100                                      | PCJ0E561MCL1GS |
|                                |                      | 680                             | 8 × 7                               | 0.12          | 340   | 13                                    | 4100                                      | PCJ0E681MCL1GS |
|                                |                      | 820                             | ▲ 8 × 8                             | 0.12          | 410   | 12                                    | 4260                                      | PCJ0E821MCL6GS |
|                                |                      | 820                             | 8 × 12                              | 0.12          | 410   | 9                                     | 5400                                      | PCJ0E821MCL1GS |
|                                |                      | 1000                            | 8 × 8                               | 0.12          | 500   | 12                                    | 4260                                      | PCJ0E102MCL1GS |
|                                |                      | 1200                            | 10 × 8                              | 0.12          | 600   | 13                                    | 4800                                      | PCJ0E122MCL1GS |
|                                |                      | 1500                            | ▲ 8 × 10                            | 0.12          | 750   | 10                                    | 5220                                      | PCJ0E152MCL6GS |
|                                |                      | 1500                            | 8 × 12                              | 0.12          | 750   | 9                                     | 5400                                      | PCJ0E152MCL1GS |
|                                |                      | 2200                            | 10 × 10                             | 0.12          | 1100  | 10                                    | 5500                                      | PCJ0E222MCL1GS |
|                                |                      | 2700                            | 10 × 12.7                           | 0.12          | 1350  | 9                                     | 5800                                      | PCJ0E272MCL1GS |
| 4<br>(0G)                      | 4.6                  | 100                             | 5 × 6                               | 0.12          | 80  | 22                                    | 2610                                      | PCJ0G101MCL1GS |
|                                |                      | 150                             | 5 × 6                               | 0.12          | 120   | 22                                    | 2610                                      | PCJ0G151MCL1GS |
|                                |                      | 270                             | 6.3 × 6                             | 0.12          | 216   | 15                                    | 3200                                      | PCJ0G271MCL1GS |
|                                |                      | 330                             | 6.3 × 6                             | 0.12          | 264   | 15                                    | 3300                                      | PCJ0G331MCL1GS |
|                                |                      | 390                             | 6.3 × 8                             | 0.12          | 312   | 14                                    | 3470                                      | PCJ0G391MCL1GS |
|                                |                      | 470                             | 8 × 7                               | 0.12          | 376   | 14                                    | 3950                                      | PCJ0G471MCL1GS |
|                                |                      | 560                             | 8 × 7                               | 0.12          | 448   | 14                                    | 4000                                      | PCJ0G561MCL1GS |
|                                |                      | 560                             | ● 8 × 12                            | 0.12          | 448   | 9                                     | 5200                                      | PCJ0G561MCL9GS |
|                                |                      | 680                             | 8 × 8                               | 0.12          | 544   | 13                                    | 3950                                      | PCJ0G681MCL1GS |
|                                |                      | 1000                            | ■ 8 × 10                            | 0.12          | 800   | 10                                    | 5220                                      | PCJ0G102MCL4GS |
|                                |                      | 1000                            | 10 × 8                              | 0.12          | 800   | 13                                    | 4300                                      | PCJ0G102MCL1GS |
|                                |                      | 1200                            | 8 × 12                              | 0.12          | 960   | 9                                     | 5400                                      | PCJ0G122MCL1GS |
|                                |                      | 1200                            | ▲ 10 × 10                           | 0.12          | 960   | 10                                    | 5500                                      | PCJ0G122MCL6GS |
|                                |                      | 1500                            | ■ 8 × 12                            | 0.12          | 1200  | 9                                     | 5200                                      | PCJ0G152MCL4GS |
|                                |                      | 1500                            | 10 × 10                             | 0.12          | 1200  | 10                                    | 5500                                      | PCJ0G152MCL1GS |
|                                |                      | 1800                            | 10 × 10                             | 0.12          | 1440  | 10                                    | 5500                                      | PCJ0G182MCL1GS |
|                                |                      | 1800                            | ● 10 × 12.7                         | 0.12          | 1440  | 9                                     | 5600                                      | PCJ0G182MCL9GS |
|                                |                      | 2200                            | 10 × 12.7                           | 0.12          | 1760  | 9                                     | 5700                                      | PCJ0G222MCL1GS |
| 6.3<br>(0J)                    | 7.2                  | 100                             | 5 × 6                               | 0.12          | 126   | 24                                    | 2500                                      | PCJ0J101MCL1GS |
|                                |                      | 120                             | 5 × 6                               | 0.12          | 151   | 24                                    | 2500                                      | PCJ0J121MCL1GS |
|                                |                      | 220                             | 6.3 × 6                             | 0.12          | 277   | 15                                    | 3200                                      | PCJ0J221MCL1GS |
|                                |                      | 270                             | 6.3 × 8                             | 0.12          | 340   | 14                                    | 3470                                      | PCJ0J271MCL1GS |
|                                |                      | 330                             | ■ 6.3 × 8                           | 0.12          | 416   | 14                                    | 3470                                      | PCJ0J331MCL4GS |
|                                |                      | 330                             | 8 × 7                               | 0.12          | 416   | 14                                    | 3950                                      | PCJ0J331MCL1GS |
|                                |                      | 390                             | 8 × 7                               | 0.12          | 491   | 14                                    | 3950                                      | PCJ0J391MCL1GS |
|                                |                      | 470                             | 8 × 8                               | 0.12          | 592   | 13                                    | 3950                                      | PCJ0J471MCL1GS |
|                                |                      | 820                             | ▲ 8 × 10                            | 0.12          | 1033  | 12                                    | 4770                                      | PCJ0J821MCL6GS |
|                                |                      | 820                             | ■ 8 × 12                            | 0.12          | 1033  | 10                                    | 5150                                      | PCJ0J821MCL4GS |
|                                |                      | 820                             | 10 × 8                              | 0.12          | 1033  | 13                                    | 4500                                      | PCJ0J821MCL1GS |
|                                |                      | 1200                            | 10 × 10                             | 0.12          | 1512  | 12                                    | 5025                                      | PCJ0J122MCL1GS |
|                                |                      | 1500                            | 10 × 10                             | 0.12          | 1890  | 12                                    | 5025                                      | PCJ0J152MCL1GS |
|                                |                      | 1500                            | ● 10 × 12.7                         | 0.12          | 1890  | 10                                    | 5500                                      | PCJ0J152MCL9GS |
|                                |                      | 1800                            | 10 × 12.7                           | 0.12          | 2268  | 11                                    | 5200                                      | PCJ0J182MCL1GS |
| 10<br>(1A)                     | 11.5                 | 47                              | 5 × 6                               | 0.12          | 94  | 28                                    | 2310                                      | PCJ1A470MCL1GS |
|                                |                      | 56                              | 5 × 6                               | 0.12          | 112   | 28                                    | 2310                                      | PCJ1A560MCL1GS |
|                                |                      | 68                              | 5 × 6                               | 0.12          | 136   | 28                                    | 2310                                      | PCJ1A680MCL1GS |
|                                |                      | 120                             | 6.3 × 6                             | 0.12          | 240   | 25                                    | 2530                                      | PCJ1A121MCL1GS |
|                                |                      | 150                             | 6.3 × 8                             | 0.12          | 300   | 21                                    | 2880                                      | PCJ1A151MCL1GS |
|                                |                      | 220                             | 8 × 7                               | 0.12          | 440   | 21                                    | 3220                                      | PCJ1A221MCL1GS |
|                                |                      | 270                             | 8 × 7                               | 0.12          | 540   | 21                                    | 3220                                      | PCJ1A271MCL1GS |
|                                |                      | 330                             | 8 × 8                               | 0.12          | 660   | 19                                    | 3390                                      | PCJ1A331MCL1GS |
|                                |                      | 390                             | 8 × 10                              | 0.12          | 780   | 17                                    | 4000                                      | PCJ1A391MCL1GS |
|                                |                      | 470                             | 10 × 8                              | 0.12          | 940   | 19                                    | 3800                                      | PCJ1A471MCL1GS |
|                                |                      | 680                             | 10 × 10                             | 0.12          | 1360  | 13                                    | 4820                                      | PCJ1A681MCL1GS |
|                                |                      | 33                              | 5 × 6                               | 0.12          | 105   | 35                                    | 2070                                      | PCJ1C330MCL1GS |
| 16<br>(1C)                     | 18.4                 | 39                              | 5 × 6                               | 0.12          | 125   | 35                                    | 2070                                      | PCJ1C390MCL1GS |
|                                |                      | 68                              | 6.3 × 6                             | 0.12          | 217   | 28                                    | 2390                                      | PCJ1C680MCL1GS |
|                                |                      | 82                              | 6.3 × 8                             | 0.12          | 262   | 24                                    | 2700                                      | PCJ1C820MCL1GS |
|                                |                      | 100                             | ■ 6.3 × 8                           | 0.12          | 320   | 24                                    | 2700                                      | PCJ1C101MCL4GS |
|                                |                      | 100                             | 8 × 7                               | 0.12          | 320   | 24                                    | 3010                                      | PCJ1C101MCL1GS |
|                                |                      | 120                             | 8 × 7                               | 0.12          | 384   | 24                                    | 3010                                      | PCJ1C121MCL1GS |
|                                |                      | 150                             | 8 × 8                               | 0.12          | 480   | 22                                    | 3150                                      | PCJ1C151MCL1GS |
|                                |                      | 180                             | 8 × 10                              | 0.12          | 576   | 18                                    | 3890                                      | PCJ1C181MCL1GS |
|                                |                      | 220                             | ■ 8 × 10                            | 0.12          | 704   | 18                                    | 3890                                      | PCJ1C221MCL4GS |
|                                |                      | 220                             | 10 × 8                              | 0.12          | 704   | 22                                    | 3450                                      | PCJ1C221MCL1GS |
|                                |                      | 270                             | 8 × 12                              | 0.12          | 864   | 16                                    | 4070                                      | PCJ1C271MCL1GS |
|                                |                      | 330                             | 10 × 10                             | 0.12          | 1056  | 16                                    | 4350                                      | PCJ1C331MCL1GS |

• For taping specifications, recommended land size/soldering by reflow and minimum order quantity, please refer to the Guidelines for Aluminum Electrolytic Capacitors.

No marked, [1] will be put at 12th digit of type numbering system.  
 ■: In this case, [4] will be put at 12th digit of type numbering system.  
 ▲: In this case, [6] will be put at 12th digit of type numbering system.  
 ●: In this case, [9] will be put at 12th digit of type numbering system.

CAT.8100L