



Model number


VAA-4E4A-KE-ZE/R

KE switch cabinet module 4 inputs (PNP) and 4 relay outputs


Features

- Housing with removable, mechanical and color coded terminals
- · Communication monitoring
- Inputs for 2- and 3-wire sensors
- Isolated relay output
- Addressing jack
- Selectable supply to the sensors: External or from the module
- Function display for bus, internal sensor supply, inputs, and outputs

Dimensions



Electrical connection




Indicating / Operating means




The plug connectors with dangerous contact voltage must not be connected or disconnected under power

ATTENTION

Do not connect the terminals I+, IN and I- with any external potential when switch set to "INT" $\,$





Technical data General specifications Standard slave Slave type AS-Interface specification V2.1 Required master specification ≥ V2.0 UL File Number E106378 Functional safety related parameters 300 a $MTTF_d$ Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means LED FAULT Fault display; Red LED red: Communication fault or address is 0 red, flashing: Overload, internal input supply LED INT Internal input supply active; LED green LED PWR AS-Interface voltage; LED green I FD IN switching state (input); 4 LED yellow LED OUT Switching state (output); 4 LED yellow **Electrical specifications** U_{EXT} 12 ... 30 V DC PELV Auxiliary voltage (input) U_e 26.5 ... 31.6 V from AS-Interface Rated operating voltage Rated operating current ≤ 35 mA (no sensors)/max. 210 mA l_e Surge protection O1 ... O4: Over voltage category II U_{EXT}, U_e: Over voltage category III, safe isolated power supplies (PELV) Input Number/Type 4 inputs for 2- or 3-wire sensors (PNP), DC Supply from AS-Interface (switch position INT, default settings) or external U_{EXT} (switch position EXT) 21 ... 31 V DC (INT) Voltage Current loading capacity ≤ 150 mA, overload- and short-circuit protected (INT) Input current ≤ 8 mA (limited internally) according to DIN EN 61131-2 (Type 2) Switching point 0 (unattenuated) \leq 2 mA 1 (attenuated) ≥ 4 mA Signal delay < 2 ms (input/AS-Interface) Output Number/Type 4 relay outputs, normally open Supply none Nominal load Per contact 2 A / 30 V DC (acc. UL max. 24 V DC); 2 A / 253 V AC Per module Control circuit < 8 mA per relay (from AS-Interface) Switching delay < 10 ms (AS-Interface/contact) Usage category DC-13 and AC-14 Switching 5×10^{6} Mechanical Electrical $0.2 \times 10^6 (250 \text{ V AC}, 2 \text{ A}, \cos \phi = 0.4)$ Galvanic isolation Input/Output safe isolation, rated insulation voltage 300 V AC Input/AS-Interface Switch position INT: None Switch position EXT: reinforced insulation, rated insulation voltage 66 V DC Output/Output basic insulation, rated insulation voltage 300 V AC Output/AS-Interface safe isolation, rated insulation voltage 300 V AC Directive conformity Electromagnetic compatibility Directive 2014/30/EU EN 62026-2:2013 EN 61326:2003 Low voltage Directive 73/23/EEC EN 60947-1:2007 Standard conformity EN 60664-1:2007 Galvanic isolation Electromagnetic compatibility NAMUR NE 21: 1998-08 Degree of protection EN 60529:2000 FN 62026-2:2013 Fieldbus standard AS-Interface EN 62026-2:2013 **Programming instructions** Profile S-7.0 IO code 7 ID code 0 ID1 code ID2 code Е Data bits (function via AS-Interface) input output D0 IN1 01 IN2 02 D₁ D2 IN3 О3

Function

The VAA-4E4A-KE-ZE/R AS-Interface I/O module is a cabinet module with 4 inputs and 4 relay outputs. The only 22.5 mm width housing requires not much space in the switch cabinet. The module is installed by snapping on the 35 mm DIN Rail in accordance with EN 50022.

The connection is made through plug-in terminals. For the inputs and outputs 4-way-terminal blocks (inputs black, outputs red) are used. The connection of the AS-Interface is made via a 2-way-terminal block (yellow). In order to avoid exchanges, the terminals for inputs and outputs as well as AS-Interface are coded mechanically.

The power supply of the inputs and the connected sensors can be made as required via the internal supply of the module (AS-Interface) or via an external voltage source. The switching is carried out by means of a switch that is positioned at the side of the module. The selection of the internal input supply is indicated via the LED INT. The current switching state of each input and output is indicated by the resp. LED IN and OUT.

The device is equipped with a communication monitoring, which switches the outputs to their de-energized state, when there is no AS-Interface communication with the module for more than 40 ms.

An overloading of the internal input supply will be reported via the function 'peripheral error' to the AS-Interface master. The communication via the AS-Interface remains intact.

Accessories

VBP-HH1-V3.0-KIT

AS-Interface Handheld with accessory

VBP-HH1-V3.0

AS-Interface Handheld

VAZ-PK-1,5M-V1-G

Adapter cable module/hand-held programming device

124422_eng.xml

PEPPERL+FUCHS

D3	IN4	O4			
Parameter bits (programmable via AS-i)	function				
P0	not used				
P1	not used				
P2	not used				
P3	not used				
Ambient conditions					
Ambient temperature	-25 60 °C (-13 140 °F)				
Storage temperature	-25 85 °C (-13 185 °F)				
Relative humidity	85 % , noncondensing				
Climatic conditions	For indoor use only				
Altitude	≤ 2000 m above MSL				
Pollution degree	2				
Mechanical specifications					
Degree of protection	IP20				
Connection	removable terminals rated connection capacity: rigid/flexible (with and without wire-end ferrules): 0.25 mm² 2.5 mm² for multiple-wire connection with two wires of equal cross-section: flexible with twin wire-end ferrules: 0.5 mm² 1.5 mm²				
Material					
Housing	PA 66-FR				
Mass	170 g				
Mounting	DIN mounting rail				
Tightening torque of clamping screws	0.5 Nm 0.6 Nm				

Notes

Installation, commissioning, maintenance:

The device has to be installed into a separate electrical operation facility with access only for electrical professionals or instructed persons.

Connectors with dangerous contact voltage must only be plugged-in or unplugged in a deenergized state.

The rights, guidelines and standards according to the intended or planned use should be observed.

Bundled devices:

Isolation to external surfaces: basic insulation to EN 60947-1, no basic insulation at the termi-

Do not connect inputs and outputs, which are supplied via the module from AS-interface or via auxiliary power, with power supply and signal circuits with external potentials.