


- 1 MOLDED PARTS: POLYESTER, UL RATED 94V-0, BLACK. CONTACTS: BERYLLIUM COPPER.
- 2 2.54 μm [.000100] MIN TIN-LEAD ON TERMINATION END, 0.76 μm [.000030] MIN GOLD ON CONTACT AREA, ALL OVER 1.27 μm [.000050] MIN NICKEL.
- 3 POSITION TOLERANCE APPLIES 0.76 [.030] ABOVE DATUM V.
- 4 POSITION NUMBER 1 INDICATOR.
- 5 ELECTRICAL ENGAGEMENT ZONE.
- 6 RECOMMENDED 28 AWG RIBBON CABLE, 0.61 - 0.97 [.024 - .038] THICK PVC, 1.0000 [.03937] PITCH. AMP LOGO ORIENTATION IS OPTIONAL.
- 7 RECESS ON EACH END, OPPOSITE CORNER.
- 8 0.13 μm [.000005] MIN GOLD ON TERMINATION END, 0.76 μm [.000030] MIN GOLD ON CONTACT AREA, ALL OVER 1.27 μm [.000050] MIN NICKEL.
- 10 MOLD GATE PROJECTION ON EITHER END OF COVER TO BE EXCLUDED FROM DIMENSION 'B' MEASUREMENT.



CONTACT FINISH	D	C	B	A	NO OF POSN	PART NO
	12.40	17.15	11	12		3-111623-1
	12.40	17.15	11	12		1-111623-7
	8.41	13.18	7	8		1-111623-6
	8.41	13.18	7	8		1-111623-5
	22.40	27.18	21	22		1-111623-5
	22.40	27.18	21	22		1-111623-4
	22.40	27.18	21	22		1-111623-3
	22.40	27.18	21	22		1-111623-2
	34.42	39.17	33	34		1-111623-1
	34.42	39.17	33	34		1-111623-0
	34.42	39.17	33	34		1-111623-9
	24.41	29.18	23	24		1-111623-7
	24.41	29.18	23	24		1-111623-5
	24.41	29.18	23	24		1-111623-4
	24.41	29.18	23	24		1-111623-3
	24.41	29.18	23	24		1-111623-2
	50.39	55.17	49	50		1-111623-1
	50.39	55.17	49	50		1-111623-0
	50.39	55.17	49	50		1-111623-9
	44.40	49.17	43	44		1-111623-8
	44.40	49.17	43	44		1-111623-7
	44.40	49.17	43	44		1-111623-6
	44.40	49.17	43	44		1-111623-5
	44.40	49.17	43	44		1-111623-4
	44.40	49.17	43	44		1-111623-3
	44.40	49.17	43	44		1-111623-2
	44.40	49.17	43	44		1-111623-1
	44.40	49.17	43	44		1-111623-0
	44.40	49.17	43	44		1-111623-9
	16.41	21.18	15	16		111623-9
	16.41	21.18	15	16		111623-8
	16.41	21.18	15	16		111623-7
	16.41	21.18	15	16		111623-6
	16.41	21.18	15	16		111623-5
	16.41	21.18	15	16		111623-4
	16.41	21.18	15	16		111623-3
	16.41	21.18	15	16		111623-2
	16.41	21.18	15	16		111623-1
	16.41	21.18	15	16		111623-0
	16.41	21.18	15	16		111623-9
	10.41	15.16	9	10		111623-8
	10.41	15.16	9	10		111623-7
	10.41	15.16	9	10		111623-6
	10.41	15.16	9	10		111623-5
	10.41	15.16	9	10		111623-4
	10.41	15.16	9	10		111623-3
	10.41	15.16	9	10		111623-2
	10.41	15.16	9	10		111623-1
	10.41	15.16	9	10		111623-0
	10.41	15.16	9	10		111623-9

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm [INCHES]. TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± .008 [0.03], 1 PLC ± .008 [0.03], 2 PLC ± .008 [0.03], 3 PLC ± .008 [0.03], 4 PLC ± .008 [0.03]. MATERIAL: POLYESTER. FINISH: CONTACTS: SEE TABLE.

DIN C. OBERMAN 02-21-92. CHK: J. McCLINTON 3-9-92. NAME: J. McCLINTON. PRODUCT SPEC: 108-1372. APPLICATION SPEC: RECEPTACLE ASSY, POLARIZED, 2mm CL, AMP-LATCH. SIZE: A1. CAGE CODE: 00779. DRAWING NO: 111623. WEIGHT: -. RESTRICTED TO: CUSTOMER DRAWING. SCALE: 10:1. SHEET: 1 of 1. REV: L2.

**STE** TE Connectivity

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-111623-9](#)