

## 107N

MINIATURE EPOXY POTTED AUDIO TRANSFORMER


Audio input, line matching and output transformers Epoxy potted in an attractive molded case, Pin type, P.C. board mount, (min. 0.187" length) Rugged epoxy potted construction produces a completely sealed unit withstanding severe environmental conditions. In some models where no center tap is present (on the secondary), pin 5 is omitted. Secondary may be used as primary and primary as secondary. Will withstand soldering for 10 sec. @ 260 degrees C, ambient temp. 85 degrees C max.

Power level: 150mw @ 150 Hz. to 50 Khz. -Freq. range @ +0 dbm is 150 Hz. to 80 Khz. +/- 1.5db -Freq. range @ +10 dbm is 150 Hz. to 80 Khz. +/- 1.5db -Freq. range @ +20 dbm is 150 Hz. to 80 Khz. +/- 1.5db -Freq. measurements with no D.C. saturation.

## **ELECTRICAL SPECIFICATIONS**

<b>Characteristic</b>	Typical
Input Impedance	10000 ΩCT
Output Impedance	600 ΩCT
Output Power	0.150 Watts
DCR	
Primary 1-3	710 Ω (410Ω/300Ω)
Secondary 4-6	70 Ω (35Ω/35Ω)
Inductance	@ 1.0 kHz, 1.0 V OC
Primary	5.89 Hy
Secondary	0.388 Hy
Leakage Inductance	7.0 mH
Impedance	@ 1.0 kHz, 1.0 V OC
Primary	45.4 ΚΩ
Secondary	3.15 ΚΩ
Frequency Response	$\pm$ 1.5db from 300Hz to 50KHz
Turns ratio	4.07:1
Dielectric Strength	100 Vrms
Temperature Range	-40 To 105°C**


## PCB LAYOUT




Hammond Mfg. Co. Ltd., Electronics Division


www.hammondmfg.com






0.630
0.630
0.566
0.566
1 2 3







107N Rs=10K, RI=600 THD+N 107N Rs=10K, RI=600 Phase Shift 50 - 0 stors -- 10 stors -- 20 stors 23 dbm 40 60 10 dbm 0 dbm 30 40 23 dbm (%) N+OH1 Degrees 20 20 0 dbm 10 dbm 10 0 -20 Ó -10 -40 20 30 40 50 70 100 200 300 500 700 1000 2000 3000 5000 10000 20000 50000 100000 20 30 40 50 70 100 200 300 500 700 1000 2000 3000 5000 10000 20000 50000 100000 Frequency (Hz) Frequency (Hz)

PRIMARY SECONDARY

Measurement instruments Hp4192a impedance analyzer Hp3456a DVM Keithley 2002 DVM D scope series iii audio analyzer

TYPICAL TEST CIRCUIT

\*\* The epoxy that is used to cast these parts has a workable temperature range of -40°C to +105°C Under a normal rate of change, this does not include thermal shock. Variations in the transformer materials and environmental conditions may reduce the workable temperature range.

This drawing and the information in it is the property of Hammond Manufacturing. It may not be reproduced, transmitted or used in any manner whatsoever without the written permission of Hammond Manufacturing. Data subject to change without notice.