

LQM31PN2R2M00#

“#” indicates a package specification code.


Size Code 3216 (1206) in mm (in inch), 0.95mm max. Thickness



< List of part numbers with package codes >

LQM31PN2R2M00L LQM31PN2R2M00B

Appearance & Shape



References

Packaging	Specifications	Standard Packing Quantity
L	180Embossed Tape	3000
B	Bulk(Bag)	1000

Mass (typ.)	
1 piece	0.024g

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

LQM31PN2R2M00#

“#” indicates a package specification code.



Specifications

L size	3.2±0.2mm
W size	1.6±0.2mm
T size	0.85±0.1mm
Size code inch (mm)	1206 (3216)
Inductance	2.2μH±20%
Inductance Test Frequency	1MHz
Rated current (Itemp) (Based on Temperature rise)	900mA
Max. of DC resistance	0.238Ω
Class of magnetic shield	Ferrite Core
Self resonance frequency (min.)	40MHz
DC Resistance Intermediate Values	0.19Ω±25%
Operating Temperature Range	-55°C to 125°C
Series	LQM31PN_00

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


LQM31PN2R2M00#

“#” indicates a package specification code.




Characteristic Data


The charts below may show another part number which shares its characteristics.




■ LQM31PN2R2M00 L



■ LQM31PN2R2M00 Q



■ LQM31PN2R2M00 |Z|



■ LQM31PN2R2M00 L-Current 20degC


Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

LQM31PN2R2M00#

“#” indicates a package specification code.

Temperature rise characteristics



■ LQM31PN2R2M00 Temp. rise

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.