

Surface Mount Type

Series: **ZA** Type: **V**

High temperature Lead-Free reflow



■ Features

- Endurance: 10000 h at 105 °C
- Low ESR and High ripple current (70 % over, Lower ESR than Current V-FP)
- High voltage (to 80V)
- Equivalent to conductive polymer type Aluminum Electrolytic Capacitor (There are little characteristics change by temperature and frequency)
- AEC-Q200 qualified*
- RoHS directive compliant

■ Specifications

Category Temp.Range	-55 °C to +105 °C																			
Rated W.V. Range	25 V.DC to 80 V.DC																			
Nominal Cap. Range	10 μF to 330 μF																			
CapacitanceTolerance	±20 % (120 Hz/+20 °C)																			
DC Leakage Current	I ≤ 0.01 CV or 3 (μA) After 2 minutes (Whichever is greater)																			
tan δ	Please see the attached Standard Products list																			
Endurance	The capacitor shall be subjected to application of the D.C. voltage with full rated ripple current at +105 °C for 10000 hours. After stabilizing at room temperature(+15 to 35 °C), the capacitor shall not exceed the specified limits. (The sum of DC voltage and ripple peak voltage shall not exceed the rated voltage.)																			
	Capacitance change	±30 % of initial measured value																		
	tan δ	≤ 200 % initial specified value																		
	E.S.R.	≤ 200 % initial specified value																		
	DC leakage current	≤ initial specified value																		
	ESR after Endurance (Ω/100 kHz) (-40°C)	<table border="1"> <tr> <th colspan="5">Size Code</th> </tr> <tr> <th>C</th> <th>D</th> <th>D8</th> <th>F</th> <th>G</th> </tr> <tr> <td>2.0</td> <td>1.4</td> <td>0.8</td> <td>0.4</td> <td>0.3</td> </tr> </table>					Size Code					C	D	D8	F	G	2.0	1.4	0.8	0.4
Size Code																				
C	D	D8	F	G																
2.0	1.4	0.8	0.4	0.3																
Shelf Life	After storage for 1000 hours at +105 °C±2 °C with no voltage applied and then being stabilized at +20 °C, capacitors shall meet the limits specified in Endurance. (With voltage treatment)																			
Damp Heat (Load)	After applying rated working voltage for 2000 hours at +85°C±2°C / 85% to 90%RH and then being stabilized at +20°C, Capacitors shall meet the following limits.																			
	Capacitance change	±30 % of initial measured value																		
	tan δ	≤ 200 % initial specified value																		
	E.S.R.	≤ 200 % initial specified value																		
	DC leakage current	≤ initial specified value																		
Resistance to Soldering Heat	After reflow soldering and then being stabilized at +20 °C, capacitors shall meet the following limits.																			
	Capacitance change	±10 % of initial measured value																		
	tan δ	≤ initial specified value																		
	DC leakage current	≤ initial specified value																		

■ Marking

Example : 25 V 33 μF Marking color : BLACK

E	25 V	J	63 V
V	35 V	K	80 V
H	50 V		

■ Dimensions in mm (not to scale)

(Unit : mm)

Size code	D	L	A, B	H	I	W	P	K
C	5.0	5.8±0.3	5.3	6.5 max.	2.2	0.65±0.1	1.5	0.35 ^{+0.15} _{-0.20}
D	6.3	5.8±0.3	6.6	7.8 max.	2.6	0.65±0.1	1.8	0.35 ^{+0.15} _{-0.20}
D8	6.3	7.7±0.3	6.6	7.8 max.	2.6	0.65±0.1	1.8	0.35 ^{+0.15} _{-0.20}
F	8.0	10.2±0.3	8.3	10.0 max.	3.4	0.90±0.2	3.1	0.70±0.2
G	10.0	10.2±0.3	10.3	12.0 max.	3.5	0.90±0.2	4.6	0.70±0.2

* This product qualifi for AEC-Q200, but it has some deviations.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Standard Products

Endurance : 105 °C 10000 h

W.V. (V)	Cap. (±20 %) (μF)	Case size			Specification			Part No. (RoHS: compliant)	Reflow	Min. Packaging Q'ty
		Dia. (mm)	Length (mm)	Size Code	Ripple Current (100 kHz) (+105 °C) (mA r.m.s.)	E.S.R. (100 kHz) (+20 °C) (mΩ)	tan δ (120 Hz) (+20 °C)			Taping (pcs)
25	33	5	5.8	C	900	80	0.14	EEHZA1E330R	(5)	1000
	56	6.3	5.8	D	1300	50	0.14	EEHZA1E560P	(5)	1000
	100	6.3	7.7	D8	2000	30	0.14	EEHZA1E101XP	(5)	900
	220	8	10.2	F	2300	27	0.14	EEHZA1E221P	(6)	500
	330	10	10.2	G	2500	20	0.14	EEHZA1E331P	(6)	500
35	22	5	5.8	C	900	100	0.12	EEHZA1V220R	(5)	1000
	27	6.3	5.8	D	1300	60	0.12	EEHZA1V270P	(5)	1000
	47	6.3	5.8	D	1300	60	0.12	EEHZA1V470P	(5)	1000
	68	6.3	7.7	D8	2000	35	0.12	EEHZA1V680XP	(5)	900
	150	8	10.2	F	2300	27	0.12	EEHZA1V151P	(6)	500
50	270	10	10.2	G	2500	20	0.12	EEHZA1V271P	(6)	500
	10	5	5.8	C	750	120	0.10	EEHZA1H100R	(5)	1000
	22	6.3	5.8	D	1100	80	0.10	EEHZA1H220P	(5)	1000
	33	6.3	7.7	D8	1600	40	0.10	EEHZA1H330XP	(5)	900
	68	8	10.2	F	1800	30	0.10	EEHZA1H680P	(6)	500
63	100	10	10.2	G	2000	28	0.10	EEHZA1H101P	(6)	500
	10	6.3	5.8	D	1000	120	0.08	EEHZA1J100P	(5)	1000
	22	6.3	7.7	D8	1500	80	0.08	EEHZA1J220XP	(5)	900
	33	8	10.2	F	1700	40	0.08	EEHZA1J330P	(6)	500
80	56	10	10.2	G	1800	30	0.08	EEHZA1J560P	(6)	500
	22	8	10.2	F	1550	45	0.08	EEHZA1K220P	(6)	500
	33	10	10.2	G	1700	36	0.08	EEHZA1K330P	(6)	500

•Please refer to the page of "Reflow Profile" and "The Taping Dimensions".

■ Frequency correction factor for ripple current

Capacitance (μF)	Frequency (kHz)	0.1	0.12	0.2	0.3	0.5	1	2	3	5	10	15	20	30	40	50	100	300	500	1000
C < 47	Correction factor	0.10	0.10	0.10	0.15	0.20	0.30	0.40	0.45	0.50	0.60	0.65	0.70	0.75	0.80	0.85	1.00	1.00	1.05	1.05
47 ≤ C < 150		0.15	0.15	0.20	0.25	0.30	0.40	0.45	0.55	0.60	0.70	0.75	0.80	0.80	0.85	0.90	1.00	1.00	1.00	1.00
150 ≤ C		0.15	0.15	0.25	0.25	0.30	0.45	0.50	0.60	0.65	0.75	0.80	0.85	0.85	0.85	0.90	1.00	1.00	1.00	1.00