

TECHNICAL DATA SHEET

Part#: 7249E

Cutters - Long Nose Fine Tip - Relieved Head -★★★★- Carbon Steel

The 7249E five star Lazer Line® relieved fine tip optimum flush cutter has a cutting capacity of .001" - .020" soft wire. It is made of carbon tool steel steel with induction hardened cutting blades to RHC 63-65. This overall length is 6". The CNC machining allows the joint surfaces to be perfect to allow for long life. The dual leaf springs provide a smooth action.

**** Precision Level

Material

 Surface Resistivity Shape

Type of Cut

• Group

Cutting Capacity

 Blade Angle • Blade Length

• Body Width

Body Height

OAL

• Weight (OZ)

• UPC Schedule B

• ECCN

• UNSPSC Code

Country of Origin

Carbon

10⁸ ohms/sq

Relieved Head

Lazer Flush

Cutting Tools

50 - 22 AWG / .001 - .020" / .03 - .63 mm

16°

.175" (4.38mm)

0.42" (10.5mm)

.25" (6.25mm)

5" (125mm)

3

662847009594

8203.20.60.60

EAR99

27111511

USA









