
### **Resistors**



# TaNFilm® Precision DIP Network Commercial and MIL Qualified

#### 1900 Series

- Inherent reliability
- MIL-PRF-83401 qualified
- Custom configuration available
- Bonded leads not susceptible to solder reflow problems
- Absolute tolerance to ±0.1% / ratio tolerance to ±0.05%
- Absolute TCR to ±15ppm/°C / ratio tracking to ±5ppm/°C



All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)

The IRC 1900 Series is the ultimate combination of precision performance, reliability, and long term stability in a low profile, TaNFilm® DIP package. Rugged welded lead construction combined with the inherent passivation characteristics of tantalum nitride ensure superior ongoing performance over the installed life of the part.

Visit our website to view a graphical demonstration of IRC's TaNFilm® reliability and performance features.

#### **Electrical Data**

Schematic	Resistance Range (Ω)	Absolute Tolerance	Optional Ratio Tolerance	Absolute TCR (ppm/°C) Tracking TCR (ppm/°C)		Military Characteristic	Element Power (mW)
A Commercial	10 - 49.9	F, G, J	F, G	±50; ±100; ±300	±20		200
	50.0 - 199	F, G, J	D, F, G	±25; ±50; ±100; ±300	±10	N1/A	
	200 - 999	B, D, F, G, J	A, B, D, F, G	±25; ±50; ±100; ±300	±5	N/A	
	1.0K - 400K	B, D, F, G, J	A, B, D, F, G	±15; ±25; ±50; ±100; ±300	5; ±25; ±50; ±100; ±300 ±5		
A Military	50 - 100K	B, D, F, G, J	N/A	N/A	N/A H, K, M		
B Commercial	50 - 149	B, D, F, G, J	B, D, F, G	±300; ±100	±50		100
	150 - 249	B, D, F, G, J	B, D, F, G	±300; ±100; ±50	±20	N/A	
	250 - 999	B, D, F, G, J	B, D, F, G	±25; ±50; ±100; ±300	±5	IN/A	
	1.0K - 200K	B, D, F, G, J	B, D, F, G	±15; ±25; ±50; ±100; ±300 ±5			
B Military	50 - 70K	B, D, F, G, J	N/A	N/A	N/A	Н, К, М	

### Package Specification Data

Schematic	Package Power (W)			Voltage Rating	Temperature Range	Substrate	Lead Finish	Noise
	8-pin	14-pin	16-pin					
Α	0.8	1.4	1.6	√PxR not to exceed 100V	-55°C to +150°C	99.6% Alumina	Gold Plate (60/40 Sn/Pb available)	<-30dB
В	0.7	1.3	1.5					

#### General Note

# **TaNFilm® Precision DIP Network Commercial and MIL Qualified**


**Electronics** 

**1900 Series** 

#### **Environmental Data**

Total Doc Mill. DDF 00404	MIL-PRF-	83401 Limits (D	TaNFilm Test Data (Delta R%)		
Test Per MIL-PRF-83401	М	К	н	Max	Typical
Thermal Shock And Power Conditioning	0.7	0.7	0.5	0.10	0.02
Low Temperature Operation	0.5	0.25	0.1	0.1	0.02
Short-term Overload	0.5	0.25	0.1	0.05	0.02
Terminal Strength	0.25	0.25	0.25	0.1	0.02
Resistance To Solder Heat	0.25	0.25	0.1	0.1	0.02
Moisture Resistance	0.5	0.5	0.4	0.1	0.02
Shock	0.25	0.25	0.25	0.1	0.02
Vibration	0.25	0.25	0.25	0.1	0.02
Life	2.0	0.5	0.5	0.1	0.02
High Temperature Exposure	1.0	0.5	0.2	0.1	0.02
Low Temperature Storage	0.5	0.25	0.1	0.1	0.02
25°C Double Load	2.0	0.5	0.5	0.05	0.02

## Physical Data




# TaNFilm® Precision DIP Network Commercial and MIL Qualified







#### Schematic Data



# Commercial and MIL-Screened (Non-QPL) Ordering Data



## MIL-PRF-83401 Ordering Data



Standard lead termination is gold plate.
Contact factory for optional 60/40 Sn/Pb solder dip finish.

#### General Note

Custom schematics and screening available