





E222871

UL Approved Illuminated Pushbutton

Specifications

Electrical Ratings	3A @ 125VAC, 65°C, 50K cycles
	3A @ 250VAC, 65°C, 50K cycles
Electrical Life	50,000 cycles typical
Mechanical Life	1,000,000 cycles typical momentary
	500,000 cycles typical latching
Contact Resistance	≤50mΩ initial

Actuation Force	200 ±50gF SPDT
	250 ±50gF DPDT
Actuation Travel	3.2 ± .25mm
Dielectric Strength	2,000Vrms min between contacts
Insulation Resistance	≥ 1,000MΩ min @ 500VDC
Sealing Degree	IP67
Operating Temperature	-20°C to 55°C
Storage Temperature	-20°C to 55°C

Materials

-	
Actuator	Stainless Steel, Anodized Aluminum
LED Lens	Polycarbonate (PC)
Threaded Body	Stainless Steel, Anodized Aluminum
Terminal Support	Polybutylene Terephthalate (PBT)
Inner Switch Body	Polybutylene Terephthalate (PBT)
Contacts	Silver plated Copper Alloy
Terminals	Silver plated Copper Alloy
Hardware	One Hex Nut & One "O" Ring Supplied

Ordering Information

1. Series	DH22U	1	N	В	S	R	12
DH22U							
2. Number of Pol 1 = SPDT 2 = DPDT	les						
3. Latching Option N = Momentar L = Latching							
	: ator, non-illuminat ator, ring illuminat						
5. Switch Finish S = Stainless S B = Black Anoc	Steel dized Aluminum						
6. First LED Colo Z = No LED R = Red Y = Yellow G = Green B = Blue W = White	or						
7. LED Voltage							

24 = 24V

N = No internal resistor in series with the LED

110 = 110V 220 = 220V


Z = No LED 6 = 6V

12 = 12V




UL Approved Illuminated Pushbutton

Dimensions




A - Flush Actuator, Non-illuminated




B - Flush Actuator, Ring Illuminated


Schematics








DPDT



Bottom View





Panel Cut-Out



UL Approved Illuminated Pushbutton

Optional Socket Housing





Terminal for use with wire sizes 18AWG to 24AWG

LED Characteristics

LED Ratings		Color						
		R	Υ	G	В	W	Units	
Reverse Voltage	V_R	5	5	5	5	5	V	
Forward Current (peak)	I _{FS}	120	120	160	160	160	mA	
Reverse Current V _R = 5V	I _R	10	10	10	10	10	μA	
Power Dissipation	P _T	80	80	120	120	120	mW	
Forward Voltage (typ) I _F = 20mA	V_{F}	2.1	2.1	3.3	3.3	3.0	V	
Luminous Intensity, I _F = 20mA	LI	120	120	170	100	700	mcd	