

AirMax VS2[®] BACKPLANE CONNECTOR SYSTEM


OVERVIEW

AirMax VS2[®] connectors provide a migration path from AirMax VS[®] for speeds up to 20Gb/s, providing margin of safety for typical 802.3ap system performance with the flexibility of an open pin field design. The connectors leverage AirMax VS[®] and VSe[®] design features and technology to achieve improved signal integrity and mechanical attributes compared to AirMax VS[®] connectors.

The connector utilizes FCI technology for a shieldless design with no metallic plates and closely coupled differential pair design to yield low loss and low crosstalk.

AirMax VS2[®] connectors are mating-compatible to both AirMax VS[®] and AirMax VSe[®] connectors and require no changes to connector PCB footprints. The mating-compatible interfaces and capability to preserve critical pin assignments can provide opportunities for cost savings as new and upgraded equipment is deployed. For example, a backplane or chassis can be designed to allow the installation and continued use of legacy daughter cards, line cards, or blades that are already in the field as well as new or future higher-speed module cards.

Right angle and vertical receptacles and headers support backplane, midplane and coplanar applications.



FEATURES

- Provides a migration path to 20Gb/s per differential pair
- Shieldless design with closely coupled pairs
- Backward mateable to existing VS and VS2 designs
- 3, 4 and 5 pair backplane and coplanar versions are available
- Available with 0.5mm or 0.4mm compliant pins
- Hard metric design practice

BENEFITS

- Enables users to upgrade systems for higher performance in the same form factor
- Cost-effective solution yields low XT and Insertion Loss
- Drop in upgrade to previous generation systems
- Same product covers a wide range of customer applications
- 0.5mm vias provide a drop-in replacement for VS parts
- Improved SI with the 0.4mm tails, same as VSe
- Can mix-and-match with other metric power and guidance components to create the precise system configuration that is needed





TECHNICAL INFORMATION

MATERIALS

- Contacts: High performance Copper Alloy
- Contact Finish:
 - Performance-based plating at separable interface (Telcordia GR-1217-CORE Central Office)
 - Tin over Nickel on press-fit tails
 - Tin-lead option
- Housings: High Performance Thermoplastic, 94-V0
- Plating GXT+™

ELECTRICAL PERFORMANCES

- Contact Resistance: ≤ 60 m Ω initial in backplane application, ≤ 120 m Ω initial in coplanar application
- Current Rating (with $\leq 30^\circ\text{C}$ temperature rise above ambient): 0.5 A/contact with all contacts powered
- Insertion Loss Performance: see graph below
- Crosstalk Performance: see graph below

ENVIRONMENTAL

- Telcordia GR-1217-CORE Central Office qualification passed

MECHANICAL PERFORMANCE

- Durability: 200 cycles
- Mating Force: 0.50N max./contact
- Unmating Force: 0.15N min./contact
- Average Compliant Pin Insertion Force/ pin:
 - 0.4mm PCB hole: 15N max.
 - 0.5mm PCB hole: 30N max.

SPECIFICATIONS

- Product: GS-12-0956
- Application: GS-20-0305

APPROVALS AND CERTIFICATIONS


- UL approved

PACKAGING

- Trays or Tubes

TARGET MARKETS/APPLICATIONS

- Communications
 - Switches
 - Routers
 - Access
 - Optical Transmission
 - Wireless Base Stations
- Data
 - Servers
 - Switches
 - Storage
- Industrial & Instrumentation
 - Test & Measurement
- Medical




PART NUMBERS

AirMax VS2® TRADITIONAL MOTHER-DAUGHTER BOARD CONNECTORS 0.5mm PTH PRESS-FIT*

Product Variation			2.0mm Column Pitch		Differential Impedance
Pairs	Columns	Differential Pairs	Mating Connector System		
			Vertical Header	Right Angle Receptacle	
3	6	18	10122769-101LF	10122643-101LF	100 OHMS
	8	24	10127937-101LF	10124355-101LF	
	10	30	10127939-101LF	10124420-101LF	
4	6	24	10130556-101LF	10130565-101LF	
	8	32	10130557-101LF	10130566-101LF	
	10	40	10122770-101LF	10122655-101LF	
5	8	40	10130558-101LF	10128702-101LF	
	10	50	10122771-101LF	10122665-101LF	




Right Angle Receptacle



Vertical Header (2 Wall)

AirMax VS2® INVERSE MOTHER-DAUGHTER BOARD CONNECTORS 0.5mm PTH PRESS-FIT*

Product Variation			2.0mm Column Pitch		Differential Impedance
Pairs	Columns	Differential Pairs	Mating Connector System		
			Vertical Receptacle	Right Angle Header (4 Wall)	
3	6	18	10124469-102LF	10123543-101LF	100 OHMS
	8	24	10125811-102LF	10124408-101LF	
	10	30	10127116-102LF	10124422-101LF	
4	6	24	10127117-102LF	10125538-101LF	
	8	32	10126796-102LF	10125530-101LF	
	10	40	10125559-102LF	10123536-101LF	
5	8	40	10127118-102LF	10128706-101LF	
	10	50	10124470-102LF	10123529-100LF	




Right Angle Header (4 Wall)



Vertical Receptacle

AirMax VS2® COPLANAR CONNECTORS 0.5mm PTH PRESS-FIT*

Product Variation			2.0mm Column Pitch		Differential Impedance
Pairs	Columns	Differential Pairs	Mating Connector System		
			Right Angle Receptacle	Right Angle Header (4 Wall)	
3	6	18	10122643-101LF	10123543-101LF	100 OHMS
	8	24	10124355-101LF	10124408-101LF	
	10	30	10124420-101LF	10124422-101LF	
4	6	24	10130565-101LF	10125538-101LF	
	8	32	10130566-101LF	10125530-101LF	
	10	40	10122655-101LF	10123536-101LF	
5	8	40	10128702-101LF	10128706-101LF	
	10	50	10122665-101LF	10123529-101LF	



Right Angle Header (4 Wall)



Right Angle Receptacle

*0.5mm standard press-fit pin is the same as the standard AirMax VS® connectors

Disclaimer


Please note that the above information is subject to change without notice.

AirMax VS2® TRADITIONAL MOTHER-DAUGHTER BOARD CONNECTORS 0.4mm PTH PRESS-FIT*

Product Variation			2.0mm Column Pitch		Differential Impedance
Pairs	Columns	Differential Pairs	Mating Connector System		
			Vertical Header	Right Angle Receptacle	
3	6	18	10123358-101LF	10123420-101LF	100 OHMS
	8	24	10127979-101LF	10124756-101LF	
	10	30	10129300-101LF	10126913-101LF	
4	6	24	10130559-101LF	10130567-101LF	
	8	32	10124957-101LF	10124997-101LF	
	10	40	10123359-101LF	10123421-101LF	
5	8	40	10130013-101LF	10129941-101LF	
	10	50	10123360-101LF	10123422-101LF	



Right Angle Receptacle



Vertical Header (2 Wall)

AirMax VS2® INVERSE MOTHER-DAUGHTER BOARD CONNECTORS 0.4mm PTH PRESS-FIT*

Product Variation			2.0mm Column Pitch		Differential Impedance
Pairs	Columns	Differential Pairs	Mating Connector System		
			Vertical Receptacle	Right Angle Header (4 Wall)	
3	6	18	10130665-102LF	10124149-101LF	100 OHMS
	8	24	10128101-102LF	10124755-101LF	
	10	30	10130666-102LF	10126918-101LF	
4	6	24	10130667-102LF	10130571-101LF	
	8	32	10130668-102LF	10130572-101LF	
	10	40	10130669-102LF	10124150-101LF	
5	8	40	10130670-102LF	10129940-101LF	
	10	50	10127982-102LF	10124151-101LF	




Right Angle Header (4 Wall)



Vertical Receptacle

AirMax VS2® COPLANAR CONNECTORS 0.4mm PTH PRESS-FIT*

Product Variation			2.0mm Column Pitch		Differential Impedance
Pairs	Columns	Differential Pairs	Mating Connector System		
			Right Angle Receptacle	Right Angle Header (4 Wall)	
3	6	18	10123420-101LF	10124149-101LF	100 OHMS
	8	24	10124756-101LF	10124755-101LF	
	10	30	10126913-101LF	10126918-101LF	
4	6	24	10130567-101LF	10130571-101LF	
	8	32	10124997-101LF	10130572-101LF	
	10	40	10123421-101LF	10124150-101LF	
5	8	40	10129941-101LF	10129940-101LF	
	10	50	12123422-101LF	10124151-101LF	



Right Angle Header (4 Wall)



Right Angle Receptacle

*0.4mm PTH press-fit pins maximizes signal integrity performance
 *0.5mm PTH press-fit pins maximizes aspect ratio

BPLAIRMVSETI15EA4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

10123529-101LF	10123420-101LF	10123543-101LF	10123422-101LF	10122770-1011LF	10122655-101LF
10123421-101LF	10124149-101LF	10123536-101LF	10122643-101LF	10122665-101LF	10124150-101LF
10124151-101LF	10124461-101LF	10124460-101LF	10124150-102LF	10124755-102LF	10125559-102LF
10124151-102LF	10123359-101LF	10123536-102LF	10124420-101LF	10123360-101LF	10124408-102LF
10123529-102LF	10124352-10PLF	10126913-101LF	10124755-112LF	10124352-10ALF	10124422-102LF
10123543-102LF	10116602-111LF	10124470-102LF	10116601-111LF	10124469-102LF	10124149-102LF
10124408-112LF	10122771-101LF	10115025-101LF	10115031-101LF	10122769-101LF	10124355-101LF
10126918-102LF	10115033-101LF	10124459-101LF	10124756-101LF	10122770-101LF	10123358-101LF
10135261-10ALF	10135261-10PLF	10135275-101LF	10135280-10PLF	10135280-10ALF	10135292-10PLF
10135292-10ALF	10135299-101LF	10135302-101LF	10135319-10ALF	10135319-10PLF	10136591-101LF
10136591-102LF	10135286-10ALF	10135286-10PLF	10135301-101LF	10136588-101LF	10136592-102LF
10136592-101LF	10136594-101LF	10136594-102LF	10136600-102LF	10136600-101LF	10133025-101LF
10135273-10PLF	10135273-10ALF	10135313-10ALF	10135313-10PLF	10136585-101LF	10135307-10PLF
10136589-102LF	10136589-101LF	10136595-102LF	10136595-101LF	10133027-101LF	10135267-10PLF
10135267-10ALF	10136586-101LF	10136587-101LF	10136590-102LF	10136590-101LF	10136593-101LF
10136593-102LF	10136596-101LF	10136596-102LF	10123358-111LF	10123359-111LF	10122771-111LF
10122770-111LF	10123360-111LF	10127982-102LF	10131108-102LF		