# **EXV, +105°C**



### **Overview**

The KEMET EXV aluminum electrolytic surface mount capacitors are designed for applications requiring ultra low impedance and a low profile vertical chip.

## **Applications**

Typical applications include audio/visual (AV), computer/monitor, communications, and switch mode power supplies (SMPS).

## **Benefits**

- · Surface mount lead terminals
- · Low profile vertical chip
- · Ultra-low impedance
- +105°C/3,000 5,000 hours





## **Part Number System**


EXV	226	M	6R3	Α	9B	AA
Series	Capacitance Code (pF)	Tolerance	Rated Voltage (VDC)	Electrical Parameters	Size Code	Packaging
Surface Mount Aluminum Electrolytic	First two digits represent significant figures for capacitance values. Last digit specifies the number of zeros to be added.	M = ±20%	6R3 = 6.3 010 = 10.0 016 = 16.0 025 = 25.0 035 = 35.0 050 = 50.0 080 = 80.0	A = Standard S = AEC-Q200	See Dimension Table	AA = Tape & Reel



## **Dimensions - Millimeters**







Size Code	D		L		A/B		С		E	
Size Coue	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance
9B	4.0	±0.5	5.4	+0.25/-0.1	4.3	±0.2	5.5	Maximum	1.8	±0.2
9D	5.0	±0.5	5.4	+0.25/-0.1	5.3	±0.2	6.5	Maximum	2.2	±0.2
9G	6.3	±0.5	5.4	+0.25/-0.1	6.6	±0.2	7.8	Maximum	2.6	±0.2
9H	6.3	±0.5	7.7	±0.3	6.6	±0.2	7.8	Maximum	2.6	±0.2
9M	8.0	±0.5	10.2	±0.3	8.3	±0.2	10.0	Maximum	3.4	±0.2
9P	10.0	±0.5	10.2	±0.3	10.3	±0.2	13.0	Maximum	3.5	±0.2
9R	12.5	±0.5	13.5	±0.5	12.8	±0.2	15.2	Maximum	4.9	±0.2
98	12.5	±0.5	16.0	±0.5	12.8	±0.2	15.2	Maximum	4.9	±0.2

Cina Cada	F		G		Р		W	
Size Code	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance	Nominal	Tolerance
9B	0.3	Maximum	0.35	+0.15/-0.2	1.0	±0.2	0.65	±0.1
9D	0.3	Maximum	0.35	+0.15/-0.2	1.5	±0.2	0.65	±0.1
9G	0.3	Maximum	0.35	+0.15/-0.2	1.8	±0.2	0.65	±0.1
9H	0.3	Maximum	0.35	+0.15/-0.2	1.8	±0.2	0.65	±0.1
9M	0.3	Maximum	0.70	±0.2	3.1	±0.2	0.90	±0.2
9P	0.3	Maximum	0.70	±0.2	4.6	±0.2	0.90	±0.2
9R	0.3	Maximum	1.0	±0.2	4.6	±0.2	1.25	±0.2
9\$	0.3	Maximum	1.0	±0.2	4.6	±0.2	1.25	±0.2



### **Environmental Compliance**

As an environmentally conscious company, KEMET is working continuously with improvements concerning the environmental effects of both our capacitors and their production. In Europe (RoHS Directive) and in some other geographical areas like China, legislation has been put in place to prevent the use of some hazardous materials, such as lead (Pb), in electronic equipment. All products in this catalog are produced to help our customers' obligations to guarantee their products and fulfill these legislative requirements. The only material of concern in our products has been lead (Pb), which has been removed from all designs to fulfill the requirement of containing less than 0.1% of lead in any homogeneous material. KEMET will closely follow any changes in legislation world wide and make any necessary changes in its products, whenever needed.

Some customer segments such as medical, military and automotive electronics may still require the use of lead in electrode coatings. To clarify the situation and distinguish products from each other, a special symbol is used on the packaging labels for RoHS compatible capacitors.

Due to customer requirements, there may appear additional markings such as lead free (LF) or lead-free wires (LFW) on the label.

#### **Performance Characteristics**

Item	Performance Characteristics
Capacitance Range	1 – 1,000 μF
Capacitance Tolerance	±20% at 120 Hz/20°C
Rated Voltage	6.3 - 80 VDC
Life Test	3,000 – 5,000 hours (see conditions in Test Method & Performance)
Operating Temperature	-55°C to +105°C
Laslana Oumant	l ≤ 0.01 CV or 3 μA, whichever is greater
Leakage Current	C = rated capacitance (μF), V = rated voltage (VDC). Voltage applied for 2 minutes at 20°C.
	Automotive version: Part number position 11 = "S"
Vibration Test Specifications	5G maximum acceleration. Vibration applied in 3 directions (X, Y, and Z axis). 4-hour sessions at 10 – 2,000 Hz
	(Capacitor clamped by the body)

## **Impedance Z Characteristics at 120 Hz**

Rated Voltage (VDC)	6	10	16	25	35	50	80
Z (-25°C)/Z (20°C)	2	2	2	2	2	2	2
Z (-40°C)/Z (20°C)	3	3	3	3	3	3	3



### **Compensation Factor of Ripple Current (RC) vs. Frequency**

Frequency	120 Hz	1 kHz	10 kHz	100 kHz
Coefficient	0.70	0.80	0.90	1.00

#### **Test Method & Performance**

Conditions	Load L	ife Test	Shelf Life Test				
Temperature	10	105°C					
Took Duration	Can Ø ≤ 6.3 mm	3,000 hours	1 000 haura				
Test Duration	Can Ø ≥ 8 mm	5,000 hours	1,000 hours				
Ripple Current	Maximum ripple current specif	No ripple current applied					
Voltage	The sum of DC voltage and the exceed the rated voltage of the	No voltage applied					
Performance	The following specificati	ons will be satisfied when the	e capacitor is restored to 20°C:				
Capacitance Change	Within ±30% of the initial value						
Dissipation Factor	Does not exceed 200% of the specified value						
Leakage Current	Does not exceed specified valu	Does not exceed specified value					

#### **Shelf Life**

The capacitance, ESR and impedance of a capacitor will not change significantly after extended storage periods, however, the leakage current will very slowly increase.

KEMET's E aluminum electrolytic capacitors should not be stored in high temperatures or where there is a high level of humidity. The suitable storage condition for KEMET's E aluminum electrolytic capacitors is +5 to +35°C and less than 75% in relative humidity. KEMET's E aluminum electrolytic capacitors should not be stored in damp conditions such as water, saltwater spray or oil spray. KEMET's E aluminum electrolytic capacitors should not be stored in an environment full of hazardous gas (hydrogen sulphide, sulphurous acid gas, nitrous acid, chlorine gas, ammonium, etc.) KEMET's E aluminum electrolytic capacitors should not be stored under exposure to ozone, ultraviolet rays or radiation.

If a capacitor has been stored for more than 18 months under these conditions and it shows increased leakage current, then a treatment by voltage application is recommended.

## **Re-Age (Reforming) Procedure**

Apply the rated voltage to the capacitor at room temperature for a period of one hour, or until the leakage current has fallen to a steady value below the specified limit. During re-aging a maximum charging current of twice the specified leakage current or 5 mA, whichever is greater, is suggested.



**Table 1 - Ratings & Part Number Reference** 

Rated Voltage	Surge Voltage	Rated Capacitance	Case Size	DF	RC	Z	LC	Part Number
(VDC)	(VDC)	120 Hz 20°C (μF)	D x L (mm)	120 Hz 20°C (tan& %)	100 kHz 105°C (mA)	100 kHz 20°C (Ω)	20°C 2 minutes (μΑ)	() Represents Part Number Options
6.3	8	680	10 x 10.2	26	850	0.12	42.8	EXV687M6R3(1)9PAA
6.3	8	1,000	10 x 10.2	26	850	0.12	63.0	EXV108M6R3(1)9PAA
6.3	8	22	4 x 5.4	26	90	1.93	3.0	EXV226M6R3(1)9BAA
6.3	8	33	4 x 5.4	26	90	1.93	3.0	EXV336M6R3(1)9BAA
6.3	8	47	5 x 5.4	26	160	1.00	3.0	EXV476M6R3(1)9DAA
6.3	8	100	6.3 x 5.4	26	240	0.52	6.3	EXV107M6R3(1)9GAA
6.3	8	150	6.3 x 7.7	26	240	0.30	9.5	EXV157M6R3(1)9HAA
6.3	8	220	6.3 x 7.7	26	240	0.30	13.9	EXV227M6R3(1)9HAA
6.3	8	330	8 x 10.2	26	600	0.16	20.8	EXV337M6R3(1)9MAA
6.3	8	470	8 x 10.2	26	600	0.16	29.6	EXV477M6R3(1)9MAA
10	13	470	10 x 10.2	19	850	0.12	47.0	EXV477M010(1)9PAA
10	13	680	10 x 10.2	19	850	0.12	68.0	EXV687M010(1)9PAA
10	13	1,000	10 x 10.2	19	850	0.12	100.0	EXV108M010(1)9PAA
10	13	22	4 x 5.4	19	90	1.93	3.0	EXV226M010(1)9BAA
10	13	33	5 x 5.4	19	160	1.00	3.3	EXV336M010(1)9DAA
10	13	47	6.3 x 5.4	19	190	0.52	4.7	EXV476M010(1)9GAA
10	13	100	6.3 x 5.4	19	190	0.52	10.0	EXV107M010(1)9GAA
10	13	150	6.3 x 7.7	19	240	0.34	15.0	EXV157M010(1)9HAA
10	13	220	8 x 10.2	19	600	0.16	22.0	EXV227M010(1)9MAA
10	13	330	8 x 10.2	19	600	0.16	33.0	EXV337M010(1)9MAA
16	20	470	10 x 10.2	16	850	0.12	75.2	EXV477M016(1)9PAA
16	20	680	10 x 10.2	16	850	0.12	108.8	EXV687M016(1)9PAA
16	20	10	4 x 5.4	16	90	1.93	3.0	EXV106M016(1)9BAA
16	20	22	4 x 5.4	16	160	1.00	3.5	EXV226M016(1)9BAA
16	20	22	5 x 5.4	16	160	1.00	3.5	EXV226M016(1)9DAA
16	20	33	6.3 x 5.4	16	240	0.52	5.3	EXV336M016(1)9GAA
16	20	47	6.3 x 5.4	16	240	0.52	7.5	EXV476M016(1)9GAA
16	20	100	6.3 x 5.4	16	240	0.52	16.0	EXV107M016(1)9GAA
16	20	100	6.3 x 7.7	16	280	0.34	16.0	EXV107M016(1)9HAA
16	20	220	6.3 x 7.7	16	280	0.34	35.2	EXV227M016(1)9HAA
16	20	150	8 x 10.2	16	370	0.22	24.0	EXV157M016(1)9MAA
16	20	220	8 x 10.2	16	370	0.22	35.2	EXV227M016(1)9MAA
16	20	330	8 x 10.2	16	600	0.16	52.8	EXV337M016(1)9MAA
16	20	470	8 x 10.2	16	600	0.16	75.2	EXV477M016(1)9MAA
25	32	330	10 x 10.2	14	850	0.12	82.5	EXV337M025(1)9PAA
Rated Voltage	Surge Voltage	Rated Capacitance	Case Size	DF	RC	Z	LC	Part Number

<sup>(1)</sup> Insert Electrical Parameters code. See Part Number System for available options.



Table 1 - Ratings & Part Number Reference cont.

Rated Voltage	Surge Voltage	Rated Capacitance	Case Size	DF	RC	Z	LC	Part Number
(VDC)	(VDC)	120 Hz 20°C (μF)	D x L (mm)	120 Hz 20°C (tanδ %)	100 kHz 105°C (mA)	100 kHz 20°C (Ω)	20°C 2 minutes (µA)	() Represents Part Number Options
25	32	470	10 x 10.2	14	850	0.12	117.5	EXV477M025(1)9PAA
25	32	10	4 x 5.4	14	90	1.93	3.0	EXV106M025(1)9BAA
25	32	22	5 x 5.4	14	160	1.00	5.5	EXV226M025(1)9DAA
25	32	33	6.3 x 5.4	14	240	0.52	8.3	EXV336M025(1)9GAA
25	32	47	6.3 x 5.4	14	240	0.52	11.8	EXV476M025(1)9GAA
25	32	68	6.3 x 7.7	14	280	0.34	17.0	EXV686M025(1)9HAA
25	32	100	6.3 x 7.7	14	300	0.34	25.0	EXV107M025(1)9HAA
25	32	150	8 x 10.2	14	600	0.16	37.5	EXV157M025(1)9MAA
25	32	220	8 x 10.2	14	600	0.16	55.0	EXV227M025(1)9MAA
35	44	150	10 x 10.2	12	850	0.12	52.5	EXV157M035(1)9PAA
35	44	220	10 x 10.2	12	850	0.12	77.0	EXV227M035(1)9PAA
35	44	330	10 x 10.2	12	850	0.12	115.5	EXV337M035(1)9PAA
35	44	4.7	4 x 5.4	12	90	1.93	3.0	EXV475M035(1)9BAA
35	44	10	5 x 5.4	12	160	1.00	3.5	EXV106M035(1)9DAA
35	44	22	5 x 5.4	12	160	1.00	7.7	EXV226M035(1)9DAA
35	44	33	6.3 x 5.4	12	240	0.52	11.6	EXV336M035(1)9GAA
35	44	47	6.3 x 7.7	12	280	0.34	16.5	EXV476M035(1)9HAA
35	44	68	6.3 x 7.7	12	280	0.34	23.8	EXV686M035(1)9HAA
35	44	100	8 x 10.2	12	600	0.16	35.0	EXV107M035(1)9MAA
50	63	47	10 x 10.2	12	670	0.34	23.5	EXV476M050(1)9PAA
50	63	68	10 x 10.2	12	670	0.34	34.0	EXV686M050(1)9PAA
50	63	100	10 x 10.2	12	670	0.34	50.0	EXV107M050(1)9PAA
50	63	150	10 x 10.2	12	670	0.34	75.0	EXV157M050(1)9PAA
50	63	220	10 x 10.2	12	670	0.34	110.0	EXV227M050(1)9PAA
50	63	330	12.5 x 13.5	12	700	0.12	165	EXV337M050(1)9RAA
50	63	1	4 x 5.4	12	60	5.00	3.0	EXV105M050(1)9BAA
50	63	2.2	4 x 5.4	12	60	5.00	3.0	EXV225M050(1)9BAA
50	63	3.3	4 x 5.4	12	60	5.00	3.0	EXV335M050(1)9BAA
50	63	4.7	5 x 5.4	12	95	4.00	3.0	EXV475M050(1)9DAA
50	63	10	6.3 x 5.4	12	140	2.60	5.0	EXV106M050(1)9GAA
50	63	22	6.3 x 7.7	12	230	1.30	11.0	EXV226M050(1)9HAA
50	63	33	8 x 10.2	12	350	0.50	16.5	EXV336M050(1)9MAA
80	100	120	12.5 x 13.5	12	400	0.45	96.0	EXV127M080(1)9RAA
80	100	150	12.5 x 13.5	12	400	0.60	120.0	EXV157M080(1)9RAA
80	100	220	12.5 x 16.0	10	520	0.60	176.0	EXV227M080(1)9SAA
Rated Voltage	Surge Voltage	Rated Capacitance	Case Size	DF	RC	Z	LC	Part Number

<sup>(1)</sup> Insert Electrical Parameters code. See Part Number System for available options.



## **Mounting Positions (Safety Vent)**

In operation, electrolytic capacitors will always conduct a leakage current, which causes electrolysis. The oxygen produced by electrolysis will regenerate the dielectric layer but, at the same time, the hydrogen released may cause the internal pressure of the capacitor to increase. The overpressure vent, or safety vent, ensures that the gas can escape when the pressure reaches a certain value. All mounting positions must allow the safety vent to work properly.

## Installing

- As a general principle, lower-use temperatures result in a longer, useful life of the capacitor. For this reason, it should be
  ensured that electrolytic capacitors are placed away from heat-emitting components. Adequate space should be allowed
  between components for cooling air to circulate, particularly when high ripple current loads are applied. In any case, the
  maximum category temperature must not be exceeded.
- Do not deform the case of the capacitors or use capacitors with a deformed case.
- Verify that the connections of the capacitors are able to insert on the board without excessive mechanical force.
- If the capacitors require mounting through additional means, the recommended mounting accessories shall be used.
- Verify the correct polarization of the capacitor on the board.
- · Verify that the space around the pressure relief device is according to the following guideline:

Case Diameter	Space Around Safety Vent
≤ 16 mm	> 2 mm
> 16 to ≤ 40 mm	> 3 mm
> 40 mm	> 5 mm

It is recommended that capacitors always be mounted with the safety device uppermost or in the upper part of the capacitor.

- If the capacitors are stored for a long time, the leakage current must be verified. If the leakage current is superior to the value listed in this catalog, the capacitors must be reformed. In this case, they can be reformed by application of the rated voltage through a series resistor approximately 1 k $\Omega$  for capacitors with  $V_R \le 160$  V (5 W resistor) and 10 k $\Omega$  for the other rated voltages.
- In the case of capacitors connected in a series, a suitable voltage sharing must be used.

  In the case of balancing resistors, the approximate resistance value can be calculated as: R = 60/C.

KEMET recommends, nevertheless, to ensure that the voltage across each capacitor does not exceed its rated voltage.



#### Electrical Ratings: Capacitance (ESC)



Simplified equivalent circuit diagram of an electrolytic capacitor

The capacitive component of the equivalent series circuit, (equivalent series capacitance - ESC), is determined by applying an alternate voltage of  $\leq 0.5$  V at a frequency of 120 or 100 Hz and 20°C (IEC 384-1, 384-4).

#### **Temperature Dependence of the Capacitance**

Capacitance of an electrolytic capacitor depends upon temperature: with decreasing temperature the viscosity of the electrolyte increases, thereby reducing its conductivity.

Capacitance will decrease if temperature decreases. Furthermore, temperature drifts cause armature dilatation and, therefore, capacitance changes (up to 20% depending on the series considered, from 0 to 80°C). This phenomenon is more evident for electrolytic capacitors than for other types.


#### **Frequency Dependence of the Capacitance**

Effective capacitance value is derived from the impedance curve, as long as impedance is still in the range where the capacitance component is dominant.

C = 
$$\frac{1}{2\pi \text{ fZ}}$$
 C = capacitance (F)  
f = frequency (Hz)  
Z = impedance ( $\Omega$ )

#### Dissipation Factor tan $\delta$ (DF)

Dissipation Factor  $\tan \delta$  is the ratio between the active and reactive power for a sinusoidal waveform voltage. It can be thought of as a measurement of the gap between an actual and ideal capacitor.



Tan  $\delta$  is measured with the same set-up used for the series capacitance ESC.

Tan  $\delta = \omega \times ESC \times ESR$  where:

ESC = Equivalent series capacitance


ESR = Equivalent series resistance



#### **Equivalent Series Inductance (ESL)**

Equivalent series inductance or self inductance results from the terminal configuration and internal design of the capacitor.

Capacitor Equivalent Internal Circuit




#### **Equivalent Series Resistance (ESR)**

Equivalent series resistance is the resistive component of the equivalent series circuit. ESR value depends on frequency and temperature, and is related to the tan  $\delta$  by the following equation:

Tolerance limits of the rated capacitance must be taken into account when calculating this value.

#### Impedance (Z)

Impedance of an electrolytic capacitor results from a circuit formed by the following individual equivalent series components:



C<sub>o</sub> = Aluminum oxide capacitance (surface and thickness of the dielectric.)

 $R_e$  = Resistance of electrolyte and paper mixture (other resistances not depending on the frequency are not considered: tabs, plates, etc.)

C<sub>a</sub> = Electrolyte soaked paper capacitance.


L = Inductive reactance of the capacitor winding and terminals.

Impedance of an electrolytic capacitor is not a constant quantity that retains its value under all conditions; it changes depending on frequency and temperature.

Impedance as a function of frequency (sinusoidal waveform) for a certain temperature can be represented as follows:




#### Impedance (Z) cont.



- · Capacitive reactance predominates at low frequencies.
- With increasing frequency, capacitive reactance  $Xc = 1/\omega C_o$  decreases until it reaches the order of magnitude of electrolyte resistance  $R_o(A)$
- At even higher frequencies, resistance of the electrolyte predominates: Z = R<sub>a</sub> (A B)
- When the capacitor's resonance frequency is reached ( $\omega_0$ ), capacitive and inductive reactance mutually cancel each other  $1/\omega C_p = \omega L$ ,  $\omega_0 = 1/SQR(LC_p)$
- Above this frequency, inductive reactance of the winding and its terminals (XL = Z = ωL) becomes effective and leads to an increase in impedance

Generally speaking, it can be estimated that  $C_a \approx 0.01 C_o$ .

Impedance as a function of frequency (sinusoidal waveform) for different temperature values can be represented as follows (typical values):



 $R_{_{\rm e}}$  is the most temperature-dependent component of an electrolytic capacitor equivalent circuit. Electrolyte resistivity will decrease if temperature rises.

In order to obtain a low impedance value throughout the temperature range,  $R_e$  must be as little as possible. However,  $R_e$  values that are too low indicate a very aggressive electrolyte, resulting in a shorter life of the electrolytic capacitor at high temperatures. A compromise must be reached.



#### **Leakage Current (LC)**


Due to the aluminum oxide layer that serves as a dielectric, a small current will continue to flow even after a DC voltage has been applied for long periods. This current is called leakage current.

A high leakage current flows after applying voltage to the capacitor then decreases in a few minutes, for example, after prolonged storage without any applied voltage. In the course of continuous operation, the leakage current will decrease and reach an almost constant value.

After a voltage-free storage the oxide layer may deteriorate, especially at a high temperature. Since there are no leakage currents to transport oxygen ions to the anode, the oxide layer is not regenerated. The result is that a higher than normal leakage current will flow when voltage is applied after prolonged storage.

As the oxide layer is regenerated in use, the leakage current will gradually decrease to its normal level.

The relationship between the leakage current and voltage applied at constant temperature can be shown schematically as follows:



#### Where:

 $V_{\epsilon}$  = Forming voltage

If this level is exceeded, a large quantity of heat and gas will be generated and the capacitor could be damaged.

 $V_p$  = Rated voltage

This level represents the top of the linear part of the curve.

V<sub>s</sub> = Surge voltage

This lies between  $V_R$  and  $V_F$ . The capacitor can be subjected to  $V_S$  for short periods only.

Electrolytic capacitors are subjected to a reforming process before acceptance testing. The purpose of this preconditioning is to ensure that the same initial conditions are maintained when comparing different products.

#### **Ripple Current (RC)**

The maximum ripple current value depends on:

- Ambient temperature
- Surface area of the capacitor (heat dissipation area)  $\tan\delta$  or ESR
- Frequency

The capacitor's life depends on the thermal stress.



#### **Frequency Dependence of the Ripple Current**

ESR and, thus, the tan  $\delta$  depend on the frequency of the applied voltage. This indicates that the allowed ripple current is also a function of the frequency.

#### **Temperature Dependence of the Ripple Current**

The data sheet specifies maximum ripple current at the upper category temperature for each capacitor.

#### **Expected Life Calculation**

Expected life depends on operating temperature according to the following formula:  $L = Lo \times 2^{(To-T)/10}$  Where:

L: Expected life


Lo: Load life at a maximum permissible operating

temperature

T: Actual operating temperature

To: Maximum permissible operating temperature

This formula is applicable between 40°C and To.






## **Packaging Quantities**

Size Code	Diameter (mm)	Length (mm)	Reel Quantity	Box Quantity (4 Reels per box)
9B	4.0	5.4	2,000	10,000
9D	5.0	5.4	1,000	10,000
9G	6.3	5.4	1,000	10,000
9H	6.3	7.7	1,000	10,000
9M	8.0	10.2	500	4,000
9P	10.0	10.2	500	4,000
9R	12.5	13.5	200	1,200
98	12.5	16.0	200	1,200

## **Standard Marking for Surface Mount Types**



Note: 6.3 V rated voltage shall be marked as 6 V, but 6.3 V shall be assured.

#### **Date Code Explanation**

#### Y = Year

Code	6	7	8	9	0	1	2	3	4	5
Year	2016	2017	2018	2019	2020	2021	2022	2023	2024	2025

#### M = Month


Code	1	2	3	4	5	6	7	8	9	Α	В	С
Month	1	2	3	4	5	6	7	8	9	10	11	12

#### S = AEC-Q200 Certified

1	2	3	4	5	6	7
8	9	Α	В	С	D	E
F	G	Н	I	J	K	L
М	N	0	Р	Q	R	S
Т	U	٧	W	Х	Υ	Z



### **Construction**






## **Soldering Process**

The soldering conditions should be within the specified conditions below:

Do not dip the capacitor body into the melted solder. Flux should only be applied to the capacitor terminals.



Vapor heat transfer systems are not recommended. The system should be thermal, such as infra-red radiation or hot blast Observe the soldering conditions as shown below.

Do not exceed these limits and avoid repeated reflowing

## **Reflow Soldering**

	Temperature (°C)	Maximum Time (Seconds)		
T0	20 - 140	60		
Pre-heat	140 - 180	150		
T1	180 - 140	100		
T2	> 200	60		
T3	230	20		

# **Lead-Free Reflow Soldering**

	Temperature (°C)	Maximum Time (Seconds)	
T0	20 - 160	60	
Pre-heat	160 - 190	120	
T1	190 - 180	90	
T2	> 220	60	

## **Lead-Free Reflow Soldering cont.**


	Size	Temperature (°C)	Maximum Time (Seconds)		
T3	Φ4 ~ Φ5 (4 - 50 V)	250	10		
13	Ψ4 ~ Ψ3 (4 - 30 ۷)	260	5		
	Φ6.3 ~ Φ10 (4 - 50 V)	250	5		
	Ф4 ~ Ф10 (63 - 100 V)	250	5		


	Size	Temperature (°C)	Maximum Time (Seconds)
	Ф4 ~ Ф5	250	10
	(4 - 50 V)	260	5
Т3	Ф6.3 ~ Ф10 (4 - 50 V)	250	5
	Φ4 ~ Φ10 (63 - 100 V)	250	5
	≥ Ф12.5	250	5




## **Lead Taping & Packaging**

		Reel	
Case Size (mm)	D	Н	W
	±0.2	±0.8	±1.0
4 x 5.4		21	14
5 x 5.4		21	14
6.3 x 5.4		21	18
6.3 x 5.8	200	21	18
6.3 x 7.7	380	21	18
8 x 6.2		21	18
8 x 10.2		21	26
10 x 10.2		21	26





## **Taping for Automatic Insertion Machines**



Dimensions (mm)	W	A	В	P <sub>0</sub>	<b>P</b> <sub>1</sub>	P <sub>2</sub>	F	D <sub>0</sub>	E	t <sub>i</sub>	t <sub>2</sub>
Tolerance	Nominal	Nominal	Nominal	±0.1	±0.1	±0.1	Nominal	±0.1	Nominal	Nominal	Nominal
4 x 5.4	12	4.7	4.7	4	8	2	5.5	1.5	1.75	0.4	5.8
5 x 5.4	12	5.7	5.7	4	12	2	5.5	1.5	1.75	0.4	5.8
6.3 x 5.4	16	7.0	7.0	4	12	2	7.5	1.5	1.75	0.4	5.8
6.3 x 7.7	16	7.0	7.0	4	12	2	7.5	1.5	1.75	0.4	5.8
8 x 6.2	16	8.7	8.7	4	12	2	7.5	1.5	1.75	0.4	6.8
8 x 10.2	24	8.7	8.7	4	16	2	11.5	1.5	1.75	0.4	11.0
10 x 10.2	24	10.7	10.7	4	16	2	11.5	1.5	1.75	0.4	11.0
12.5 x 13.5	32	13.4	13.4	4	24	2	14.2	1.5	1.75	0.5	14.0
12.5 x 16	32	13.4	13.4	4	24	2	14.2	1.5	1.75	0.5	17.5
16 x 16.5	44	17.5	17.5	4	28	2	20.2	1.5	1.75	0.5	17.5



#### **Construction Data**

The manufacturing process begins with the anode foil being electrochemically etched to increase the surface area and then "formed" to produce the aluminum oxide layer. Both the anode and cathode foils are then interleaved with absorbent paper and wound into a cylinder. During the winding process, aluminum tabs are attached to each foil to provide the electrical contact.

The deck, complete with terminals, is attached to the tabs and then folded down to rest on top of the winding. The complete winding is impregnated with electrolyte before being housed in a suitable container, usually an aluminum can, and sealed. Throughout the process, all materials inside the housing must be maintained at the highest purity and be compatible with the electrolyte.

Each capacitor is aged and tested before being sleeved and packed. The purpose of aging is to repair any damage in the oxide layer and thus reduce the leakage current to a very low level. Aging is normally carried out at the rated temperature of the capacitor and is accomplished by applying voltage to the device while carefully controlling the supply current. The process may take several hours to complete.

Damage to the oxide layer can occur due to variety of reasons:

- Slitting of the anode foil after forming
- Attaching the tabs to the anode foil
- Minor mechanical damage caused during winding

A sample from each batch is taken by the quality department after completion of the production process. This sample size is controlled by the use of recognized sampling tables defined in BS 6001.


The following tests are applied and may be varied at the request of the customer. In this case the batch, or special procedure, will determine the course of action.


#### Electrical:

- · Leakage current
- Capacitance
- ESR
- Impedance
- Tan Delta

#### Mechanical/Visual:

- Overall dimensions
- Torque test of mounting stud
- · Print detail
- Box labels
- Packaging, including packed quantity







### **KEMET Electronics Corporation Sales Offices**

For a complete list of our global sales offices, please visit www.kemet.com/sales.

#### **Disclaimer**

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## KEMET:

EXV227M035A9PAA	EXV337M025A9PAA	EXV107M050A9PAA	EXV477M016A9MAA	EXV227M025A9MAA
EXV107M035A9MAA	EXV226M050A9HAA	EXV476M016A9GAA	EXV107M016A9GAA	EXV476M025A9GAA
EXV106M035A9DAA	EXV106M025A9BAA	EXV227M050A9PAA	EXV226M016A9BAA	EXV476M050A9PAA
EXV106M050A9GAA	EXV336M050A9MAA	EXV107M025A9HAA	EXV105M050A9BAA	EXV227M6R3A9HAA
EXV226M010A9BAA	EXV687M6R3A9PAA	EXV227M010A9MAA	EXV687M010S9PAA	EXV335M050A9BAA
EXV336M035S9GAA	EXV477M016S9PAA	EXV686M025S9HAA	EXV686M035S9HAA	EXV687M6R3S9PAA
EXV476M6R3A9DAA	EXV476M016S9GAA	EXV157M6R3S9HAA	EXV475M035S9BAA	EXV476M035S9HAA
EXV107M050S9PAA	EXV157M010S9HAA	EXV226M025S9DAA	EXV337M010S9MAA	EXV226M6R3S9BAA
EXV105M050S9BAA	EXV107M6R3S9GAA	EXV226M016S9DAA	EXV337M6R3S9MAA	EXV687M016S9PAA
EXV107M025S9HAA	EXV336M6R3A9BAA	EXV106M050S9GAA	EXV107M035S9MAA	EXV687M016A9PAA
EXV225M050A9BAA	EXV226M035A9DAA	EXV336M035A9GAA	EXV157M050A9PAA	EXV686M035A9HAA
EXV227M6R3S9HAA	EXV336M6R3S9BAA	EXV335M050S9BAA	EXV477M010S9PAA	EXV476M010S9GAA
EXV336M010A9DAA	EXV476M6R3S9DAA	EXV336M016S9GAA	EXV108M6R3S9PAA	EXV336M025S9GAA
EXV475M050S9DAA	EXV476M025S9GAA	EXV477M025A9PAA	EXV337M016A9MAA	EXV106M035S9DAA
EXV108M010S9PAA	EXV226M010S9BAA	EXV337M025S9PAA	EXV227M016S9MAA	EXV108M010A9PAA
EXV337M016S9MAA	EXV227M035S9PAA	EXV336M050S9MAA	EXV336M010S9DAA	EXV477M6R3S9MAA
EXV476M050S9PAA	EXV477M025S9PAA	EXV157M010A9HAA	EXV157M025A9MAA	EXV106M016S9BAA
EXV476M035A9HAA	EXV226M050S9HAA	EXV108M6R3A9PAA	EXV475M035A9BAA	EXV475M050A9DAA
EXV337M035S9PAA	EXV686M050S9PAA	EXV157M050S9PAA	EXV226M035S9DAA	EXV106M025S9BAA
EXV227M050S9PAA	EXV157M016S9MAA	EXV225M050S9BAA	EXV227M010S9MAA	EXV227M025S9MAA