

Coaxial Cable Connector 11_MCX-50-2-21/133_N

Description

Straight cable plug

Interface standards

IEC 60169-36_CECC 22220



Technical Data

Electrical Data

| | |
|--------------------------|-------|
| Impedance | 50 Ω |
| Interface frequency max. | 6 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | crimped |
| Outer contact | crimped |
| Weight | 0.0008 kg |

Environmental Data

| | |
|--|------------------|
| Operating temperature | -55 °C to 155 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|-----------------------------------|
| Centre contact | Brass | Gold Plating (Nickel underplated) |
| Outer contact | Copper Beryllium Alloy | SUCOPLATE (R) Plating |
| Body | Brass | SUCOPLATE (R) Plating |
| Insulator | PFA / PTFE | |
| Crimp ferrule | Copper | SUCOPLATE (R) Plating |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00066000 |
| Assembly instruction | DOC-0000223887 |

Ordering Information

| | |
|----------------------|-----------------------|
| Bulk 100 pcs package | 11_MCX-50-2-21/133_NH |
|----------------------|-----------------------|

Additional Information

| | |
|-----------------|---------------|
| Suitable cables | G_01130_HT-24 |
|-----------------|---------------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_MCX-50-2-21/133_NH](#)