

Coaxial Cable Connector 11_QMA-50-4-2/133_N

Description

Straight cable plug

Interface standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	18 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	31.5 dB	27 dB	22.5 dB

Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.0076 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00002188
Catalogue drawing	DCA-00200057
Assembly instruction	DOC-0000231592

Ordering Information

Bulk 100 pcs package	11_QMA-50-4-2/133_NH
Single package	11_QMA-50-4-2/133_NE

Additional Information

Suitable cables	S_04262_D, S_04262_D-03, SX_04272_D-02, SPUMA_240
-----------------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11_QMA-50-4-2/133_NH](#)