

Within Series Adaptor 34_MMCX-50-0-1/111_O

Description

Bulkhead adaptor jack/jack
MMCX jack (female) / MMCX jack (female)

Interface standard
Series MMCX - SUHNER-MMCX



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	6 GHz	
Frequency range	DC to 1.5 GHz	1.5 to 6 GHz
Return loss	≥ 30 dB	≥ 20 dB

Mechanical Data

Number of matings	500
Weight	0.0008 kg

Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - MMCX jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Interface - MMCX jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00013615
Mounting hole	DOU-00011744

Ordering Information

Single package	34_MMCX-50-0-1/111_OE
----------------	-----------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[34_MMCX-50-0-1/111_OE](#)