


## Standard Open Toroidal Transformers

### 50VA Open Style, with Leads. 230V Primary, Dual Secondaries

High quality open style toroidal transformers with a single 230V/50-60Hz primary winding. Twin secondary windings may be connected in series or parallel, or used independently



Primary 230V @ 50-60Hz  
Secondary: 2 x Vsec @ 25VA Each  
Suitable for Series/Parallel connection



Nuvotem Part Number	Full Load Vsec [V]	Rated Current per Sec [A]	No Load Vsec [V]	DC Resistance [Ohms] @ 25°C	DEKRA Certificate
0050P1-2-006	2 x 6	4.167	2 x 6.80	2 x 0.0914	2161054.01
0050P1-2-009	2 x 9	2.778	2 x 10.20	2 x 0.2139	2161054.01
0050P1-2-012	2 x 12	2.083	2 x 13.71	2 x 0.3977	2161054.01
0050P1-2-015	2 x 15	1.667	2 x 17.22	2 x 0.6411	2161054.01
0050P1-2-018	2 x 18	1.389	2 x 20.39	2 x 0.8519	2161054.01
0050P1-2-025	2 x 25	1.000	2 x 28.78	2 x 1.9135	2161054.02
0050P1-2-055	2 x 55	0.455	2 x 63.22	2 x 9.4110	2161054.02

Primary Winding	Input Voltage Range : 207V–253V (230V +/- 10%) @ 50/60Hz DC Resistance @ 25°C = Approx 49 Ohms		
Losses	Iron Losses	0.41 Watts approx	
	Copper Losses	8.35 Watts approx	
Temperature Class	Winding Wire (Primary & Secondary)	Class H (180°C)	
	Insulation between input and output	Class B (130°C)	
	Connection lead insulation	Class A (105°C)	
Standards	Approved to UL506 & UL5085 : File E215495 Approved to EN61558 : DEKRA Certificates 2161054.01 or 2161054.02 (see table above) Conforms to EN60065, VDE0550, BS415.		
Physical Data	Approximate Dimensions	Diameter	80mm*
		Height	33mm
	Approximate Weight	0.45 Kg	
Terminations	Primary	Flexible equipment wire UL Style 1569 (105°C), CSA Type TR-64 (90°C) Double-insulated over entire length with 105°C PVC tubings. 150mm Long, 10mm tinned ends.	
	Secondary	Solid copper conductors (extension of winding wire), insulated over their entire length with 105°C PVC tubing. 150mm Long, 10mm tinned ends.	
Mounting Hardware	Each transformer is supplied with a mounting kit, comprising: Neoprene Insulating disc                      2 pieces Dished Steel Washer                            1 piece		

**Regional Locations - Design, Manufacturing, Sales & Marketing**
**Talema Group Global Offices**
**North America**
**United States  
(Sales & Marketing)**

**Talema Group, LLC**  
 PO Box 935  
 900 Innovation Drive  
 Suite 120, Rolla  
 Missouri 65402  
 Tel: +1 573-303-3675  
 E-Mail:  
 sales@talema.com  
 Web: talema.com

**Asia**
**India  
(Design, Manufacturing, Sales & Marketing)**
**Administrative Office**

**Talema Electronic India Private Limited**  
 Door No. 221, 1st and 2nd Floor  
 KJ Plaza, Opp.to Vidya Mandir School  
 Meyanur Main Road  
 Salem - 636 004 Tamil Nadu INDIA.  
 Tel: +91 427 - 243 3100  
 Fax: +91 427 - 243 3109  
 E-Mail: talema@talemaindia.net  
 Web: talema.com

**Factory Premises**

**Talema Electronic India Private Limited**  
 No. 31 & 31, Electronic Industrial Estate  
 Suramangalam Post  
 Salem - 636 005 Tamil Nadu INDIA  
 Tel: +91 427 - 243 3000  
 E-Mail: talema@talemaindia.net  
 Web: talema.com

**Europe**
**Germany  
(Design, Sales & Marketing)**

**Talema Elektronik GmbH**  
 Sembdnerstr. 5  
 82110 Germering  
 Tel: +49 89 - 841 00 - 0  
 Fax: +49 89 - 841 00 25  
 E-Mail: info@talema.de  
 Web: talema.com

**Ireland  
(Design, Sales & Marketing)**

**Nuvotem TEO**  
 Units W & X, Gweedore Business Park  
 Derrybeg, Letterkenny, Co. Donegal  
 Tel: +353 (0) 74 95 48666  
 Fax: +353 (0) 74 95 48139  
 E-Mail: info@nuvotem.com  
 Web: talema.com

**Czech Republic  
(Design, Manufacturing, Sales & Marketing)**

**NT Magnetics s.r.o.**  
 Chebská 27  
 322 00 Plzeň  
 Tel: +420 377 - 338 351  
 Fax: +420 377 - 338 350  
 E-Mail: talema@talema.cz  
 Web: talema.com

**Locations of Talema Group Global Offices**
