

Part Number: 1503A

Audio Cable, #22-2c, TC, O/A Foil, CMR



Product Description

Audio Cable, Riser-CMR, 1-22 AWG stranded tinned copper pair with PVC insulation, Beldfoil® shield, drain, PVC jacket

Technical Specifications

Product Overview

Environmental Space:	Indoor - Riser
----------------------	----------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs
22	7x30	TC - Tinned Copper	0.0285 in	1

Conductor Count:	2
Total Number of Pairs:	1
Conductor Size:	22 AWG

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.0485 in	0.01 in

Color Chart

Number	Color
1	Black & Red

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	0.024 in	24	7x32

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.142 in	0.02 in
	0.142 in	

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR
14.7 Ohm/1000ft	14.7 Ohm/1000ft		18 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
53 pF/ft	97 pF/ft

Inductance

Nominal Inductance

0.18 µH/ft

Impedance

Nominal Characteristic Impedance

38 Ohm

Delay

Nominal Delay Nominal Velocity of Propagation (VP) [%]

1.5 ns/ft 66 %

Current

Max. Recommended Current [A]

2.9 Amps per conductor @ 25°C

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

UL Temp Rating:	60°C
Operating Temp Range:	-30°C To +90°C

Mechanical Characteristics

Bulk Cable Weight:	14 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius/Minor Axis:	1.5 in

Standards

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMG
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1666 Riser
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color
1503A 010U1000	Black
1503A 006U1000	Blue, Light
1503A 001U1000	Brown

1503A 008U1000	Gray
1503A N3UU1000	Green, Mil
1503A 003U1000	Orange
1503A 002U1000	Red
1503A 007U1000	Violet
1503A 009U1000	White
1503A 004U1000	Yellow

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.