SEALED, ILLUMINATED ROCKER SWITCHES

LOW COST, SNAP-IN ROCKER FOR WET & DUSTY ENVIRONMENTS

The K series rockers are rugged, high performance sealed switches designed for use under severe conditions found in marine, appliance, heavy equipment and industrial control applications. Sealed to IP68S with an optional panel gasket available.

The K1 series is offered in single pole configuration while the K2 series is available in single and double pole configurations. Both series offer illuminated models. Illumination can be independent or dependent of the switch position or a combination of both. A choice of red, green, clear or amber colored lenses are offered in illuminated models. Illumination options include incandescent, LED or neon light sources.

Mounting is simple and quick; snaps into panel from the front. The OTTO snap-in design supports a variety of panel thicknesses with just one cutout size specified.

A choice of models are offered to handle power levels to 16 amps, 1/2 HP and low level electronic switching applications.

OTTO can provide custom colors upon request. Value-added assemblies with wire leads are also available. Please consult the factory for assistance.

Features:

- Withstands direct water spray
- Watertight to IP68S
- Fits industry standard panel openings for drop-in replacement of panel sealed & unsealed switches
- Snap-in feature accommodates a wide range of panel cutouts
- Switches up to 16 amps
- UV & solvent resistant
- Withstands extreme shock & vibration
- Custom legends available
- 2 & 3-position, momentary & maintained action
- Incandescent, LED & neon illumination with independent & dependent light source options
- UL recognized & CSA certified
- Ignition protected
- RoHS/WEEE/Reach compliant





Single & Double Pole



		c Us				
Standard Character	istics/Ratings:					
ELECTRICAL RATINGS:						
Load	Sea Level @ 28VDC or 125/250VAC, 60Hz	Cycles				
Resistive	16A	25,000				
Resistive	10A	50,000				
Inductive	10A	25,000				
Lamp	5A	25,000				
Motor	0.5HP	25,000				
DWV	1050Vrms except across light terminals					
Low Level	10mA @ 30mV					
Electrical Life:	See Rating Chart					
LIGHTING:						
Light Source	Rating					
Incandescent	(VDC) 6V, 12V, 24V					
Neon	(VAC) 125V, 250V					
LED	(VDC) 2V, 6V, 12V, 24V					
Mechanical Life:	100,000 cycles					
Seal:	IP68S					
Operating Temp Range:	-30°C to +85°C					
MATERIALS:						
Case:	Thermoplastic					
Button:	Thermoplastic					
Base:	Thermoplastic					
Terminals/Contact:	Brass, silver alloy with sil	lver plate, gold flash for low level				
Terminal Hardware:	Screws and lockwashers provided when applicable K1/K2 series recommended Quick Connect terminals: AMP 60253-2 for 12-16 AWG AMP 42100-2 for 14-18 AWG					
Mounting Hardware:	None provided					

K1

SEALED, ILLUMINATED ROCKER SWITCHES

LOW COST, SNAP-IN ROCKER FOR WET & DUSTY ENVIRONMENTS

K1 PART NUMBER CODE X

Terminal Style/ Switch Rating

- A. Q.C./Std.
- B. Screw/Std.
- c. Solder/Std.
- D. Q.C./Low Level
- E. Screw/Low Level F. Solder/Low Level
- G. PC Pin/Std.
- H. PC Pin/Low Level

Actuator Color/Style

X


A. Red/Rocker

X

- B. Black/Rocker
- c. White/Rocker
- D. Red/Paddle
- E. Black/Paddle
- F. White/Paddle
- G. Red/Rocker Pinned
- H. Black/Rocker Pinned
- J. White/Rocker Pinned
- K. Red/Short Paddle Pinned
- L. Black/Short Paddle Pinned
- M. White/Short Paddle Pinned
- N. Red/Standard Paddle Pinned
- P. Black/Standard Paddle Pinned
- R. White/Standard Paddle Pinned
- T. Red/Short Paddle
- U. Black/Short Paddle
- v. White/Short Paddle

Switch Action/Circuit

	Position	Position	Position	Circuit		
	"A"	"B"	"C"			
A.	1-C	NONE	OFF	SPST		
B.	1-C	NONE	2-C	SPDT		
C.	(1-C)	NONE	OFF	SPST		
D.	(1-C)	NONE	2-C	SPDT		
E.	(1-C)	OFF	(2-C)	SPDT		
F.	1-C	OFF	2-C	SPDT		
G.	(1-C)	OFF	2-C	SPDT		
H.	OFF	NONE	2-C	SPST		
NOTE: () denotes momentary action						



Light Type

X


- A. No Light
- B. 6V Incandescent
- c. 12V Incandescent

Part Number Code Continued Below

- D. 24V Incandescent
- E. 125VAC Neon
- F. 250VAC Neon
- G. 2V Red LED
- H. 2V Green LED
- J. 2V Amber LED K. 6V Red LED
- L. 6V Green LED
- M.6V Amber LED
- N. 12V Red LED
- P. 12V Green LED
- Q. 12V Amber LED
- R. 24V Red LED S. 24V Green LED
- T. 24V Amber LED

K1 PART NUMBER CODE CONTINUED FROM ABOVE

K1 Continued



Position "A" Position "C" A. No Lens

- A. No Lens B. Red
- B. Red
- C. Green D. Amber
- C. Green D. Amber
- E. Clear
- E. Clear

Light/Circuit Location

X

A. No Light







D Independent Light ON in position "C"

Dependent Light ON in position "C" Wired to terms 2 & 4 G



ON in position Wired to terms 3 & 4

Dependent Light

ed to terms 2 & 4

at position "A" Wired to terms 3 & 4

Independent Light at position "A" Wired to terms 3 & 4


Independent Light Wired to terms 3 & 4

D = Dependent Light I = Independent Light

- LED anode (+) terminal number shown in bold.
- Light on OFF side must be independent.
- Contact factory for multiple light types in the same switch.

NOTES:


- No momentary switches with dependent lights.
- . Neon lamps only to be coded with clear or amber
- LED lenses must be clear or same color as LED.
- No dependent light in OFF position.
- All legends printed on actuators without lens(es) will be white except actuator codes C, F, J, M & R.
- · All legends printed on lenses will be white except on clear lens(es) will be black.
- K1 panel plugs available as shown on page 167.



X

ROCKER SWIT

LOW COST, SNAP-IN ROCKER FOR WET & DUSTY ENVIRONMENTS





MOUNTING HOLE:

PANEL THICKNESS RANGE OF .025 - .105 A GASKET IS RECOMMENDED,

0.031" THICKNESS = GASKET P/N 807039-2 0.062" THICKNESS = GASKET P/N 807039-1

PANEL THICKNESS RANGE OF .105 - .187 W/O GASKET PANEL OPENING: MIN. TYP. MAX.
WIDTH 480 .515 .550 WIDTH .480 .515 LENGTH 1.072 1.099 1.125





TERMINAL STYLES (.032 THICK)						
SCREW	QUICK CONNECT	SOLDER	P.C. PIN			
#6-32 THD 7	Ø.08	Ø.11 ———————————————————————————————————	.25			