

SPECIFICATION

Part No. : **TG.22.0222**

Product Name : 2G/3G Penta-Band Cellular Connector Mount Monopole Antenna

For Sierra Wireless Airlink GL Series Module

824MHz~2170MHz

Features : Omni-Directional

Robust and Compact

OdBi Gain on lower bands, 4dBi on higher bands

FME(F) Right Angle 45*24.7*7.8 mm RoHS Compliant





1. INTRODUCTION

The TG.22.0222 824MHz to 2170MHz monopole antenna is a quality robust antenna with high gain in small form factor.

Connection is made via right angle FME(F) connector with a hardened TPEE casing, this antenna is the ideal for remote monitoring devices or telematics applications. The TG.22.0222 antenna has been tuned specifically for optimum efficiency when connected directly to the Sierra Wireless Airlink GL series programmable module.

2. SPECIFICATION

ELECTRICAL								
Standard	GSM Penta-Band							
Operation Frequency (MHz)	824-896	880-960	1710-1880	1850-1990	1920-2170			
Polarization	Linear							
Impedance	50 ohm							
VSWR	3:1	3:1	2:1	2:1	2:1			
Return Loss (dB)	<-5dB	<-8dB	<-10dB	<-10dB	<-10dB			
Efficiency (%)	51.37	49.71	74.64	80.57	76.56			
Gain (dBi)	-0.04	-0.03	3.98	4.61	4.61			
Average Gain (dB)	-2.91	-3.07	-1.28	-0.94	-1.17			
Max Input Power			5W					


^{*} The TG.22.0222 antenna performance was measured on a 62*46.5 mm evaluation board

MECHANICAL					
Dimensions (mm)	45x24.7x.7.8				
Required Space (mm)	45x24.7x.7.8				
Material	TPEE				
Connector	FME(F)RA				
Weight	0.05Kg				
Recommended Torque for Mounting	0.78N·m				
Max Torque for Mounting	1.47N⋅m				

ENVIRONMENTAL					
Operation Temperature	-40°C to 85°C				
Storage Temperature	-40°C to 85°C				
Relative Humidity	40% to 95%				
RoHs Compliant	Yes				



3. TEST SET UP







Figure 1. Impedance measurements (left hand) and peak gain, efficiency and radiation pattern measurements (right hand).

4. ANTENNA PARAMETERS

4.1. Return Loss






4.2. Efficiency




4.3. Peak Gain






4.4. Average Gain






5. Antenna Radiation Patterns

5.1. 2D Radiation pattern





XZ-Plane





YZ-Plane





Figure 6. 2D Radiation Pattern of the TG.22 Antenna.




6. Mechanical Drawing



	Name	P/N	Materlal	Finish	QTY
1	Antenna Housing	000111F030002A	TPEE	Black	1
2	FME(F) RA	202513J000002A	Brass	Ni Plated	1

Figure 7. Mechanical Drawings of the TG.22



62mm

Figure 8. TG.22 Antenna EVB



7. Installation Guide



Recommended Torque for Mounting 0.78N·m Maximum Torque for Mounting 1.47N·m



8. Packaging

- 1pcs TG.22 antenna per small PE bag (74*42mm)(Weight 0.05kg)
 100 small PE bags put in one big PE bag. Final package will have 100pcs TG.22 antennas in big PE bag (263*172mm)

