Datasheet revision 1.0 www.chipquik.com

Smooth Flow™ Solder Paste No-Clean Sn42/Bi57/Ag1 T4 (15g Syringe)

Clear residue

Dispense grade

Low voiding

Product Highlights

Smooth Flow[™] Technology

Developed with a lower density flux vehicle for better shear spread and improved flow during heating

Printing speeds up to 125mm/sec Long stencil life, Wide process window Halogen Free (EN14582 test method)

Specifications

Alloy: Sn42/Bi57/Ag1

Mesh Size: T4
Micron (µm) Range: 20-38

Flux Type: Synthetic No-Clean

Flux Classification: ROL0

Metal Load: 86.75% Metal by Weight

Melting Point: 137°C (279°F)
Packaging: 5cc/15g Syringe

Shelf Life: Refrigerated >12 months, Unrefrigerated >6 months *See notes below:

No. of the last of

Excellent wetting compatibility on most board finishes

Compatible with enclosed print heads

RoHS 3 and REACH compliant

*Shelf Life Notes: Chip Quik® solder paste is good past its quoted shelf life, regardless of refrigeration. Before use, visually inspect the solder paste to ensure it is not dried out or clumpy, or check stencil release. If stored in a jar, stir the product thoroughly for 2-3 minutes before inspection and use.

Chip Quik® solder paste is manufactured using Made in USA high quality synthetic flux and precision atomized metal powder. Chip Quik® solder paste is guaranteed for 12 months from date of manufacture, regardless of refrigeration. If you have any issues with our solder paste, please contact Chip Quik® directly for no charge warranty replacement. Please retain original bill of sale, and solder paste in original container as we may request its return for internal R&D testing purposes.

Printer Operation

Print Speed: 25-125mm/sec

Squeegee Pressure: 70-250g/cm of blade

Under Stencil Wipe: Once every 10-25 prints, or as necessary

Stencil Life

>8 hours @ 20-50% RH 22-28°C (72-82°F) >4 hours @ 50-70% RH 22-28°C (72-82°F)

Stencil Cleaning

Automated stencil cleaning systems for both stencil and misprinted boards. Manual cleaning using isopropyl alcohol (IPA).

Storage and Handling


Refrigerate at 3-8°C (37-46°F). Do not freeze. Allow 4 hours for solder paste to reach an operating temperature of 20-25°C (68-77°F) before use.

Transportation

This product has no shipping restrictions. Shipping below 0°C (32°F) or above 25°C (77°F) for normal transit times by ground or air will not impact this product's stated shelf life.

Recommended Profile

Reflow profile for Sn42/Bi57/Ag1 solder assembly, designed as a starting point for process optimization.



Test Results

rest Results		
Test J-STD-004 or other	Test Requirement	Result
requirements as stated		
Copper Mirror	IPC-TM-650: 2.3.32	L: No breakthrough
Corrosion	IPC-TM-650: 2.6.15	L: No corrosion
Quantitative Halides	IPC-TM-650: 2.3.28.1	L: <0.05%
Electrochemical Migration	IPC-TM-650: 2.6.14.1	L: <1 decade drop (No-clean)
Surface Insulation Resistance 85°C,	IPC-TM-650: 2.6.3.7	L: ≥100MΩ (No-clean)
85% RH @ 168 Hours		
Tack Value	IPC-TM-650: 2.4.44	34g
Viscosity – Malcom @ 10 RPM/25°C	IPC-TM-650: 2.4.34.4	Print: 130-185, Dispense: 105-150
(x10 ³ mPa/s)		
Visual	IPC-TM-650: 3.4.2.5	Clear and free from precipitation
Conflict Minerals Compliance	Electronic Industry Citizenship Coalition (EICC)	Compliant
REACH Compliance	Articles 33 and 67 of Regulation (EC) No 1907/2006	Contains no substance >0.1% w/w that is listed as a SVHC or restricted for use in solder materials

Conforms to the following Industry Standards:

J-STD-004B, Amendment 1 (Solder Fluxes):	Yes
J-STD-005A (Solder Pastes):	Yes
J-STD-006C, Amendments 1 & 2 (Solder Alloys and Fluxed/Non-Fluxed Solders):	Yes
RoHS 3 Directive (EU) 2015/863:	Yes