



广州市番禺奥迪威电子有限公司

Audiowell Electronics (Guangzhou) Co., Ltd.

地址: 中国广东省广州市番禺区迎宾路东升工业区 邮政编码: 511400
 Add: Dongsheng Industrial Park, Yingbin Road, Panyu, Guangzhou 511400, China
 Tel: +86-20-84802041 84802405 84871596 34516786 Fax: 84665207




超声波换能片

Ultrasonic Piezoelectric Transducer

- 1、品名(Name): **HN0037-001**
- 2、产品型号(Model): **AW11Y20100B**
- 3、性能参数(Electrical specification):

项目 Item	单位 Unit	标准 Standard	测试条件(Test condition): T=25°C
厚向谐振频率(Ft) Thick resonant frequency	MHz	2.25±0.1	Agilent 4294A
谐振阻抗(R) Resonant impedance	Ω	≤2.0	Agilent 4294A
静电容量(C ₀) Static capacitance	pF	4100±20%	数字电桥 1000Hz/1V Digital electric bridge At 1000Hz/1V
机电耦合系数(K _p) Electrical-mechanical coupling coefficient		≥0.53	阻抗分析仪 Impedance analyzer

- 4、外观尺寸(Appearance and dimensions): 计量单位(Unit): mm



- 5、包装 (Package):

片/箱 PCS	包装盘 008(cm) Size	包装箱 037(cm) (外尺寸) Size	毛重(Kg) Gross weight	净重(Kg) Net weight
4500	34.3*27.0*3.0	36.0*28.5*14.0	11.2	9.7

制作/日期 Accomplished by / Date	<i>[Signature]</i> / 2013.2.18	确认/日期 Approved by / Date	
---------------------------------	--------------------------------	-----------------------------	--