




PRODUCT NUMBER	DIM A	DIM B	NOTES
84620-101	10.00	11.88	TOOLED
84620-101LF	10.00	11.88	
84620-102	22.00	23.88	NOT TOOLED
84620-103	34.00	35.88	
84620-104	46.00	47.88	
84620-105	58.00	59.88	
84620-106	70.00	71.88	

NOTES:

- SEE APPLICATION SPECIFICATION GS-20-010 FOR INFORMATION ON AVAILABLE TOOLING, CIRCUIT BOARD DESIGN CONSIDERATIONS, REPAIR PROCEDURES AND PRODUCT OFFERINGS.
- UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5, 1994.
- HOUSING MATERIAL: LIQUID CRYSTAL POLYMER, 30% GLASS FILLED, FLAME RETARDANT PER UL 94-V0.
- TEMPERATURE RANGE: -55°C TO +105°C.
- THE PRODUCTS WHERE THE PART NUMBERS END IN LF AND NON LF PARTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260° FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN. FOR LEAD FREE PART NUMBERS, ADD "LF" SUFFIX. EXAMPLE: 84620-101LF.



mat'l code SEE NOTE 3				tolerances unless otherwise specified		CUSTOMER	FCj www.fciconnect.com	
ltr	ecn no.	dr	date	linear	0.X ±0.3	projection	title	
A	V21194	TAB	2002-07-22		0.XX ±0.13		VERTICAL SIGNAL HDR SHROUD	
B	V06-0107	DAI	2006-02-22	angles	0.XXX ±0.051	MM	5 ROW, PRESS-FIT, STANDARD	
C	V06-0544	DCH	2006-06-12		0° ±2°		product family METRAL 1000/2000	
D	V07-0693	HTB	2007-11-27	dr	T.BRUNGARD	2002-07-17	code	213
				enr	J. VOLSTORF	2001-02-25	size	dwg no
				chr	M. STRAWSER	2002-07-17	A	84620
				appd	M. STRAWSER	2002-07-17	scale	1 of 1
							2:1	
sheet index	revision sheet	D						
		I						



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCj. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCj. Copyright FCj.