

# IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL



ABM12W SERIES

1.6 x 1.2 x 0.4mm



RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE

## FEATURES

- Optimized for energy saving wearables and IoT applications
- Plated at exceptionally low plating capacitance, as low as 4pF, with optimized ESR
- 0.4 mm max height ideally suited for height constrained designs
- Seam sealed for longterm reliability


## APPLICATIONS

- Wearables
- Internet of Things (IoT)
- Bluetooth/Bluetooth Low Energy (BLE)
- Wireless modules
- Machine-to-machine (M2M) connectivity
- Ultra-low power MCU
- Near Field Communication (NFC)
- ISM Band

## STANDARD SPECIFICATIONS

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency Range	24.0000		52.0000	MHz	
Operation Mode	Fundamental				
Operating Temperature Range	-40		+125	°C	See options
Storage Temperature	-55		+125	°C	
Frequency Tolerance @ +25°C	-10		+10	ppm	See options
Frequency Stability over the Operating Temperature ( ref. to +25°C)	-10		+10	ppm	See options
Equivalent series resistance (R1) (over -40°C to +125°C)		< 90	150	Ω	24.0000 – 31.9999MHz
		< 80	100		32.0000 – 36.9999MHz
		< 60	80		37.0000 – 52.0000MHz
Shunt capacitance (C0)		< 1.0	2.0	pF	
Load capacitance (CL)		4.0		pF	See options
Drive Level		10	100	μW	
Aging (1 year)	-2		+2	ppm	@ 25°C±3°C
Insulation Resistance	500			MΩ	@ 100Vdc ± 15V

# IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL



1.6 x 1.2 x 0.4mm



RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE

ABM12W SERIES

## OPTIONS AND PART IDENTIFICATION (NOTE 1)

Note 1: Contact Abracon for part number requests with carrier frequency callouts up to 5 & 6 digit accuracy after the decimal.

ABM12W- [ ] MHz - [ ] - [ ] - [ ] - [ ] - [ ]

**Frequency in MHz**  
Please specify the Frequency in MHz out to **4 digit** accuracy after the decimal.  
(e.g. 16.0000MHz)

Load Capacitance (pF)
8: 8pF
7: 7pF
6: 6pF
4: 4pF

**Custom ESR**  
if other than standard  
R □: Specify a value in Ω (e.g.: R70)

Packaging
Blank: Bulk
T3: 3kpcs / reel

Operating Temp.
I: 0°C ~ 50°C
E: 0°C ~ +70°C
B: -20°C ~ +70°C
C: -30°C ~ +70°C
N: -30°C ~ +85°C
D: -40°C ~ +85°C
J: -40°C ~ +105°C (*)
K: -40°C ~ +125°C (*)

Freq. Tolerance
1: ± 10 ppm
7: ± 15 ppm
2: ± 20 ppm
3: ± 25 ppm
4: ± 30 ppm
5: ± 50 ppm

Freq. Stability
U: ± 10 ppm (*)
G: ± 15 ppm (**)
X: ± 20 ppm (**)
W: ± 25 ppm (**)
Y: ± 30 ppm (**)
H: ± 35 ppm (**)
Z: ± 50 ppm
Q: ± 100 ppm

(\*) Only offered @ Freq. Stability options: Z & Q.


Contact ABRACON for tighter Frequency Stability.

(\*) Only offered @ Operating Temp. Range options: I, E, & B

(\*\*) Only offered @ Operating Temp. Range options: I, E, B, C, N, & D

Contact ABRACON for wider Operating Temp. Range.

# IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL



ABM12W SERIES



1.6 x 1.2 x 0.4mm





RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE


## TYPICAL FREQUENCY Vs. TEMPERATURE CHARACTERISTICS



## TYPICAL ESR (EQUIVALENT SERIES RESISTANCE) Vs. TEMPERATURE CHARACTERISTICS



# IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL



ABM12W SERIES


1.6 x 1.2 x 0.4mm






RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE

## TYPICAL FREQUENCY TOLERANCE DISTRIBUTION (AT 25°C ± 3°C)



## TYPICAL ESR DISTRIBUTION (AT 25°C ± 3°C)



# IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL



ABM12W SERIES


1.6 x 1.2 x 0.4mm



RoHS/RoHS II Compliant





MSL = N/A: NOT APPLICABLE

## SPICE MODELS (BASED ON TYPICAL VALUES AT 25°C ± 3°C)



<b>Frequency: 24.0000MHz</b> <b>Plating Load: 4pF</b>				<b>Frequency: 24.0000MHz</b> <b>Plating Load: 6pF</b>			
C0	=	0.58	pF	C0	=	0.49	pF
R1	=	54.20	Ω	R1	=	67.91	Ω
L1	=	52.83	mH	L1	=	50.66	mH
C1	=	0.83	fF	C1	=	0.87	fF
<b>Frequency: 40.0000MHz</b> <b>Plating Load: 4pF</b>				<b>Frequency: 40.0000MHz</b> <b>Plating Load: 6pF</b>			
C0	=	0.65	pF	C0	=	0.63	pF
R1	=	27.21	Ω	R1	=	22.99	Ω
L1	=	10.55	mH	L1	=	10.47	mH
C1	=	1.50	fF	C1	=	1.51	fF
<b>Frequency: 52.0000MHz</b> <b>Plating Load: 4pF</b>				<b>Frequency: 52.0000MHz</b> <b>Plating Load: 6pF</b>			
C0	=	0.63	pF	C0	=	0.64	pF
R1	=	18.03	Ω	R1	=	18.27	Ω
L1	=	5.74	mH	L1	=	5.50	mH
C1	=	1.63	fF	C1	=	1.70	fF


## MECHANICAL DIMENSIONS



Note:

Due to material availability the Chamfer could be located on pin #1, 2 or 4. Be advised that the Chamfer location has no impact on the electrical performance of the device.

# IoT OPTIMIZED LOW PROFILE QUARTZ CRYSTAL




ABM12W SERIES

1.6 x 1.2 x 0.4mm

RoHS/RoHS II Compliant

MSL = N/A: NOT APPLICABLE


## REFLOW PROFILE



Zone	Description	Temperature	Time
1	Preheat	$T_{SMIN} \sim T_{SMAX}$ 150°C ~ 180°C	60 ~ 120 sec.
2	Reflow	$T_L$ 217°C	45 ~ 90 sec.
3	Peak Heat	$T_p$ 260°C MAX	10 sec.

## PACKAGING

T3: Tape and reel (3,000 pcs/reel)



DIMENSIONS: mm

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## ABRACON:

[ABM12W-38.8800MHZ-8-B1U-T3](#) [ABM12W-33.3333MHZ-7-J1J-T3](#) [ABM12W-26.0000MHZ-6-B2U-T3](#) [ABM12W-37.0000MHZ-8-K1J-T3](#) [ABM12W-33.3333MHZ-7-K1Z-T3](#) [ABM12W-24.5454MHZ-8-K1Z-T3](#) [ABM12W-37.4000MHZ-4-J1Z-T3](#) [ABM12W-25.0000MHZ-7-J2J-T3](#) [ABM12W-24.5760MHZ-8-J2J-T3](#) [ABM12W-24.0000MHZ-7-J2J-T3](#) [ABM12W-27.0000MHZ-6-B1U-T3](#) [ABM12W-38.8800MHZ-8-D1X-T3](#) [ABM12W-33.0000MHZ-8-B1U-T3](#) [ABM12W-24.5455MHZ-4-D2X-T3](#) [ABM12W-38.8800MHZ-7-K1J-T3](#) [ABM12W-33.0000MHZ-6-B1U-T3](#) [ABM12W-33.0000MHZ-8-K1J-T3](#) [ABM12W-33.3333MHZ-7-J2Z-T3](#) [ABM12W-37.0500MHZ-8-D1X-T3](#) [ABM12W-38.4000MHZ-7-D2X-T3](#) [ABM12W-24.5455MHZ-6-J1J-T3](#) [ABM12W-33.0000MHZ-7-D1X-T3](#) [ABM12W-38.8800MHZ-7-K2J-T3](#) [ABM12W-37.0500MHZ-8-K1J-T3](#) [ABM12W-24.5454MHZ-6-D1X-T3](#) [ABM12W-24.0000MHZ-7-J1J-T3](#) [ABM12W-37.4000MHZ-6-K2J-T3](#) [ABM12W-24.9231MHZ-7-J2Z-T3](#) [ABM12W-38.8800MHZ-7-J1Z-T3](#) [ABM12W-26.0000MHZ-6-J2Z-T3](#) [ABM12W-33.3333MHZ-8-K1Z-T3](#) [ABM12W-24.9231MHZ-8-D1X-T3](#) [ABM12W-33.3300MHZ-7-D2X-T3](#) [ABM12W-30.3200MHZ-4-J1Z-T3](#) [ABM12W-36.0000MHZ-7-K2Z-T3](#) [ABM12W-33.3330MHZ-6-J1Z-T3](#) [ABM12W-38.4000MHZ-6-K1J-T3](#) [ABM12W-37.0500MHZ-6-J1J-T3](#) [ABM12W-38.8800MHZ-6-K2Z-T3](#) [ABM12W-32.0000MHZ-7-B1U-T3](#) [ABM12W-24.5455MHZ-6-K1J-T3](#) [ABM12W-24.5727MHZ-8-K2Z-T3](#) [ABM12W-24.5727MHZ-8-J1Z-T3](#) [ABM12W-24.0000MHZ-8-K2Z-T3](#) [ABM12W-37.4000MHZ-8-J2Z-T3](#) [ABM12W-37.0500MHZ-8-K1Z-T3](#) [ABM12W-40.0000MHZ-4-J1J-T3](#) [ABM12W-26.0000MHZ-4-B1U-T3](#) [ABM12W-24.0000MHZ-6-D2X-T3](#) [ABM12W-24.5727MHZ-7-J2J-T3](#) [ABM12W-26.0410MHZ-8-K1Z-T3](#) [ABM12W-33.3300MHZ-7-K1Z-T3](#) [ABM12W-30.0000MHZ-4-D2X-T3](#) [ABM12W-24.9231MHZ-7-K1Z-T3](#) [ABM12W-33.0000MHZ-7-D2X-T3](#) [ABM12W-25.0000MHZ-7-K2Z-T3](#) [ABM12W-37.0000MHZ-6-B1U-T3](#) [ABM12W-37.0500MHZ-6-D1X-T3](#) [ABM12W-24.5760MHZ-7-B2U-T3](#) [ABM12W-25.0000MHZ-8-D2X-T3](#) [ABM12W-38.4000MHZ-7-B1U-T3](#) [ABM12W-33.0000MHZ-7-B2U-T3](#) [ABM12W-33.0000MHZ-8-B2U-T3](#) [ABM12W-24.5454MHZ-8-J2J-T3](#) [ABM12W-24.0000MHZ-8-J2Z-T3](#) [ABM12W-38.8800MHZ-4-J2Z-T3](#) [ABM12W-33.3333MHZ-6-K2Z-T3](#) [ABM12W-24.5760MHZ-6-D2X-T3](#) [ABM12W-29.4912MHZ-4-B2U-T3](#) [ABM12W-24.5455MHZ-8-D1X-T3](#) [ABM12W-24.5454MHZ-8-K2Z-T3](#) [ABM12W-24.5535MHZ-8-K2Z-T3](#) [ABM12W-33.3333MHZ-6-K1J-T3](#) [ABM12W-24.9231MHZ-8-K2J-T3](#) [ABM12W-37.4000MHZ-8-B2U-T3](#) [ABM12W-38.4000MHZ-6-B1U-T3](#) [ABM12W-38.0000MHZ-8-J2Z-T3](#) [ABM12W-36.0000MHZ-7-K2J-T3](#) [ABM12W-32.0000MHZ-8-D2X-T3](#) [ABM12W-48.0000MHZ-8-D2X-T3](#) [ABM12W-33.3330MHZ-8-D2X-T3](#) [ABM12W-24.9231MHZ-7-B2U-T3](#) [ABM12W-24.5455MHZ-7-B1U-T3](#) [ABM12W-25.0000MHZ-6-D2X-T3](#) [ABM12W-37.0000MHZ-7-J2J-T3](#) [ABM12W-38.4000MHZ-6-J2J-T3](#) [ABM12W-33.3300MHZ-4-J1Z-T3](#) [ABM12W-24.5454MHZ-7-J2Z-T3](#) [ABM12W-30.0000MHZ-6-J2J-T3](#) [ABM12W-37.0000MHZ-6-D2X-T3](#) [ABM12W-24.0000MHZ-7-D2X-T3](#) [ABM12W-30.0000MHZ-8-D1X-T3](#) [ABM12W-26.0410MHZ-6-K2Z-T3](#) [ABM12W-33.3333MHZ-6-B1U-T3](#) [ABM12W-32.0000MHZ-7-J1Z-T3](#) [ABM12W-38.8800MHZ-7-J2J-T3](#) [ABM12W-24.5535MHZ-8-](#)

[B2U-T3](#) [ABM12W-24.5760MHZ-7-K1J-T3](#) [ABM12W-24.5760MHZ-6-B2U-T3](#) [ABM12W-40.0000MHZ-7-K1J-T3](#)