



# MS17349 and MS17350 Protective Receptacle and Plug Covers



**MATING CONNECTOR**  
MIL-DTL-22992



**TABLE I: Dash Number, Thread, Attachment and Dimensions**

Dash No.	E Thread	G Max	H Max	J Chain Length (Inches)	L Min	M Dia Min
12	.8750-0.1P-0.2L-DS	1.094 (27.8)	.765 (19.4)	5.00 (127.0)	1.016 (25.8)	.150 (3.8)
14	1.0000-0.1P-0.2L-DS	1.219 (31.0)	.765 (19.4)	5.00 (127.0)	1.141 (29.0)	.150 (3.8)
16	1.1250-0.1P-0.2L-DS	1.344 (34.1)	.980 (24.9)	5.00 (127.0)	1.266 (32.2)	.150 (3.8)
18	1.2500-0.1P-0.2L-DS	1.469 (37.3)	.980 (24.9)	5.00 (127.0)	1.391 (35.3)	.177 (4.5)
20	1.3750-0.1P-0.2L-DS	1.562 (39.7)	.980 (24.9)	5.00 (127.0)	1.516 (38.5)	.177 (4.5)
22	1.5000-0.1P-0.2L-DS	1.688 (42.9)	.980 (24.9)	6.00 (152.4)	1.641 (41.7)	.177 (4.5)
24	1.7500-0.1P-0.2L-DS	1.938 (49.2)	.980 (24.9)	6.00 (152.4)	1.891 (48.0)	.177 (4.5)
28	2.0000-0.1P-0.2L-DS	2.219 (56.4)	.980 (24.9)	6.00 (152.4)	2.141 (54.4)	.177 (4.5)
32	2.2500-0.1P-0.2L-DS	2.469 (62.7)	.980 (24.9)	6.00 (152.4)	2.391 (60.7)	.199 (5.1)
36	2.5000-0.1P-0.2L-DS	2.719 (69.1)	.980 (24.9)	6.00 (152.4)	2.641 (67.1)	.199 (5.1)
40	2.7500-0.1P-0.2L-DS	2.969 (75.4)	.980 (24.9)	6.00 (152.4)	2.891 (73.4)	.199 (5.1)
44	3.0000-0.1P-0.2L-DS	3.219(81.8)	.980 (24.9)	6.00 (152.4)	3.141 (79.8)	.199 (5.1)

- APPLICATION NOTES**
1. Assembly identified with manufacturer's name and part number, space permitting.
  2. For complete dimensions, see the applicable Military Specification.
  3. Metric dimensions (mm) are in parentheses.

Dimensions in inches (millimeters) and are subject to change without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Glenair:

[MS17349C18A](#) [MS17349C24A](#) [MS17350C24](#) [MS17349N18B](#) [MS17349C32B](#) [MS17349C36B](#) [MS17349C12A](#)  
[MS17349C12B](#) [MS17349C14A](#) [MS17349C14B](#) [MS17349C16A](#) [MS17349C16B](#) [MS17349C18B](#) [MS17349C24B](#)  
[MS17349C28A](#) [MS17349C28B](#) [MS17349C32A](#) [MS17349C36A](#) [MS17349C40A](#) [MS17349C44B](#) [MS17349N12A](#)  
[MS17349N12B](#) [MS17349N14A](#) [MS17349N14B](#) [MS17349N16A](#) [MS17349N16B](#) [MS17349N18A](#) [MS17349N20A](#)  
[MS17349N20B](#) [MS17349N22A](#) [MS17349N22B](#) [MS17349N24A](#) [MS17349N28A](#) [MS17349N28B](#) [MS17349N32B](#)  
[MS17349N36A](#) [MS17349N36B](#) [MS17349N40B](#) [MS17349N44B](#) [MS17350C12](#) [MS17350C14](#) [MS17350C16](#)  
[MS17350C18](#) [MS17350C20](#) [MS17350C22](#) [MS17350C28](#) [MS17350C32](#) [MS17350C36](#) [MS17350C40](#) [MS17350C44](#)  
[MS17350N12](#) [MS17350N14](#) [MS17350N16](#) [MS17350N18](#) [MS17350N20](#) [MS17350N22](#) [MS17350N24](#)  
[MS17350N28](#) [MS17350N32](#) [MS17350N36](#) [MS17350N40](#) [MS17350N44](#) [MS17349C20A](#) [MS17349C20B](#)  
[MS17349C22A](#) [MS17349C22B](#) [MS17349N24B](#) [MS17349N32A](#) [MS17349C40B](#)