


**Product:** [9L26010](#) 

Flat Gray Ribbon Cable .050" Pitch, 9L260XX Series, #26-10c, PVC Ins

## Product Description

Flat Gray Ribbon Cable .050" Pitch, 9L260XX Series, 10 Conductor, 26 AWG (7x34) Tinned Copper, PVC Insulation

## Technical Specifications

### Product Overview

Suitable Applications:	Internal interconnection, internal wiring of electronic equipment, reliable mass-termination to standard IDC connectors
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material
26	7x34	TC - Tinned Copper

Conductor Count:	10
------------------	----

#### Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.010 in

#### Color Chart

Color
Gray

Table Notes:	First Conductor has Blue Stripe
--------------	---------------------------------

### Construction and Dimensions

Conductor Spacing Center-Center:	.050 +/- .002 in
Conductor Spacing Center-Center Outside:	.450 +/- .006 in
OuterJacket1, Nominal Width:	.500 +/- .006 in
OuterJacket1, Nom Thick Flat Section:	0.039 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR
43 Ohm/1000ft

#### Capacitance

Element	Nom. Capacitance Conductor to Conductor
@ 1 kHz (GSG)	23 pF/ft
@ 1 MHz (GS)	11 pF/ft
@ 1 MHz (GSG)	18 pF/ft

Min Insulation Resistance:	10,000 MOhm
----------------------------	-------------

#### Inductance

Element	Nominal Inductance
@ 1 MHz (GS)	0.23 $\mu$ H/ft

@ 1 MHz (GSG)	0.15 µH/ft
---------------	------------

#### Impedance

Nominal Characteristic Impedance	Nominal Characteristic Impedance Description
135 Ohm	(GS)
90 Ohm	(GSG)

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
10 MHz	3.9 dB/100ft
20 MHz	6.4 dB/100ft
30 MHz	8.7 dB/100ft
40 MHz	13 dB/100ft
50 MHz	16.9 dB/100ft
60 MHz	20.1 dB/100ft
70 MHz	22.5 dB/100ft
80 MHz	23.9 dB/100ft
90 MHz	25.1 dB/100ft
100 MHz	26.4 dB/100ft

Table Notes:	GS=Ground-Signal Mode; GSG=Ground-Signal-Ground Mode
--------------	--

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.48 ns/ft	68%

#### Unbalanced Crosstalk

Element	Typical Unbalanced NEXT %	Typical Unbalanced FEXT %	Typical Cross Talk Pulse Rise Time (ns)
10 ft. sample length	5.2	6.2	3 ns
10 ft. sample length	4.2	5	5 ns
10 ft. sample length	3.3	3.8	7 ns

#### Current

Max. Recommended Current [A]
1.5 Amps per Conductor at 20°C

#### Voltage

Dielectric Withstand Voltage	UL Voltage Rating
2000 V	300 V

#### Temperature Range

Operating Temp Range:	-40°C to +105°C
-----------------------	-----------------

#### Mechanical Characteristics

Bulk Cable Weight:	16 lbs/1000ft
Min. Bend Radius During Installation:	2.0 in
Min. Bend Radius/Minor Axis:	0.5 in

#### Standards

UL AWM Style Compliance:	2651
CSA AWM Compliance:	1 A

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
CSA Flammability:	FT1
UL voltage rating:	300 V

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Length	UPC
9L26010 008H100	Gray	100 ft	612825221517
9L26010 008H300	Gray	300 ft	612825221524

## History

Update and Revision:	Revision Number: 0.392 Revision Date: 12-15-2021
----------------------	--

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9L26010 008H100](#) [9L26010 008H300](#)