



MS8910 Smart SMD Tester

Display: 3000 counts LCD display.

Auto Scanning & Auto Ranging function. Therefore, fully automatic detecting the chip type resistance, capacitance or diode measurement.

The construction of tester is compact and small type. So it is as portable Testing set.

The test leads is special construction and fixed on the main body for convenience of user.

Data HOLD function

Low-Battery Indication

Auto Power OFF.

Operating temperature & Humidity: 0 ~ 40°C (32 ~ 104 °F) & < 80% RH

Storage temperature & Humidity: -10 ~ 50°C (14 ~ 122 °F) & < 70%RH

Power supply: 3V Lithium Battery 1 pcs.

"FUNC" key is used to selecting any measurement mode.

Dimension[L x W x H]: 175 x 32 x 19mm

Specifications

Function	Range	Best Resolution	Accuracy
Resistance	300/3K/30K/300K/3M/30M	0.1 Ω	±(1%rdg+3dgt)
Capacitance	3nF/30nF/300nF/3uF/30uF/300uF/3mF/30mF	1pF	±(2%rdg+3dgt)
Continuity Check.	When the resistance is less than 30 Ω, the Buzzer is sounded.		
Diode Check	✓		