




Precision Thin Film Chip Resistors



FEATURES

- Rated dissipation P_{70} up to 0.4 W for size 1206
- AEC-Q200 qualified
- Approved to EN 140401-801
- Superior temperature cycling robustness
- Superior moisture resistivity, $|\Delta R/R| < 0.5\%$ (85 °C; 85 % RH; 1000 h)
- Advanced sulfur resistance verified according to ASTM B 809
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

RoHS
COMPLIANT

Vishay Automotive Grade MC AT precision thin film chip resistors are the perfect choice for most fields of modern precision electronics where reliability and stability is of major concern. Typical applications include automotive, industrial, telecommunication and medical equipment, as well as precision test and measuring equipment.

APPLICATIONS

- Automotive
- Industrial equipment
- Telecommunication
- Medical equipment

TECHNICAL SPECIFICATIONS

DESCRIPTION	MCS 0402 AT	MCT 0603 AT ⁽²⁾	MCU 0805 AT	MCA 1206 AT
Imperial size	0402	0603	0805	1206
Metric size code	RR1005M	RR1608M	RR2012M	RR3216M
Resistance range	47 Ω to 221 k Ω	47 Ω to 511 k Ω	47 Ω to 1 M Ω	47 Ω to 10 M Ω
Resistance tolerance	$\pm 0.1\%$			
Temperature coefficient	± 25 ppm/K; ± 15 ppm/K; ± 10 ppm/K	± 25 ppm/K; ± 15 ppm/K; ± 10 ppm/K; ± 5 ppm/K	± 25 ppm/K; ± 15 ppm/K; ± 10 ppm/K	
Rated dissipation P_{70} ⁽¹⁾	0.100 W	0.125 W	0.200 W	0.400 W
Operating voltage, U_{max} , AC _{RMS} /DC	50 V	75 V	150 V	200 V
Permissible film temperature, $\vartheta_{F max}$ ⁽¹⁾	155 °C			
Operating temperature range	-55 °C to 155 °C			
Internal thermal resistance ⁽¹⁾	90 K/W	63 K/W	38 K/W	32 K/W
Permissible voltage against ambient (insulation): 1 min; U_{ins}	75 V	100 V	200 V	300 V
Failure rate: FIT _{observed}	$\leq 0.1 \times 10^{-9}/h$			

Notes

⁽¹⁾ Please refer to APPLICATION INFORMATION, see below

⁽²⁾ AEC-Q200 qualification for TCR ± 5 ppm/K pending, CECC not applicable for TCR ± 5 ppm/K



APPLICATION INFORMATION

When the resistor dissipates power, a temperature rise above the ambient temperature occurs, dependent on the thermal resistance of the assembled resistor together with the printed circuit board. The rated dissipation applies only if the permitted film temperature is not exceeded.

Please consider the application note “Thermal Management in Surface-Mounted Resistor Applications” (www.vishay.com/doc?28844) for information on the general nature of thermal resistance.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.

MAXIMUM RESISTANCE CHANGE AT RATED DISSIPATION			
OPERATION MODE		STANDARD	POWER
Rated dissipation, P_{70}	MCS 0402 AT	0.063 W	0.100 W
	MCT 0603 AT	0.100 W	0.125 W
	MCU 0805 AT	0.125 W	0.200 W
	MCA 1206 AT	0.250 W	0.400 W
Operating temperature range		-55 °C to 125 °C	-55 °C to 155 °C
Permissible film temperature, ϑ_F max.		125 °C	155 °C
Max. resistance change at P_{70} for resistance range, $ \Delta R/R $ after:	MCS 0402 AT	47 Ω to 221 k Ω	47 Ω to 221 k Ω
	MCT 0603 AT	47 Ω to 511 k Ω	47 Ω to 511 k Ω
	MCU 0805 AT	47 Ω to 1 M Ω	47 Ω to 1 M Ω
	MCA 1206 AT	47 Ω to 10 M Ω	47 Ω to 10 M Ω
	1000 h	≤ 0.1 %	≤ 0.2 %
	8000 h	≤ 0.2 %	≤ 0.4 %
	225 000 h	≤ 0.6 %	-

Note

- The presented operation modes do not refer to different types of resistors, but actually show examples of different loads, that lead to different film temperatures and different achievable load-life stability (drift) of the resistance value. A suitable low thermal resistance of the circuit board assembly must be safeguarded in order to maintain the film temperature of the resistors within the specified limits. Please consider the application note “Thermal Management in Surface-Mounted Resistor Applications” (www.vishay.com/doc?28844) for information on the general nature of thermal resistance

TEMPERATURE COEFFICIENT AND RESISTANCE RANGE				
TYPE / SIZE	TCR	TOLERANCE	RESISTANCE	E-SERIES
MCS 0402 AT	± 25 ppm/K	± 0.1 %	47 Ω to 221 k Ω	E24; E192
	± 15 ppm/K		47 Ω to 100 k Ω	
	± 10 ppm/K		47 Ω to 10 k Ω	
MCT 0603 AT	± 25 ppm/K	± 0.1 %	47 Ω to 511 k Ω	E24; E192
	± 15 ppm/K		47 Ω to 221 k Ω	
	± 10 ppm/K		47 Ω to 100 k Ω	
	± 5 ppm/K		3.9 k Ω to 100 k Ω	
MCU 0805 AT	± 25 ppm/K	± 0.1 %	47 Ω to 1 M Ω	E24; E192
	± 15 ppm/K		47 Ω to 332 k Ω	
	± 10 ppm/K		47 Ω to 33.2 k Ω	
MCA 1206 AT	± 25 ppm/K	± 0.1 %	47 Ω to 10 M Ω	E24; E192
	± 15 ppm/K		47 Ω to 511 k Ω	
	± 10 ppm/K		47 Ω to 43.2 k Ω	



PACKAGING						
TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS
MCS 0402 AT	E1	1000	Paper tape acc. IEC 60286-3, type 1a	8 mm	2 mm	Ø 180 mm / 7"
	E5	5000				
	E0	10 000				
MCT 0603 AT	P1	1000			4 mm	Ø 180 mm / 7"
	P5	5000				Ø 330 mm / 13"
	PW	20 000				Ø 330 mm / 13"
MCU 0805 AT	P1	1000				Ø 180 mm / 7"
	P5	5000				Ø 330 mm / 13"
	PW	20 000				Ø 330 mm / 13"
MCA 1206 AT	P1	1000				Ø 180 mm / 7"
	P5	5000				

PART NUMBER AND PRODUCT DESCRIPTION																	
Part Number: MCT0603MD4641BPW00																	
M	C	T	0	6	0	3	M	D	4	6	4	1	B	P	W	0	0
TYPE/SIZE			VERSION			TCR			RESISTANCE			TOLERANCE		PACKAGING			
MCS0402 MCT0603 MCU0805 MCA1206			M = AT (automotive)			G = ± 5 ppm/K F = ± 10 ppm/K E = ± 15 ppm/K D = ± 25 ppm/K			3 digit value 1 digit multiplier Multiplier 9 = *10 ⁻¹ 0 = *10 ⁰ 1 = *10 ¹ 2 = *10 ² 3 = *10 ³ 4 = *10 ⁴ 5 = *10 ⁵			B = ± 0.1 %		E1 E5 E0 P1 P5 PW			
Product Description: MCT 0603-25 0.1 % AT PW 4K64																	
MCT	0603	-25	0.1 %	AT	PW	4K64											
TYPE	SIZE	TCR	TOLERANCE	VERSION	PACKAGING	RESISTANCE											
MCS MCT MCU MCA	0402 0603 0805 1206	± 5 ppm/K ± 10 ppm/K ± 15 ppm/K ± 25 ppm/K	± 0.1 %	AT = automotive	E1 E5 E0 P1 P5 PW	4K64 = 4.64 kΩ											

Note

- Products can be ordered using either the PART NUMBER or PRODUCT DESCRIPTION



DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous film of special metal alloy is deposited on a high grade ceramic substrate (Al_2O_3) and conditioned to achieve the desired temperature coefficient. Specially designed inner contacts are deposited on both sides. A special laser is used to achieve the target value by smoothly cutting a meander groove in the resistive layer without damaging the ceramics. The resistor elements are covered by a unique protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure matte tin on nickel plating.

The result of the determined production is verified by an extensive testing procedure and optical inspection performed on 100 % of the individual chip resistors. This includes full screening for the elimination of products with potential risk of early field failures (feasible for $R \geq 10 \Omega$). Only accepted products are laid directly into the paper tape in accordance with **IEC 60286-3 Type 1a** ⁽¹⁾.

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapour phase as shown in **IEC 61760-1** ⁽¹⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

The resistors are RoHS-compliant; the pure matte tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. Solderability is specified for 2 years after production or requalification. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein ⁽²⁾
- The Global Automotive Declarable Substance List (GADSL) ⁽³⁾
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) ⁽⁴⁾ for its supply chain

Notes

- ⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents
- ⁽²⁾ The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at <http://std.iec.ch/iec62474>
- ⁽³⁾ The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at www.gadsl.org
- ⁽⁴⁾ The SVHC list is maintained by the European Chemical Agency (ECHA) and available at <http://echa.europa.eu/candidate-list-table>

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

APPROVALS

The resistors are approved within the IECQ-CECC Quality Assessment System for Electronic Components to the detail specification **EN 140401-801** which refers to **EN 60115-1**, **EN 60115-8** and the variety of environmental test procedures of the **IEC 60068** ⁽¹⁾ series. The detail specification refers to the climatic categories 55/125/56, which relates to the “standard operation mode” of this datasheet.

Conformity is attested by the use of the **CECC** logo () as the mark of conformity on the package label.

Vishay Beyschlag has achieved “**Approval of Manufacturer**” in accordance with **IECQ 03-1**. The release certificate for “**Technology Approval Schedule**” in accordance with **CECC 240001** based on **IECQ 03-3-1** is granted for the Vishay Beyschlag manufacturing process.

The resistors are qualified according to AEC-Q200.

RELATED PRODUCTS

For more information about products with higher operation temperature please refer to the **MC AT - Professional** datasheet (www.vishay.com/doc?28760).

Chip resistor arrays may be used in sensing applications or precision amplifiers where close matching between multiple resistors is necessary. Please refer to the **ACAS AT - Precision** datasheet (www.vishay.com/doc?28770).

MC AT - Precision is also available with gold termination for conductive gluing: **MC ATAU - Precision**. Please refer to the datasheet (www.vishay.com/doc?28877).


For high power and high temperature applications **MCW AT** wide terminal thin film chip resistors offer extremely high power ratings and extraordinary temperature cycling robustness.

Please refer to the datasheets for precision (www.vishay.com/doc?28847) and professional (www.vishay.com/doc?28796) specification.


These wide-terminal products are also available in low-ohmic values, **NCW AT** (www.vishay.com/doc?28849).




FUNCTIONAL PERFORMANCE



Derating - Standard Operation



Derating - Power Operation



Current noise A_1 in accordance with IEC 60195

Current Noise



TESTS AND REQUIREMENTS

All tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification

EN 60115-8 (successor of EN 140400), sectional specification

EN 140401-801, detail specification

IEC 60068-2-xx, test methods

The components are approved under the IECQ-CECC quality assessment system for electronic components.

The parameters stated in the Test Procedures and Requirements table are based on the required tests and permitted limits of EN 140401-801. The table presents only the most important tests, for the full test schedule refer to the documents listed above. However, some additional tests and a number of improvements against those minimum requirements have been included.

The testing also covers most of the requirements specified by EIA/ECA-703 and JIS-C-5201-1.

The tests are carried out under standard atmospheric conditions in accordance with IEC 60068-1, 4.3, whereupon the following values are applied:

Temperature: 15 °C to 35 °C

Relative humidity: 25 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar)

A climatic category LCT / UCT / 56 is applied, defined by the lower category temperature (LCT), the upper category temperature (UCT), and the duration of exposure in the damp heat, steady state test (56 days).

The components are mounted for testing on printed circuit boards in accordance with EN 60115-8, 2.4.2, unless otherwise specified.

TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 ⁽¹⁾ TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)
				STABILITY CLASS 0.25 OR BETTER ⁽²⁾
			Stability for product types:	
			MCS 0402 AT	47 Ω to 221 k Ω
			MCT 0603 AT	47 Ω to 511 k Ω
			MCU 0805 AT	47 Ω to 1 M Ω
			MCA 1206 AT	47 Ω to 10 M Ω
4.5	-	Resistance		$\pm 0.1 \% R$
4.8	-	Temperature coefficient	At (20 / -55 / 20) °C and (20 / 155 / 20) °C	± 25 ppm/K; ± 15 ppm/K; ± 10 ppm/K; ± 5 ppm/K
4.25.1	-	Endurance at 70 °C: Standard operation mode	$U = \sqrt{P_{70} \times \bar{R}}$ or $U = U_{\max.}$; whichever is the less severe; 1.5 h on; 0.5 h off; 70 °C; 1000 h 70 °C; 8000 h	$\pm (0.1 \% R + 0.02 \Omega)$ $\pm (0.2 \% R + 0.02 \Omega)$
		Endurance at 70 °C: Power operation mode	$U = \sqrt{P_{70} \times \bar{R}}$ or $U = U_{\max.}$; whichever is the less severe; 1.5 h on; 0.5 h off; 70 °C; 1000 h 70 °C; 8000 h	$\pm (0.2 \% R + 0.02 \Omega)$ $\pm (0.4 \% R + 0.05 \Omega)$
4.25.3	-	Endurance at upper category temperature	125 °C; 1000 h 155 °C; 1000 h	$\pm (0.15 \% R + 0.02 \Omega)$ $\pm (0.3 \% R + 0.02 \Omega)$
4.24	78 (Cab)	Damp heat, steady state	(40 $\pm$ 2) °C; 56 days; (93 $\pm$ 3) % RH	$\pm (0.1 \% R + 0.02 \Omega)$
4.37	67 (Cy)	Damp heat, steady state, accelerated Standard operation mode	(85 $\pm$ 2) °C (85 $\pm$ 5) % RH $U = \sqrt{0.1 \times P_{70} \times \bar{R}}$; $U \leq 0.3 \times U_{\max.}$; 1000 h	$\pm (0.5 \% R + 0.05 \Omega)$



TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 ⁽¹⁾ TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)
				STABILITY CLASS 0.25 OR BETTER ⁽²⁾
			Stability for product types:	
			MCS 0402 AT	47 Ω to 221 k Ω
			MCT 0603 AT	47 Ω to 511 k Ω
			MCU 0805 AT	47 Ω to 1 M Ω
			MCA 1206 AT	47 Ω to 10 M Ω
4.23	2 (Bb) 30 (Db) 1 (Ab) 13 (M) 30 (Db) -	Climatic sequence: Standard operation mode	125 °C; 16 h 55 °C; 24 h; ≥ 90 % RH; 1 cycle -55 °C; 2 h 8.5 kPa; 2 h; (25 $\pm$ 10) °C 55 °C; 24 h; ≥ 90 % RH; 5 cycles $U = \sqrt{P_{70}} \times \bar{R} \leq U_{\max.}$; 1 min	$\pm (0.25 \% R + 0.02 \Omega)$
4.23.2		Dry heat		
4.23.3		Damp heat, cyclic		
4.23.4		Cold		
4.23.5		Low air pressure		
4.23.6		Damp heat, cyclic		
4.23.7		DC load		
-	1 (Aa)	Storage at low temperature	-55 °C; 2 h	$\pm (0.05 \% R + 0.01 \Omega)$
4.19	14 (Na)	Rapid change of temperature	30 min at -55 °C and 30 min at 155 °C; 1000 cycles	$\pm (0.25 \% R + 0.02 \Omega)$
		Extended rapid change of temperature	30 min at -40 °C; 30 min at 125 °C ⁽³⁾ ; MCS 0402 AT: 3000 cycles MCT 0603 AT: 2000 cycles MCU 0805 AT: 1500 cycles MCA 1206 AT: 1000 cycles	$\pm (0.25 \% R + 0.05 \Omega)$; (≥ 50 % of initial shear force)
4.13	-	Short time overload: Standard operation mode	$U = 2.5 \times \sqrt{P_{70}} \times \bar{R}$ or $U = 2 \times U_{\max.}$; whichever is the less severe; 5 s	$\pm (0.05 \% R + 0.01 \Omega)$
4.27	-	Single pulse high voltage overload: Standard operation mode	Severity no. 4: $U = 10 \times \sqrt{P_{70}} \times \bar{R}$ or $U = 2 \times U_{\max.}$; whichever is the less severe; 10 pulses 10 μ s/700 μ s	$\pm (0.25 \% R + 0.05 \Omega)$
4.39	-	Periodic electric overload: Standard operation mode	$U = \sqrt{15 \times P_{70}} \times \bar{R}$ or $U = 2 \times U_{\max.}$; whichever is the less severe; 0.1 s on; 2.5 s off; 1000 cycles	$\pm (0.5 \% R + 0.05 \Omega)$
4.38	-	Electro static discharge (human body model)	IEC 61340-3-1 ⁽¹⁾ ; 3 pos. + 3 neg. (equivalent to MIL-STD-883, method 3015) MCS 0402 AT: 500 V MCT 0603 AT: 1000 V MCU 0805 AT: 1500 V MCA 1206 AT: 2000 V	$\pm (0.5 \% R + 0.05 \Omega)$




TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 ⁽¹⁾ TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)
				STABILITY CLASS 0.25 OR BETTER ⁽²⁾
			Stability for product types:	
			MCS 0402 AT	47 Ω to 221 k Ω
			MCT 0603 AT	47 Ω to 511 k Ω
			MCU 0805 AT	47 Ω to 1 M Ω
			MCA 1206 AT	47 Ω to 10 M Ω
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude ≤ 1.5 mm or ≤ 200 m/s ² ; 7.5 h	$\pm (0.05 \% R + 0.01 \Omega)$ no visible damage
4.17	58 (Td)	Solderability	Solder bath method; SnPb40; non-activated flux (215 $\pm$ 3) $^{\circ}$ C; (3 $\pm$ 0.3) s	Good tinning ($\geq 95 \%$ covered); no visible damage
			Solder bath method; SnAg3Cu0.5 or SnAg3.5; non-activated flux; (235 $\pm$ 3) $^{\circ}$ C; (2 $\pm$ 0.2) s	Good tinning ($\geq 95 \%$ covered); no visible damage
4.18	58 (Td)	Resistance to soldering heat	Solder bath method; (260 $\pm$ 5) $^{\circ}$ C; (10 $\pm$ 1) s	$\pm (0.05 \% R + 0.01 \Omega)$ ⁽⁴⁾
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol +50 $^{\circ}$ C; method 2	No visible damage
4.32	21 (Ue ₃)	Shear (adhesion)	MCS 0402 AT and MCT 0603 AT; 9 N	No visible damage
			MCU 0805 AT and MCA 1206 AT; 45 N	
4.33	21 (Ue ₁)	Substrate bending	Depth 2 mm, 3 times	$\pm (0.05 \% R + 0.01 \Omega)$ no visible damage; no open circuit in bent position
4.7	-	Voltage proof	$U_{RMS} = U_{ins}$; (60 $\pm$ 5) s	No flashover or breakdown
4.35	-	Flammability	IEC 60695-11-5 ⁽¹⁾ , needle flame test; 10 s	No burning after 30 s

Notes


- ⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents
- ⁽²⁾ According to the detail specification EN 140401-801 the stability class applies to the category temperatures 85 °C and 125 °C and their respective test conditions
- ⁽³⁾ Tested on a 4-layer printed circuit board with SAC micro alloy
- ⁽⁴⁾ For resistance values above 1 M Ω in case size 1206: $\pm (0.10 \% R + 0.01 \Omega)$

DIMENSIONS



DIMENSIONS AND MASS							
TYPE / SIZE	H (mm)	L (mm)	W (mm)	W _T (mm)	T _t (mm)	T _b (mm)	MASS (mg)
MCS 0402 AT	0.32 ± 0.05	1.0 ± 0.05	0.5 ± 0.05	> 75 % of W	0.2 + 0.1/- 0.15	0.2 ± 0.1	0.6
MCT 0603 AT	0.45 + 0.1/- 0.05	1.55 ± 0.05	0.85 ± 0.1	> 75 % of W	0.3 + 0.15/- 0.2	0.3 + 0.15/- 0.2	1.9
MCU 0805 AT	0.52 ± 0.1	2.0 ± 0.1	1.25 ± 0.15	> 75 % of W	0.4 + 0.1/- 0.2	0.4 + 0.1/- 0.2	4.6
MCA 1206 AT	0.55 ± 0.1	3.2 + 0.1/- 0.2	1.6 ± 0.15	> 75 % of W	0.5 ± 0.25	0.5 ± 0.25	9.2

SOLDER PAD DIMENSIONS



RECOMMENDED SOLDER PAD DIMENSIONS								
TYPE / SIZE	WAVE SOLDERING				REFLOW SOLDERING			
	G (mm)	Y (mm)	X (mm)	Z (mm)	G (mm)	Y (mm)	X (mm)	Z (mm)
MCS 0402 AT	-	-	-	-	0.35	0.55	0.55	1.45
MCT 0603 AT	0.55	1.10	1.10	2.75	0.65	0.70	0.95	2.05
MCU 0805 AT	0.80	1.25	1.50	3.30	0.90	0.90	1.40	2.70
MCA 1206 AT	1.40	1.50	1.90	4.40	1.50	1.15	1.75	3.80

Notes

- The given solder pad dimensions reflect the considerations for board design and assembly as outlined e.g. in standards IEC 61188-5-x ⁽¹⁾, or in publication IPC-7351

⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

MCT0603MD1000BP100	MCT0603MD1001BP100	MCT0603MD1002BP100	MCT0603MD1003BP100
MCT0603MD1500BP100	MCT0603MD1501BP100	MCT0603MD1502BP100	MCT0603MD3320BP100
MCT0603MD3321BP100	MCT0603MD3322BP100	MCT0603MD4700BP100	MCT0603MD4701BP100
MCT0603MD4702BP100	MCT0603MD7502BP100	MCU0805MD1003BP100	MCT0603MD1331BP100
MCU0805MD5111BP100	MCS0402MD2491BE100	MCT0603MD5112BP100	MCA1206MD7502BP100
MCS0402MD4751BE100	MCU0805MD4990BP100	MCT0603MD2001BP100	MCS0402MD7509BE100
MCU0805MD2001BP100	MCA1206MD2001BP100	MCS0402MD1002BE100	MCS0402MD7501BE100
MCT0603MD3011BP100	MCS0402MD1502BE100	MCT0603MD1102BP100	MCA1206MD1502BP100
MCT0603MD5361BP100	MCU0805MD3322BP100	MCT0603MD2492BP100	MCT0603MD2432BP100
MCA1206MD2490BP100	MCS0402MD2002BE100	MCT0603MD9091BP100	MCT0603MD2002BP100
MCU0805MD2211BP100	MCS0402MD1000BE100	MCT0603MD3922BP100	MCS0402MD1501BE100
MCU0805MD4992BP100	MCU0805MD1502BP100	MCS0402MD4022BE100	MCT0603MD4990BP100
MCA1206MD4990BP100	MCA1206MD4999BP100	MCT0603MD1402BP100	MCU0805MD2002BP100
MCT0603MD4999BP100	MCS0402MD4702BE100	MCU0805MD1000BP100	MCS0402MD2492BE100
MCU0805MD2492BP100	MCT0603MD2490BP100	MCS0402MD1001BE100	MCT0603MD4991BP100
MCS0402MD2211BE100	MCU0805MD5112BP100	MCA1206MD4021BP100	MCU0805MD2491BP100
MCS0402MD4990BE100	MCS0402MD4999BE100	MCT0603MD4021BP100	MCS0402MD2001BE100
MCA1206MD4991BP100	MCA1206MD1001BP100	MCA1206MD1002BP100	MCU0805MD1001BP100
MCU0805MD4991BP100	MCT0603MD1021BP100	MCT0603MD2211BP100	MCU0805MD3011BP100
MCT0603MD7501BP100	MCT0603MD1212BP100	MCU0805MD4751BP100	MCT0603MD2000BP100
MCT0603MD4992BP100	MCA1206MD1000BP100	MCS0402MD2000BE100	MCT0603MD3012BP100
MCA1206MD4992BP100	MCU0805MD1002BP100	MCA1206MD1003BP100	MCT0603MD1202BP100
MCS0402MD3012BE100	MCA1206MD2002BP100	MCU0805MD4021BP100	MCS0402MD4991BE100
MCS0402MD2490BE100	MCT0603MD2321BP100	MCU0805MD4999BP100	MCT0603MD7509BP100
MCU0805MD7502BP100	MCT0603MD2491BP100	MCS0402MD1022BE100	MCA1206MD5111BP100