



3601

3601

MALE STUD, BSP PARALLEL AND METRIC  
for metric tubing

Part No	ØD (mm)	C	E (mm)	F (mm)	F1 (mm)	F2 (mm)	H (mm)	K (mm)	(kg)
3601 04 10	4	G1/8			13,0	3,0	14,5	14,0	0,008
3601 04 13	4	G1/4			16,0	3,0	14,5	17,5	0,013
3601 04 19	4	M5x0,8			10,0	2,5	15,5	11,0	0,005
3601 04 52	4	M6x1			10,0	3,0	16,0	11,0	0,006
3601 04 56	4	M8x1			11,0	3,0	14,5	12,0	0,007
3601 06 10	6	G1/8			13,0	4,0	17,5	14,0	0,009
3601 06 13	6	G1/4			16,0	4,0	17,0	17,5	0,018
3601 06 19	6	M5x0,8			13,0	2,5	19,0	14,0	0,009
3601 06 60	6	M10x1			13,0	4,0	17,5	14,0	0,010
3601 08 10	8	G1/8			15,0	5,0	20,0	16,0	0,015
3601 08 13	8	G1/4			16,0	6,0	18,0	17,5	0,019
3601 08 17	8	G3/8			20,0	6,0	19,0	22,0	0,028



3601  
 MALE STUD, BSP PARALLEL AND METRIC

3601

internal hexagon

maximum working pressure	bar	MPa	psi
	20	2,0	290
working temperature	°C (Celsius)	F (Fahrenheit)	K (Kelvin)
	From -20 to 120	From -4 to 248	From 253 to 393
body	nickel-plated brass		
'O'-rings	Fluoroelastomer FKM (FPM)		
'O'ring	engineering grade polymer		

3601 10 13	10	G1/4	18,0	7,0	25,0	19,5	0,024
3601 10 17	10	G3/8	20,0	8,0	22,5	22,0	0,031
3601 12 13	12	G1/4	20,0	7,0	26,5	22,0	0,029
3601 12 17	12	G3/8	20,0	9,0	26,0	22,0	0,032
3601 12 21	12	G1/2	24,0	10,0	23,5	26,0	0,047
3601 14 17	14	G3/8	22,0	9,0	28,0	24,0	0,042
3601 14 21	14	G1/2	24,0	11,0	26,5	26,0	0,047