Voltage selector switch, 3 stages, step switch, panel mounting



See below:

Approvals and Compliances

Description

- Voltage Selector, 3 stages
- Step switch
- Solder terminals

References

Alternative: version for PCB mounting SWM2 (Print)

Weblinks

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Detailed request for product

Technical Data		
Ratings	IEC: 6.3 A / 250 VAC; 50 Hz	
	UL: 10 A / 250 VAC; 60 Hz	
	CSA: 10 A / 250 VAC; 60 Hz	
Mounting	Panel mount front side	
Attachment	Screw-on mounting	
Terminal	Solder	
Number of Stages	3	
Lifetime	300 operating cycles (without load)	
Degree of Protection	IP40	
Protection Class	Suitable for appliances with protection class II acc. to IEC 61140	
Allowable Operation Temperature	-40 °C to 85 °C	
Climatic Category	25/85/21 acc. to IEC 60068-1	
Material: Socket	Thermoplastic, black, UL 94V-0	
Weight	6.5 g	

Solderability	350 °C / 2 sec acc. to IEC 60068-2-20, Test Ta, method 2
Resistance to Soldering Heat	350°C / 10 sec acc. to IEC 60068-2-20, Test Tb, method 2
Insulation Resistance	> 10'000MΩ (500VDC; 1min)
Contact Resistance	$< 10\text{m}\Omega$ at 20 mV
Dielectric Strength	> 2kVAC between L-N > 4kVAC between L/N-PE (1min; 50Hz)
Clearance and Creepage Distance	> 3mm > 8mm between L/N-PE
Resistance to Vibration	acc. to IEC 60068-2-6, test Fc
Panel Thickness S	max 8mm

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products. Approval Reference Type: SWM

Approval Logo	Certificates	Certification Body	Description
1 0	VDE Approvals	VDE	Certificate Number:
	UL Approvals	UL	UL File Number: E72661

Product standards

Product standards that are referenced

Organization Design Standard Description

Designed according to UL 508 Industrial control equipment

© CSA C22.2 no. 55 Fuseholder general requirements

Application standards

Application standards where the product can be used

 Organization
 Design
 Standard
 Description

 IEC
 Designed for applications acc.
 IEC/UL 62368-1
 IEC 62368-1 includes the basic requirements for safety of audio, video, information technology and office equipment.

 IEC
 Designed for applications acc.
 IEC 60335-1
 Safety of electrical appliances for household and similar purposes. Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 & -13.

Compliances


The product complies with following Guide Lines


 Identification
 Details
 Initiator
 Description


 C E
 CE declaration of conformity
 SCHURTER AG
 The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.

 REACH
 SCHURTER AG
 On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.


Dimension [mm] 23 mm







Panel mounting hole



Diagrams

$$1 = C$$
0
$$5 \bigcirc \longrightarrow \bigcirc 2 = B$$
0
$$3 = A$$

All Variants

	Letterings		Order Number	
Α	В	С		
110	150	220	0033.4001	
110	220	240	0033.4002	
220	240		0033.4003	
200	220	240	0033.4004	
220	240	250	0033.4006	
100	115	230	0033.4008	
220	230	240	0033.4011	
			0033.4014	
115	220	240	0033.4019	
220 V	230 V	240 V	0033.4028	
4	8	16	0033.4032	
100	110	230	0033.4040	
115	0	230	0033.4044	
230	240	250	0033.4049	
115 V	230 V	240 V	0033.4055	
1	2	3	0033.4056	
100	120	230-240	0033.4057	
110		230	0033.4062	

Most Popular.

Availability for all products can be searched real-time:https://www. schurter.com/en/Stock-Check/Stock-Check-SCHURTER

50 Pcs **Packaging Unit**